Articulated foot with solid base foot Ø40 Ste Sta

PTA40
PTA40ss

Accepts loads up to 3000N


- **Articulated foot**
- Up to +/- 5° from vertical
- Materials:
  - ***Steel version:***
    Base: Galvanised sheet steel C40
    Shaft: Galvanised steel (nut not supplied)
    Sole: Vulcanised NBR rubber, hardness 80° Shore
  - ***Stainless steel version:***
    Base: Sheet stainless steel 304
    Shaft: Stainless steel 304 (nut not supplied)
    Sole: Vulcanised NBR rubber, hardness 80° Shore

Option

- Other shaft size available upon request

Stainless steel version, sanded finish





DISCOUNTS

Qty	1+	15+	20+	25+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number bright	Part number sanded finish	ØD	ØF	B	A	A/F	G	H	Static load (N)		Price each 1 to 14
Steel foot											
PTA40-8-25	-	40	M8	25	26	6	15	51	3000	-	11,02 €
PTA40-8-50	-	40	M8	50	26	6	15	76	3000	-	11,44 €
PTA40-8-75	-	40	M8	75	26	6	15	101	3000	-	11,91 €
PTA40-10-25	-	40	M10	25	26	8	15	51	3000	-	11,44 €
PTA40-10-50	-	40	M10	50	26	8	15	76	3000	-	11,91 €
PTA40-10-75	-	40	M10	75	26	8	15	101	3000	-	12,33 €
PTA40-10-100	-	40	M10	100	26	8	15	126	3000	-	12,64 €
PTA40-10-125	-	40	M10	125	26	8	15	152	3000	-	12,80 €
Stainless steel foot											
PTA40-8-25/SS	PTA40-8-25/SS/SB	40	M8	25	26	6	15	51	3000	-	13,40 €
PTA40-8-50/SS	PTA40-8-50/SS/SB	40	M8	50	26	6	15	76	3000	-	13,81 €
PTA40-8-75/SS	PTA40-8-75/SS/SB	40	M8	75	26	6	15	101	3000	-	14,29 €
PTA40-10-25/SS	PTA40-10-25/SS/SB	40	M10	25	26	8	15	51	3000	-	14,59 €
PTA40-10-50/SS	PTA40-10-50/SS/SB	40	M10	50	26	8	15	76	3000	-	15,06 €
PTA40-10-75/SS	PTA40-10-75/SS/SB	40	M10	75	26	8	15	101	3000	-	15,51 €
PTA40-10-100/SS	PTA40-10-100/SS/SB	40	M10	100	26	8	15	126	3000	-	16,40 €
PTA40-10-125/SS	PTA40-10-125/SS/SB	40	M10	125	26	8	15	151	3000	-	17,05 €

All dimensions in mm

Sta Ste Articulated levelling foot, pressed base Ø50

Accepts loads up to 4.000N

PTA50
PTA50ss


Stainless steel version, sanded finish



- **Tilting foot**
- Tilt up to +/- 5° from vertical
- The base of the stainless steel version is available with either a glossy or sandblasted finish
- Materials:

Steel version:
Base: Galvanised sheet steel C40
Spindle: Galvanised steel (nut not supplied)
Sole: Vulcanised NBR rubber, hardness 80° Shore

Stainless steel version:
Base: Sheet stainless steel 304
Spindle: Stainless steel 304 (nut not supplied)
Sole: Vulcanised NBR rubber, hardness 80° Shore



Option

- Other shaft dimensions are available on request

DISCOUNTS

Qty	1+	15+	20+	25+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number bright	Part number sanded finish	ØD	ØF	B	A	A/F	G	H	Static load (N)	Stock* bright	Price each 1 to 14
Steel foot											
PTA50-10-100	-	50	M10	100	29	14	19	129	4000	✔	18,07 €
PTA50-12-100	-	50	M12	100	29	14	19	129	4000	✔	18,07 €
PTA50-12-150	-	50	M12	150	29	14	19	179	4000	-	19,50 €
PTA50-16-75	-	50	M16	75	29	16	19	104	4000	✔	18,55 €
PTA50-16-100	-	50	M16	100	29	16	19	129	4000	-	19,82 €
PTA50-16-150	-	50	M16	150	29	16	19	179	4000	✔	22,47 €
Stainless steel foot											
PTA50-10-75/SS	PTA50-10-75/SS/SB	50	M10	75	29	14	19	104	4000	✔	19,59 €
PTA50-10-125/SS	PTA50-10-125/SS/SB	50	M10	125	29	14	19	154	4000	✔	22,29 €
PTA50-12-75/SS	PTA50-12-75/SS/SB	50	M12	75	29	14	19	104	4000	✔	19,59 €
PTA50-12-125/SS	PTA50-12-125/SS/SB	50	M12	125	29	14	19	154	4000	✔	22,29 €
PTA50-16-75/SS	PTA50-16-75/SS/SB	50	M16	75	34	13	19	109	4000	✔	22,88 €
PTA50-16-100/SS	PTA50-16-100/SS/SB	50	M16	100	34	13	19	134	4000	✔	23,78 €
PTA50-16-150/SS	PTA50-16-150/SS/SB	50	M16	150	34	13	19	184	4000	-	26,16 €

*Depending on availability - Dimensions in mm

Articulated levelling foot, pressed base Ø80 Ste Sta

PTA80
PTA80ss


Accepts loads up to 10.000N


- **Tilting foot**
- Tilt up to +/- 5° from vertical
- The base of the stainless steel version is available with either a glossy or sandblasted finish
- Materials:

Steel version:
Base: Galvanised sheet steel C40
Spindle: Galvanised steel (nut not supplied)
Sole: Vulcanised NBR rubber, hardness 80° Shore

Stainless steel version:
Base: Stainless steel sheet 304
Spindle: Stainless steel 304 (nut not supplied)
Sole: Vulcanised NBR rubber, hardness 80° Shore

Stainless steel version, sanded finish





Option

- Other shaft dimensions are available on request

DISCOUNTS

Qty	1+	15+	20+	25+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number bright	Part number sanded finish	ØD	ØF	B	A	A/F	G	H	Static load (N)	Stock* bright	Price each 1 to 14
Steel foot											
PTA80-12-100	-	80	M12	100	35	14	25	135	10000	✔	25,69 €
PTA80-12-150	-	80	M12	150	35	14	25	185	10000	-	28,59 €
PTA80-16-100	-	80	M16	100	35	16	25	135	10000	✔	28,39 €
PTA80-16-150	-	80	M16	150	35	16	25	185	10000	-	31,39 €
PTA80-20-100	-	80	M20	100	36	20	25	136	10000	-	29,81 €
PTA80-20-150	-	80	M20	150	36	20	25	186	10000	-	33,47 €
PTA80-20-200	-	80	M20	200	36	20	25	236	10000	✔	36,54 €
Stainless steel foot											
PTA80-12-100/SS	PTA80-12-100/SS/SB	80	M12	100	35	14	25	135	10000	✔	39,22 €
PTA80-12-150/SS	PTA80-12-150/SS/SB	80	M12	150	35	14	25	185	10000	✔	42,13 €
PTA80-16-100/SS	PTA80-16-100/SS/SB	80	M16	100	35	13	25	135	10000	-	42,13 €
PTA80-16-150/SS	PTA80-16-150/SS/SB	80	M16	150	35	13	25	185	10000	✔	45,07 €
PTA80-20-100/SS	PTA80-20-100/SS/SB	80	M20	100	38	17	25	138	10000	-	47,26 €
PTA80-20-150/SS	PTA80-20-150/SS/SB	80	M20	150	38	17	25	188	10000	✍	50,86 €
PTA80-20-200/SS	PTA80-20-200/SS/SB	80	M20	200	38	17	25	238	10000	✍	56,36 €

*Depending on availability - Dimensions in mm

Articulated fixable foot, pressed bolt-down base Ø80


Accepts loads up to 10.000N

PTAF80
PAMF80

- **Tilting foot**
- Tilt up to +/- 5° from vertical
- With non-slip sole
- Materials:

Steel version:
Base : Galvanised sheet steel C40
Spindle: Galvanised steel (nut not supplied)
Sole: Vulcanised NBR rubber, hardness 80° Shore

Stainless steel version:
Base: Stainless steel sheet 304
Spindle: Stainless steel 304 (nut not supplied)
Sole: Vulcanised NBR rubber, 80° Shore



Advantages

- Easy to secure due to large distance between shaft and mounting hole

Option

- Other shaft dimensions are available on request

DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	List	-5%	-10%	-15%	On request

Part number Bright	Part number Sanded finish	Thread ØD	Thread ØF	B	A	A/F	G	H	Static load(N)	Bright	Price each 1 to 5
Steel foot											
PTAF80-12-100	-	80	M12	100	35	14	25	135	10000	✔	30,77 €
PTAF80-12-150	-	80	M12	150	35	14	25	185	10000	✔	33,36 €
PTAF80-16-100	-	80	M16	100	35	16	25	135	10000	✔	33,00 €
PTAF80-16-150	-	80	M16	150	35	16	25	185	10000	✔	36,24 €
PTAF80-20-100	-	80	M20	100	36	20	25	136	10000	-	34,74 €
PTAF80-20-150	-	80	M20	150	36	20	25	186	10000	-	38,02 €
PTAF80-20-200	-	80	M20	200	36	20	25	236	10000	-	41,38 €
Stainless steel foot											
PAMF80-12-100	PAMF80-12-100/SB	80	M12	100	35	14	25	135	10000	✔	48,07 €
PAMF80-12-150	PAMF80-12-150/SB	80	M12	150	35	14	25	185	10000	✔	50,94 €
PAMF80-16-75	PAMF80-16-75/SB	80	M16	75	35	13	25	110	10000	✔	48,76 €
PAMF80-16-125	PAMF80-16-125/SB	80	M16	125	35	13	25	160	10000	✔	52,44 €
PAMF80-16-175	PAMF80-16-175/SB	80	M16	175	35	13	25	210	10000	✔	56,07 €
PAMF80-20-100	PAMF80-20-100/SB	80	M20	100	38	17	25	138	10000	-	56,07 €
PAMF80-20-150	PAMF80-20-150/SB	80	M20	150	38	17	25	188	10000	-	59,73 €
PAMF80-20-200	PAMF80-20-200/SB	80	M20	200	38	17	25	238	10000	-	65,18 €

*Depending on availability - Dimensions in mm

Articulated fixable foot, pressed bolt-down base Ø100 Ste Sta


PTAF100
PAMF100

Accepts loads up to 15.000N

- **Tilting foot**
- Tilt up to +/- 5° from vertical
- With non-slip sole
- Materials:

Steel version:
Base: Galvanised sheet steel C40
Spindle: Galvanised steel (nut not supplied)
Sole: Vulcanised NBR rubber, hardness 80° Shore

Stainless steel version:
Base: Stainless sheet steel 304
Spindle: Stainless steel plate 304 (nut not supplied)
Sole: Vulcanised NBR rubber, 80° Shore



Advantages

- Easy to install due to large distance between shaft and mounting hole

Option

- Other shaft dimensions are available on request

DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	List	-5%	-10%	-15%	On request

Part number Bright	Part number Sanded finish	ØD	Thread ØF	B	A	A/F	G	H	Static load (N)	Stock* Bright	Price each 1 to 5
Steel foot											
PTAF100-16-100	-	100	M16	100	38	16	28	137,5	15000	✔	38,65 €
PTAF100-16-150	-	100	M16	150	38	16	28	187,5	15000	✔	41,69 €
PTAF100-16-200	-	100	M16	200	38	16	28	237,5	15000	✔	42,87 €
PTAF100-20-100	-	100	M20	100	39	20	28	138,5	15000	-	40,18 €
PTAF100-20-150	-	100	M20	150	39	20	28	188,5	15000	✔	43,80 €
PTAF100-20-200	-	100	M20	200	39	20	28	238,5	15000	✔	47,46 €
PTAF100-24-100	-	100	M24	100	39	24	28	138,5	15000	✔	46,19 €
PTAF100-24-150	-	100	M24	150	39	24	28	188,5	15000	-	50,12 €
Stainless steel foot											
PAMF100-16-100	PAMF100-16-100/SB	100	M16	100	39,5	13	30	139,5	15000	✔	69,93 €
PAMF100-16-150	PAMF100-16-150/SB	100	M16	150	39,5	13	30	189,5	15000	✔	72,12 €
PAMF100-16-200	PAMF100-16-200/SB	100	M16	200	39,5	13	30	239,5	15000	-	77,20 €
PAMF100-20-100	PAMF100-20-100/SB	100	M20	100	43,0	17	30	143,0	15000	-	74,29 €
PAMF100-20-150	PAMF100-20-150/SB	100	M20	150	43,0	17	30	193,0	15000	-	78,72 €
PAMF100-20-200	PAMF100-20-200/SB	100	M20	200	43,0	17	30	243,0	15000	-	83,78 €

*Depending on availability - Dimensions in mm

Ste Sta Articulated levelling foot, pressed base Ø100

Accepts loads up to 15.000N

PTA100
PTA100ss


- **Tilting foot**
- tilt up to +/- 5° from vertical
- The base of the stainless steel version is available with either a glossy or sandblasted finish
- Materials:

Steel version:
Base: Galvanised sheet steel C40
Spindle: Galvanised steel (nut not supplied)
Sole: Vulcanised NBR rubber, hardness 80° Shore

Stainless steel version:
Base: Stainless steel sheet 304
Spindle: Stainless steel plate 304 (nut not supplied)
Sole: Vulcanised NBR rubber, hardness 80° Shore

Stainless steel version, sanded finish





Option

- Other shaft dimensions are available on request

DISCOUNTS

Qty	1+	15+	20+	25+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number bright	Part number sanded finish	ØD	ØF	B	A	A/F	G	H	Static load (N)	Stock* bright	Price each 1 to 14
Steel foot											
PTA100-16-100	-	100	M16	100	38,0	16	28	137,5	15000	✔	31,39 €
PTA100-16-150	-	100	M16	150	38,0	16	28	187,5	15000	✔	34,49 €
PTA100-16-200	-	100	M16	200	38,0	16	28	237,5	15000	-	35,62 €
PTA100-20-100	-	100	M20	100	39,0	20	28	138,5	15000	✔	32,90 €
PTA100-20-150	-	100	M20	150	39,0	20	28	188,5	15000	-	36,54 €
PTA100-20-200	-	100	M20	200	39,0	20	28	238,5	15000	-	40,18 €
PTA100-24-100	-	100	M24	100	39,0	24	28	138,5	15000	-	38,90 €
PTA100-24-150	-	100	M24	150	39,0	24	28	188,5	15000	-	42,67 €
Stainless steel foot											
PTA100-16-100/SS	PTA100-16-100/SS/SB	100	M16	100	39,5	13	30	139,5	15000	✔	61,08 €
PTA100-16-150/SS	PTA100-16-150/SS/SB	100	M16	150	39,5	13	30	189,5	15000	-	63,24 €
PTA100-16-200/SS	PTA100-16-200/SS/SB	100	M16	200	39,5	13	30	239,5	15000	-	68,36 €
PTA100-20-100/SS	PTA100-20-100/SS/SB	100	M20	100	43,0	17	30	143,0	15000	-	65,46 €
PTA100-20-150/SS	PTA100-20-150/SS/SB	100	M20	150	43,0	17	30	193,0	15000	-	69,78 €
PTA100-20-200/SS	PTA100-20-200/SS/SB	100	M20	200	43,0	17	30	243,0	15000	-	74,88 €
PTA100-24-100/SS	PTA100-24-100/SS/SB	100	M24	100	44,0	20	30	144,0	15000	-	70,52 €
PTA100-24-150/SS	PTA100-24-150/SS/SB	100	M24	150	44,0	20	30	194,0	15000	-	72,74 €

*Depending on availability - Dimensions in mm

Pressed steel articulated foot Ø150 Ste Sta


PTA150 PTA150ss

Accepts loads up to 40,000N

- **Levelling foot**
- Brilliant finish (sand-blasted finish for base of the stainless steel version)
- Materials:

Steel version:
Base: Chromed steel sheet C40
Rod: Chromed steel (nut not supplied)
Sole: Vulcanised rubber NBR hardness 80° Shore

Stainless steel version:
Base: 304 stainless steel, brilliant or sand-blasted finish
Rod: 304 stainless steel (nut not supplied)
Sole: Vulcanised rubber NBR hardness 80° Shore



Options

- Other rod sizes are available

DISCOUNTS

Qty	1+	15+	20+	25+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number bright	Part number sanded finish	ØD	ØF	B	A	A/F	G	H	Static load (N)	Price each 1 to 14
Steel foot										
PTA150-24-100	-	150	M24	100	44	24	35	144	40000	60,98 €
PTA150-24-150	-	150	M24	150	44	24	35	194	40000	64,37 €
PTA150-24-200	-	150	M24	200	44	24	35	244	40000	68,02 €
PTA150-24-250	-	150	M24	250	44	24	35	294	40000	71,44 €
PTA150-30-100	-	150	M30	100	44	30	35	145	40000	66,94 €
PTA150-30-150	-	150	M30	150	44	30	35	195	40000	69,04 €
PTA150-30-200	-	150	M30	200	44	30	35	245	40000	75,99 €
PTA150-30-250	-	150	M30	250	44	30	35	395	40000	85,59 €
Stainless steel foot										
PTA150-24-100/SS	PTA150-24-100/SS/SB	150	M24	100	49	20	35	149	40000	87,88 €
PTA150-24-150/SS	PTA150-24-150/SS/SB	150	M24	150	49	20	35	199	40000	92,71 €
PTA150-24-200/SS	PTA150-24-200/SS/SB	150	M24	200	49	20	35	249	40000	97,56 €
PTA150-24-250/SS	PTA150-24-250/SS/SB	150	M24	250	49	20	35	299	40000	102,39 €
PTA150-30-100/SS	PTA150-30-100/SS/SB	150	M30	100	50	26	35	150	40000	100,01 €
PTA150-30-150/SS	PTA150-30-150/SS/SB	150	M30	150	50	26	35	200	40000	107,08 €
PTA150-30-200/SS	PTA150-30-200/SS/SB	150	M30	200	50	26	35	250	40000	113,02 €
PTA150-30-250/SS	PTA150-30-250/SS/SB	150	M30	250	50	26	35	300	40000	118,93 €

All dimensions in mm

Sta Articulated foot with sheet metal base Ø50

Max load: 4000N
Rubber sole in EPDM, blue

PTA50SS/EB

- ***Articulated adjustable levelling feet***
- *Axial articulation +/- 10°*
- *With non-slip sole in EPDM Blue*
- *Stainless steel in shiny finish*
- *Materials:*
  Base: shiny 304 stainless steel sheet
  Thread: 304 stainless steel, supplied without nut
  Sole: EPDM blue




Options

- *Other thread dimensions on request*
- *316 grade Stainless steel on request*

Advantages

- *Hygienic special sole for easy cleaning.*
- *Food processing, Pharmaceutical and Chemical Environment*



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	Price	-5%	-10%	-15%	On request

Part number	ØD	ØF	B	A	A/F	G	H	Static load(N)	Price per unit 1 to 5
PTA50-10-75/SS/EB	50	M10	75	29	14	19	104	4,000	23,42 €
PTA50-10-125/SS/EB	50	M10	125	29	14	19	154	4,000	23,79 €
PTA50-12-75/SS/EB	50	M12	75	29	14	19	104	4,000	23,42 €
PTA50-12-125/SS/EB	50	M12	125	29	14	19	154	4,000	25,88 €
PTA50-16-75/SS/EB	50	M16	75	34	13	19	109	4,000	22,51 €
PTA50-16-100/SS/EB	50	M16	100	34	13	19	134	4,000	23,57 €
PTA50-16-150/SS/EB	50	M16	150	34	13	19	184	4,000	25,66 €

** Depending on availability - Dimensions in mm*

Sta Articulated foot with sheet metal base Ø80

Max load: 10,000N
Rubber sole in EPDM, blue

PTA80SS/EB

- ***Articulated adjustable levelling feet***
- *Axial articulation +/- 10°*
- *With non-slip sole in EPDM Blue*
- *Stainless steel in shiny finish*
- *Materials:*
  Base: shiny 304 stainless steel sheet
  Thread: 304 stainless steel, supplied without nut
  Sole: EPDM blue




Options

- *Other thread dimensions on request*
- *316 grade Stainless steel on request*

Advantages

- *Hygienic special sole for easy cleaning.*
- *Food processing, Pharmaceutical and Chemical Environment*



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	Price	-5%	-10%	-15%	On request

Part number	ØD	ØF	B	A	A/F	G	H	Static load(N)	Price per unit 1 to 5
PTA80-12-100/SS/EB	80	M12	100	35	14	25	135	10000	35,57 €
PTA80-12-150/SS/EB	80	M12	150	35	14	25	185	10000	38,15 €
PTA80-16-100/SS/EB	80	M16	100	35	13	25	135	10000	38,15 €
PTA80-16-150/SS/EB	80	M16	150	35	13	25	185	10000	40,63 €
PTA80-20-100/SS/EB	80	M20	100	38	17	25	138	10000	42,60 €
PTA80-20-150/SS/EB	80	M20	150	38	17	25	188	10000	45,72 €
PTA80-20-200/SS/EB	80	M20	200	38	17	25	238	10000	50,48 €

** Depending on availability - Dimensions in mm*

Articulated foot with sheet metal base Ø100

PTA100SS/EB

Max load: 15,000N
Rubber sole in EPDM, blue

- ***Articulated adjustable levelling feet***
- *Axial articulation +/- 10°*
- *With non-slip sole in EPDM Blue*
- *Stainless steel in shiny finish*
- *Materials:*
  Base: shiny 304 stainless steel sheet
  Thread: 304 stainless steel, supplied without nut
  Sole: EPDM blue




Options

- *Other thread dimensions on request*
- *316 grade Stainless steel on request*

Advantages

- *Hygienic special sole for easy cleaning.*
- *Food processing, Pharmaceutical and Chemical Environment*



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	Price	-5%	-10%	-15%	On request

Part number	ØD	ØF	B	A	A/F	G	H	Static load(N)	Price per unit 1 to 5
PTA100-16-100/SS/EB	100	M16	100	39.5	13	30	139.5	15000	54,84 €
PTA100-16-150/SS/EB	100	M16	150	39.5	13	30	189.5	15000	56,75 €
PTA100-16-200/SS/EB	100	M16	200	39.5	13	30	239.5	15000	61,21 €
PTA100-20-100/SS/EB	100	M20	100	43.0	17	30	143.0	15000	58,66 €
PTA100-20-150/SS/EB	100	M20	150	43.0	17	30	193.0	15000	62,42 €
PTA100-20-200/SS/EB	100	M20	200	43.0	17	30	243.0	15000	66,87 €
PTA100-24-100/SS/EB	100	M24	100	44.0	20	30	144.0	15000	63,08 €
PTA100-24-150/SS/EB	100	M24	150	44.0	20	30	194.0	15000	64,99 €


** Depending on availability - Dimensions in mm*

Sta Articulated foot with sheet metal base Ø80

Max load: 10,000N
Rubber sole in EPDM, blue

PAMF80EB

- **Articulated adjustable levelling feet**
- Axial articulation +/- 10°
- With non-slip sole in EPDM Blue
- Stainless steel in shiny finish
- Materials:
  Base: shiny 304 stainless steel sheet
  Thread: 304 stainless steel, supplied without nut
  Sole: EPDM blue




Options

- Other thread dimensions on request
- 316 grade Stainless steel on request

Advantages

- Hygienic special sole for easy cleaning
- Food processing, Pharmaceutical and Chemical Environment



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	Price	-5%	-10%	-15%	On request

Part number	ØD	ØF	B	A	A/F	G	H	Static load(N)	Price per unit 1 to 5
PAMF80-12-100/EB	80	M12	100	35	14	25	135	10000	39,71 €
PAMF80-12-150/EB	80	M12	150	35	14	25	185	10000	41,97 €
PAMF80-16-75/EB	80	M16	75	35	13	25	110	10000	40,25 €
PAMF80-16-125/EB	80	M16	125	35	13	25	160	10000	43,13 €
PAMF80-16-175/EB	80	M16	175	35	13	25	210	10000	45,97 €
PAMF80-20-100/EB	80	M20	100	38	17	25	138	10000	45,97 €
PAMF80-20-150/EB	80	M20	150	38	17	25	188	10000	48,81 €
PAMF80-20-200/EB	80	M20	200	38	17	25	238	10000	53,08 €

*Within the limits of available stock - Dimensions in mm

Articulated foot with sheet metal base Ø100

PAMF100EB

Max load: 15,000N
Rubber sole in EPDM, blue

- ***Articulated adjustable levelling feet***
- *Axial articulation +/- 10°*
- *With non-slip sole in EPDM Blue*
- *Stainless steel in shiny finish*
- *Materials:*
  Base: shiny 304 stainless steel sheet
  Thread: 304 stainless steel, supplied without nut
  Sole: EPDM blue


Options

- *Other thread dimensions on request*
- *316 grade Stainless steel on request*

Advantages

- *Hygienic special pad for easy cleaning.*
- *Food processing, Pharmaceutical and Chemical Environment*





DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	Price	-5%	-10%	-15%	On request

Part number	Threading ØD	ØF	B	A	A/F	G	H	Static load(N)	Price per unit 1 to 5
PAMF100-16-100/EB	100	M16	100	39.5	13	30	139.5	15000	57,67 €
PAMF100-16-150/EB	100	M16	150	39.5	13	30	189.5	15000	59,42 €
PAMF100-16-200/EB	100	M16	200	39.5	13	30	239.5	15000	63,43 €
PAMF100-20-100/EB	100	M20	100	43.0	17	30	143.0	15000	61,11 €
PAMF100-20-150/EB	100	M20	150	43.0	17	30	193.0	15000	64,59 €
PAMF100-20-200/EB	100	M20	200	43.0	17	30	243.0	15000	68,58 €

** Depending on availability - Dimensions in mm*


Articulated fixable foot, pressed bolt-down base Ø120 Sta

PAMF120 Accepts loads up to 30 000N

Tilting foot
- Tilt up to +/- 5° from vertical
- With non-slip sole
- Materials:
  Base: Stainless steel sheet 304
  Spindle: Stainless steel 304
  (nut not supplied)
  Sole: Vulcanised NBR rubber, 80° Shore

Advantages
- Easy to secure due to large distance between shaft and mounting hole

Options
- Other shaft dimensions are available on request



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	ØF	B	A	A/F	G	H	Static load (N)	Price each 1 to 5
PAMF120-16-100/SS	120	M16	100	47	13	32	147	30000	75,62 €
PAMF120-16-150/SS	120	M16	150	47	13	32	197	30000	77,73 €
PAMF120-16-200/SS	120	M16	200	47	13	32	247	30000	81,44 €
PAMF120-20-100/SS	120	M20	100	47	17	32	147	30000	78,04 €
PAMF120-20-150/SS	120	M20	150	47	17	32	197	30000	81,10 €
PAMF120-20-200/SS	120	M20	200	47	17	32	247	30000	85,04 €
PAMF120-20-250/SS	120	M20	250	47	17	32	297	30000	89,94 €
PAMF120-24-150/SS	120	M24	150	49	20	32	199	30000	89,94 €
PAMF120-24-200/SS	120	M24	200	49	20	32	249	30000	94,51 €
PAMF120-24-250/SS	120	M24	250	49	20	32	299	30000	101,91 €

Dimensions in mm