

Articulated foot with solid base foot Ø40 **Ste** **Sta**

PTA40 PTA40ss

Accepts loads up to 3000N

- **Articulated foot**
- Up to +/- 5° from vertical
- **Materials:**


Steel version:

Base: Galvanised sheet steel C40
Shaft: Galvanised steel (nut not supplied)
Sole: Vulcanised NBR rubber, hardness 80° Shore

Stainless steel version:

Base: Sheet stainless steel 304
Shaft: Stainless steel 304 (nut not supplied)
Sole: Vulcanised NBR rubber, hardness 80° Shore

Stainless steel version, sanded finish



Option

- Other shaft size available upon request

DISCOUNTS

Qty	1+	15+	20+	25+	40+
Disc.	List -5%	-10%	-15%	On request	

Part number		ØD	ØF	B	A	A/F	G	H	Static load (N)	Price each 1 to 14	
bright	sanded finish										
Steel foot											
PTA40-8-25	-	40	M8	25	26	6	15	51	3000	-	11,02 €
PTA40-8-50	-	40	M8	50	26	6	15	76	3000	-	11,44 €
PTA40-8-75	-	40	M8	75	26	6	15	101	3000	-	11,91 €
PTA40-10-25	-	40	M10	25	26	8	15	51	3000	-	11,44 €
PTA40-10-50	-	40	M10	50	26	8	15	76	3000	-	11,91 €
PTA40-10-75	-	40	M10	75	26	8	15	101	3000	-	12,33 €
PTA40-10-100	-	40	M10	100	26	8	15	126	3000	-	12,64 €
PTA40-10-125	-	40	M10	125	26	8	15	152	3000	-	12,80 €
Stainless steel foot											
PTA40-8-25/SS	PTA40-8-25/SS/SB	40	M8	25	26	6	15	51	3000	-	13,40 €
PTA40-8-50/SS	PTA40-8-50/SS/SB	40	M8	50	26	6	15	76	3000	-	13,81 €
PTA40-8-75/SS	PTA40-8-75/SS/SB	40	M8	75	26	6	15	101	3000	-	14,29 €
PTA40-10-25/SS	PTA40-10-25/SS/SB	40	M10	25	26	8	15	51	3000	-	14,59 €
PTA40-10-50/SS	PTA40-10-50/SS/SB	40	M10	50	26	8	15	76	3000	-	15,06 €
PTA40-10-75/SS	PTA40-10-75/SS/SB	40	M10	75	26	8	15	101	3000	-	15,51 €
PTA40-10-100/SS	PTA40-10-100/SS/SB	40	M10	100	26	8	15	126	3000	-	16,40 €
PTA40-10-125/SS	PTA40-10-125/SS/SB	40	M10	125	26	8	15	151	3000	-	17,05 €

All dimensions in mm

StaSte Articulated levelling foot, pressed base Ø50

Accepts loads up to 4.000N

PTA50
PTA50ss

- **Tilting foot**
- Tilt up to +/- 5° from vertical
- The base of the stainless steel version is available with either a glossy or sandblasted finish
- Materials:


Steel version:

Base: Galvanised sheet steel C40
Spindle: Galvanised steel (nut not supplied)
Sole: Vulcanised NBR rubber, hardness 80° Shore

Stainless steel version:

Base: Sheet stainless steel 304
Spindle: Stainless steel 304 (nut not supplied)
Sole: Vulcanised NBR rubber, hardness 80° Shore

Stainless steel version, sanded finish



Option

- Other shaft dimensions are available on request

DISCOUNTS

Qty	1+	15+	20+	25+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number		ØD	ØF	B	A	A/F	G	H	Static load (N)	Stock* bright	Price each 1 to 14
bright	sanded finish										
Steel foot											
PTA50-10-100	-	50	M10	100	29	14	19	129	4000	✓	18,07 €
PTA50-12-100	-	50	M12	100	29	14	19	129	4000	✓	18,07 €
PTA50-12-150	-	50	M12	150	29	14	19	179	4000	-	19,50 €
PTA50-16-75	-	50	M16	75	29	16	19	104	4000	✓	18,55 €
PTA50-16-100	-	50	M16	100	29	16	19	129	4000	-	19,82 €
PTA50-16-150	-	50	M16	150	29	16	19	179	4000	✓	22,47 €
Stainless steel foot											
PTA50-10-75/SS	PTA50-10-75/SS/SB	50	M10	75	29	14	19	104	4000	✓	19,59 €
PTA50-10-125/SS	PTA50-10-125/SS/SB	50	M10	125	29	14	19	154	4000	✓	22,29 €
PTA50-12-75/SS	PTA50-12-75/SS/SB	50	M12	75	29	14	19	104	4000	✓	19,59 €
PTA50-12-125/SS	PTA50-12-125/SS/SB	50	M12	125	29	14	19	154	4000	✓	22,29 €
PTA50-16-75/SS	PTA50-16-75/SS/SB	50	M16	75	34	13	19	109	4000	✓	22,88 €
PTA50-16-100/SS	PTA50-16-100/SS/SB	50	M16	100	34	13	19	134	4000	✓	23,78 €
PTA50-16-150/SS	PTA50-16-150/SS/SB	50	M16	150	34	13	19	184	4000	-	26,16 €

*Depending on availability - Dimensions in mm

Articulated levelling foot, pressed base Ø80 **Ste** **Sta**

PTA80

Accepts loads up to 10.000N

PTA80ss

- **Tilting foot**
- Tilt up to +/- 5° from vertical
- The base of the stainless steel version is available with either a glossy or sandblasted finish
- Materials:



Steel version:

Base: Galvanised sheet steel C40
 Spindle: Galvanised steel (nut not supplied)
 Sole: Vulcanised NBR rubber, hardness 80° Shore

Stainless steel version:

Base: Stainless steel sheet 304
 Spindle: Stainless steel 304 (nut not supplied)
 Sole: Vulcanised NBR rubber, hardness 80° Shore

Stainless steel version, sanded finish



Option

- Other shaft dimensions are available on request

DISCOUNTS

Qty	1+	15+	20+	25+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number	bright	sanded finish	ØD	ØF	B	A	A/F	G	H	Static load (N)	Stock* bright	Price each 1 to 14
Steel foot												
PTA80-12-100	-	-	80	M12	100	35	14	25	135	10000	✓	25,69 €
PTA80-12-150	-	-	80	M12	150	35	14	25	185	10000	-	28,59 €
PTA80-16-100	-	-	80	M16	100	35	16	25	135	10000	✓	28,39 €
PTA80-16-150	-	-	80	M16	150	35	16	25	185	10000	-	31,39 €
PTA80-20-100	-	-	80	M20	100	36	20	25	136	10000	-	29,81 €
PTA80-20-150	-	-	80	M20	150	36	20	25	186	10000	-	33,47 €
PTA80-20-200	-	-	80	M20	200	36	20	25	236	10000	✓	36,54 €
Stainless steel foot												
PTA80-12-100/SS	PTA80-12-100/SS/SB		80	M12	100	35	14	25	135	10000	✓	39,22 €
PTA80-12-150/SS	PTA80-12-150/SS/SB		80	M12	150	35	14	25	185	10000	✓	42,13 €
PTA80-16-100/SS	PTA80-16-100/SS/SB		80	M16	100	35	13	25	135	10000	-	42,13 €
PTA80-16-150/SS	PTA80-16-150/SS/SB		80	M16	150	35	13	25	185	10000	✓	45,07 €
PTA80-20-100/SS	PTA80-20-100/SS/SB		80	M20	100	38	17	25	138	10000	-	47,26 €
PTA80-20-150/SS	PTA80-20-150/SS/SB		80	M20	150	38	17	25	188	10000	↗	50,86 €
PTA80-20-200/SS	PTA80-20-200/SS/SB		80	M20	200	38	17	25	238	10000	↗	56,36 €

*Depending on availability - Dimensions in mm

Accepts loads up to 10.000N

PTAF80
PAMF80

- Tilting foot
- Tilt up to +/- 5° from vertical
- With non-slip sole
- Materials:

Steel version:


Base : Galvanised sheet steel C40
 Spindle: Galvanised steel (nut not supplied)
 Sole: Vulcanised NBR rubber, hardness 80° Shore
Stainless steel version:
 Base: Stainless steel sheet 304
 Spindle: Stainless steel 304 (nut not supplied)
 Sole: Vulcanised NBR rubber, 80° Shore

Advantages

- Easy to secure due to large distance between shaft and mounting hole

Option

- Other shaft dimensions are available on request

**DISCOUNTS**

Qty	1+	6+	10+	15+	20+
Disc.	List	-5%	-10%	-15%	On request

Part number	Thread	Bright							Static load(N)	Price each 1 to 5	
		Sanded finish	ØD	ØF	B	A	A/F	G			H
Steel foot											
PTAF80-12-100	-	80	M12	100	35	14	25	135	10000	✓	30,77 €
PTAF80-12-150	-	80	M12	150	35	14	25	185	10000	✓	33,36 €
PTAF80-16-100	-	80	M16	100	35	16	25	135	10000	✓	33,00 €
PTAF80-16-150	-	80	M16	150	35	16	25	185	10000	✓	36,24 €
PTAF80-20-100	-	80	M20	100	36	20	25	136	10000	-	34,74 €
PTAF80-20-150	-	80	M20	150	36	20	25	186	10000	-	38,02 €
PTAF80-20-200	-	80	M20	200	36	20	25	236	10000	-	41,38 €
Stainless steel foot											
PAMF80-12-100	PAMF80-12-100/SB	80	M12	100	35	14	25	135	10000	✓	48,07 €
PAMF80-12-150	PAMF80-12-150/SB	80	M12	150	35	14	25	185	10000	✓	50,94 €
PAMF80-16-75	PAMF80-16-75/SB	80	M16	75	35	13	25	110	10000	✓	48,76 €
PAMF80-16-125	PAMF80-16-125/SB	80	M16	125	35	13	25	160	10000	✓	52,44 €
PAMF80-16-175	PAMF80-16-175/SB	80	M16	175	35	13	25	210	10000	✓	56,07 €
PAMF80-20-100	PAMF80-20-100/SB	80	M20	100	38	17	25	138	10000	-	56,07 €
PAMF80-20-150	PAMF80-20-150/SB	80	M20	150	38	17	25	188	10000	-	59,73 €
PAMF80-20-200	PAMF80-20-200/SB	80	M20	200	38	17	25	238	10000	-	65,18 €

*Depending on availability - Dimensions in mm

Articulated fixable foot, pressed bolt-down base Ø100 **Ste** **Sta**

PTAF100 PAMF100

Accepts loads up to 15.000N

- Tilting foot
- Tilt up to +/- 5° from vertical
- With non-slip sole
- Materials:


Steel version:

Base: Galvanised sheet steel C40
Spindle: Galvanised steel (nut not supplied)
Sole: Vulcanised NBR rubber, hardness 80° Shore

Stainless steel version:


Base: Stainless sheet steel 304
Spindle: Stainless steel plate 304 (nut not supplied)
Sole: Vulcanised NBR rubber, 80° Shore

Stainless steel version, sanded finish



Large hole allows use of a rawlplug

Large spacing allows use of a hammer drill



Advantages

- Easy to install due to large distance between shaft and mounting hole

Option

- Other shaft dimensions are available on request

DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	List	-5%	-10%	-15%	On request

Part number	Bright	Sanded finish	Thread					Static load (N)	Stock* Bright	Price each 1 to 5		
			ØD	ØF	B	A	A/F				G	H
Steel foot												
PTAF100-16-100	-	-	100	M16	100	38	16	28	137,5	15000	✓	38,65 €
PTAF100-16-150	-	-	100	M16	150	38	16	28	187,5	15000	✓	41,69 €
PTAF100-16-200	-	-	100	M16	200	38	16	28	237,5	15000	✓	42,87 €
PTAF100-20-100	-	-	100	M20	100	39	20	28	138,5	15000	-	40,18 €
PTAF100-20-150	-	-	100	M20	150	39	20	28	188,5	15000	✓	43,80 €
PTAF100-20-200	-	-	100	M20	200	39	20	28	238,5	15000	✓	47,46 €
PTAF100-24-100	-	-	100	M24	100	39	24	28	138,5	15000	✓	46,19 €
PTAF100-24-150	-	-	100	M24	150	39	24	28	188,5	15000	-	50,12 €
Stainless steel foot												
PAMF100-16-100	PAMF100-16-100/SB	-	100	M16	100	39,5	13	30	139,5	15000	✓	69,93 €
PAMF100-16-150	PAMF100-16-150/SB	-	100	M16	150	39,5	13	30	189,5	15000	✓	72,12 €
PAMF100-16-200	PAMF100-16-200/SB	-	100	M16	200	39,5	13	30	239,5	15000	-	77,20 €
PAMF100-20-100	PAMF100-20-100/SB	-	100	M20	100	43,0	17	30	143,0	15000	-	74,29 €
PAMF100-20-150	PAMF100-20-150/SB	-	100	M20	150	43,0	17	30	193,0	15000	-	78,72 €
PAMF100-20-200	PAMF100-20-200/SB	-	100	M20	200	43,0	17	30	243,0	15000	-	83,78 €

*Depending on availability - Dimensions in mm

SteSta Articulated levelling foot, pressed base Ø100

Accepts loads up to 15.000N

PTA100
PTA100ss

- **Tilting foot**
- tilt up to +/- 5° from vertical
- The base of the stainless steel version is available with either a glossy or sandblasted finish
- Materials:

Steel version:

Base: Galvanised sheet steel C40

Spindle: Galvanised steel
(nut not supplied)

Sole: Vulcanised NBR
rubber, hardness 80°
Shore


Stainless steel version:

Base: Stainless steel
sheet 304

Spindle: Stainless steel
plate 304 (nut not
supplied)

Sole: Vulcanised NBR
rubber, hardness
80° Shore

Stainless
steel version,
sanded finish



Option

- Other shaft dimensions are available on request

DISCOUNTS

Qty	1+	15+	20+	25+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number		ØD	ØF	B	A	A/F	G	H	Static load (N)	Stock* bright	Price each 1 to 14
bright	sanded finish										
Steel foot											
PTA100-16-100	-	100	M16	100	38,0	16	28	137,5	15000	✓	31,39 €
PTA100-16-150	-	100	M16	150	38,0	16	28	187,5	15000	✓	34,49 €
PTA100-16-200	-	100	M16	200	38,0	16	28	237,5	15000	-	35,62 €
PTA100-20-100	-	100	M20	100	39,0	20	28	138,5	15000	✓	32,90 €
PTA100-20-150	-	100	M20	150	39,0	20	28	188,5	15000	-	36,54 €
PTA100-20-200	-	100	M20	200	39,0	20	28	238,5	15000	-	40,18 €
PTA100-24-100	-	100	M24	100	39,0	24	28	138,5	15000	-	38,90 €
PTA100-24-150	-	100	M24	150	39,0	24	28	188,5	15000	-	42,67 €
Stainless steel foot											
PTA100-16-100/SS	PTA100-16-100/SS/SB	100	M16	100	39,5	13	30	139,5	15000	✓	61,08 €
PTA100-16-150/SS	PTA100-16-150/SS/SB	100	M16	150	39,5	13	30	189,5	15000	-	63,24 €
PTA100-16-200/SS	PTA100-16-200/SS/SB	100	M16	200	39,5	13	30	239,5	15000	-	68,36 €
PTA100-20-100/SS	PTA100-20-100/SS/SB	100	M20	100	43,0	17	30	143,0	15000	-	65,46 €
PTA100-20-150/SS	PTA100-20-150/SS/SB	100	M20	150	43,0	17	30	193,0	15000	-	69,78 €
PTA100-20-200/SS	PTA100-20-200/SS/SB	100	M20	200	43,0	17	30	243,0	15000	-	74,88 €
PTA100-24-100/SS	PTA100-24-100/SS/SB	100	M24	100	44,0	20	30	144,0	15000	-	70,52 €
PTA100-24-150/SS	PTA100-24-150/SS/SB	100	M24	150	44,0	20	30	194,0	15000	-	72,74 €

*Depending on availability - Dimensions in mm

Pressed steel articulated foot Ø150 **SteSta**

PTA150 Accepts loads up to 40,000N PTA150ss

- **Levelling foot**
- Brilliant finish (Sand-blasted finish for base of the stainless steel version)
- **Materials:**

Steel version:

Base: Chromed steel sheet C40

Rod: Chromed steel (nut not supplied)

Sole: Vulcanised rubber NBR hardness

80° Shore


Stainless steel version:

Base: 304 stainless steel, brilliant or sand-blasted finish

Rod: 304 stainless steel (nut not supplied)

Sole: Vulcanised rubber NBR hardness 80° Shore

Sand-blasted stainless-steel version



Options

- Other rod sizes are available

DISCOUNTS

Qty	1+	15+	20+	25+	40+
Disc.	List	-5%	-10%	-15%	On request

Part number	Static load (N)	Price each						
bright	sanded finish	1 to 14						
ØD	ØF	B	A	A/F	G	H		
Steel foot								
PTA150-24-100	-	150 M24 100	44	24	35	144	40000	60,98 €
PTA150-24-150	-	150 M24 150	44	24	35	194	40000	64,37 €
PTA150-24-200	-	150 M24 200	44	24	35	244	40000	68,02 €
PTA150-24-250	-	150 M24 250	44	24	35	294	40000	71,44 €
PTA150-30-100	-	150 M30 100	44	30	35	145	40000	66,94 €
PTA150-30-150	-	150 M30 150	44	30	35	195	40000	69,04 €
PTA150-30-200	-	150 M30 200	44	30	35	245	40000	75,99 €
PTA150-30-250	-	150 M30 250	44	30	35	295	40000	85,59 €
Stainless steel foot								
PTA150-24-100/SS	PTA150-24-100/SS/SB	150 M24 100	49	20	35	149	40000	87,88 €
PTA150-24-150/SS	PTA150-24-150/SS/SB	150 M24 150	49	20	35	199	40000	92,71 €
PTA150-24-200/SS	PTA150-24-200/SS/SB	150 M24 200	49	20	35	249	40000	97,56 €
PTA150-24-250/SS	PTA150-24-250/SS/SB	150 M24 250	49	20	35	299	40000	102,39 €
PTA150-30-100/SS	PTA150-30-100/SS/SB	150 M30 100	50	26	35	150	40000	100,01 €
PTA150-30-150/SS	PTA150-30-150/SS/SB	150 M30 150	50	26	35	200	40000	107,08 €
PTA150-30-200/SS	PTA150-30-200/SS/SB	150 M30 200	50	26	35	250	40000	113,02 €
PTA150-30-250/SS	PTA150-30-250/SS/SB	150 M30 250	50	26	35	300	40000	118,93 €

All dimensions in mm

Articulated foot with sheet metal base Ø50

Max load: 4000N
Rubber sole in **EPDM, blue**

PTA50SS/EB


- Articulated adjustable levelling feet
- Axial articulation +/- 10°
- With non-slip sole in EPDM Blue
- Stainless steel in shiny finish
- Materials:
 - Base: shiny 304 stainless steel sheet
 - Thread: 304 stainless steel, supplied without nut
 - Sole: EPDM blue

Options

- Other thread dimensions on request
- 316 grade Stainless steel on request

Advantages

- Hygienic special sole for easy cleaning.
- Food processing, Pharmaceutical and Chemical Environment



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc. Price	-5%	-10%	-15%	On request	

Part number	ØD	ØF	B	A	A/F	G	H	Static load(N)	Price per unit 1 to 5
PTA50-10-75/SS/EB	50	M10	75	29	14	19	104	4,000	23,42 €
PTA50-10-125/SS/EB	50	M10	125	29	14	19	154	4,000	23,79 €
PTA50-12-75/SS/EB	50	M12	75	29	14	19	104	4,000	23,42 €
PTA50-12-125/SS/EB	50	M12	125	29	14	19	154	4,000	25,88 €
PTA50-16-75/SS/EB	50	M16	75	34	13	19	109	4,000	22,51 €
PTA50-16-100/SS/EB	50	M16	100	34	13	19	134	4,000	23,57 €
PTA50-16-150/SS/EB	50	M16	150	34	13	19	184	4,000	25,66 €

* Depending on availability - Dimensions in mm



Articulated foot with sheet metal base Ø80

Max load: 10,000N

PTA80SS/EB

Rubber sole in **EPDM, blue**

- **Articulated adjustable levelling feet**
- Axial articulation +/- 10°
- With non-slip sole in EPDM Blue
- Stainless steel in shiny finish
- **Materials:**
 - Base: shiny 304 stainless steel sheet
 - Thread: 304 stainless steel, supplied without nut
 - Sole: EPDM blue

Options


- Other thread dimensions on request
- 316 grade Stainless steel on request

Advantages

- Hygienic special sole for easy cleaning.
- Food processing, Pharmaceutical and Chemical Environment

Food industry

Sole in EPDM, blue



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	Price	-5%	-10%	-15%	On request

Part number	ØD	ØF	B	A	A/F	G	H	Static load(N)	Price per unit 1 to 5
PTA80-12-100/SS/EB	80	M12	100	35	14	25	135	10000	35,57 €
PTA80-12-150/SS/EB	80	M12	150	35	14	25	185	10000	38,15 €
PTA80-16-100/SS/EB	80	M16	100	35	13	25	135	10000	38,15 €
PTA80-16-150/SS/EB	80	M16	150	35	13	25	185	10000	40,63 €
PTA80-20-100/SS/EB	80	M20	100	38	17	25	138	10000	42,60 €
PTA80-20-150/SS/EB	80	M20	150	38	17	25	188	10000	45,72 €
PTA80-20-200/SS/EB	80	M20	200	38	17	25	238	10000	50,48 €

* Depending on availability - Dimensions in mm

Articulated foot with sheet metal base Ø100

PTA100SS/EB

Max load: 15,000N
Rubber sole in **EPDM, blue**

- **Articulated adjustable levelling feet**
- Axial articulation +/- 10°
- With non-slip sole in EPDM Blue
- Stainless steel in shiny finish
- **Materials:**
 - Base: shiny 304 stainless steel sheet
 - Thread: 304 stainless steel, supplied without nut
 - Sole: EPDM blue

Options


- Other thread dimensions on request
- 316 grade Stainless steel on request

Advantages

- Hygienic special sole for easy cleaning.
- Food processing, Pharmaceutical and Chemical Environment

Food industry

Sole in EPDM, blue



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	Price	-5%	-10%	-15%	On request

Part number	ØD	ØF	B	A	A/F	G	H	Static load(N)	Price per unit 1 to 5
PTA100-16-100/SS/EB	100	M16	100	39.5	13	30	139.5	15000	54,84 €
PTA100-16-150/SS/EB	100	M16	150	39.5	13	30	189.5	15000	56,75 €
PTA100-16-200/SS/EB	100	M16	200	39.5	13	30	239.5	15000	61,21 €
PTA100-20-100/SS/EB	100	M20	100	43.0	17	30	143.0	15000	58,66 €
PTA100-20-150/SS/EB	100	M20	150	43.0	17	30	193.0	15000	62,42 €
PTA100-20-200/SS/EB	100	M20	200	43.0	17	30	243.0	15000	66,87 €
PTA100-24-100/SS/EB	100	M24	100	44.0	20	30	144.0	15000	63,08 €
PTA100-24-150/SS/EB	100	M24	150	44.0	20	30	194.0	15000	64,99 €

* Depending on availability - Dimensions in mm



Articulated foot with sheet metal base Ø80

Max load: 10,000N

Rubber sole in **EPDM, blue**

PAMF80EB

- Articulated adjustable levelling feet
- Axial articulation +/- 10°
- With non-slip sole in EPDM Blue
- Stainless steel in shiny finish
- Materials:
 - Base: shiny 304 stainless steel sheet
 - Thread: 304 stainless steel, supplied without nut
 - Sole: EPDM blue

Options

- Other thread dimensions on request
- 316 grade Stainless steel on request

Advantages


- Hygienic special sole for easy cleaning
- Food processing, Pharmaceutical and Chemical Environment



Food industry

Hole for fixing bolt

Large spacing allows use of a hammer drill



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc. Price		-5%	-10%	-15%	On request

Part number	ØD	ØF	B	A	A/F	G	H	Static load(N)	Price per unit 1 to 5
PAMF80-12-100/EB	80	M12	100	35	14	25	135	10000	39,71 €
PAMF80-12-150/EB	80	M12	150	35	14	25	185	10000	41,97 €
PAMF80-16-75/EB	80	M16	75	35	13	25	110	10000	40,25 €
PAMF80-16-125/EB	80	M16	125	35	13	25	160	10000	43,13 €
PAMF80-16-175/EB	80	M16	175	35	13	25	210	10000	45,97 €
PAMF80-20-100/EB	80	M20	100	38	17	25	138	10000	45,97 €
PAMF80-20-150/EB	80	M20	150	38	17	25	188	10000	48,81 €
PAMF80-20-200/EB	80	M20	200	38	17	25	238	10000	53,08 €

*Within the limits of available stock - Dimensions in mm

Articulated foot with sheet metal base Ø100 Sta

PAMF100EB

Max load: 15,000N
Rubber sole in **EPDM, blue**



- Articulated adjustable levelling feet
- Axial articulation +/- 10°
- With non-slip sole in EPDM Blue
- Stainless steel in shiny finish
- Materials:
 - Base: shiny 304 stainless steel sheet
 - Thread: 304 stainless steel, supplied without nut
 - Sole: EPDM blue

Options

- Other thread dimensions on request
- 316 grade Stainless steel on request

Advantages

- Hygienic special pad for easy cleaning.
- Food processing, Pharmaceutical and Chemical Environment



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc. Price	-5%	-10%	-15%	On request	

Part number	Threading							Static load(N)	Price per unit 1 to 5
	ØD	ØF	B	A	A/F	G	H		
PAMF100-16-100/EB	100	M16	100	39.5	13	30	139.5	15000	57,67 €
PAMF100-16-150/EB	100	M16	150	39.5	13	30	189.5	15000	59,42 €
PAMF100-16-200/EB	100	M16	200	39.5	13	30	239.5	15000	63,43 €
PAMF100-20-100/EB	100	M20	100	43.0	17	30	143.0	15000	61,11 €
PAMF100-20-150/EB	100	M20	150	43.0	17	30	193.0	15000	64,59 €
PAMF100-20-200/EB	100	M20	200	43.0	17	30	243.0	15000	68,58 €

* Depending on availability - Dimensions in mm

Articulated fixable foot, pressed bolt-down base Ø120 **Sta**

PAMF120 Accepts loads up to 30 000N

Tilting foot


- Tilt up to +/- 5° from vertical
- With non-slip sole
- Materials:
 - Base: Stainless steel sheet 304
 - Spindle: Stainless steel 304 (nut not supplied)
 - Sole: Vulcanised NBR rubber, 80° Shore

Advantages

- Easy to secure due to large distance between shaft and mounting hole

Options

- Other shaft dimensions are available on request



DISCOUNTS

Qty	1+	6+	10+	15+	20+
Disc.	List	-5%	-10%	-15%	On request

Part number	ØD	ØF	B	A	A/F	G	H	Static load (N)	Price each 1 to 5
PAMF120-16-100/SS	120	M16	100	47	13	32	147	30000	75,62 €
PAMF120-16-150/SS	120	M16	150	47	13	32	197	30000	77,73 €
PAMF120-16-200/SS	120	M16	200	47	13	32	247	30000	81,44 €
PAMF120-20-100/SS	120	M20	100	47	17	32	147	30000	78,04 €
PAMF120-20-150/SS	120	M20	150	47	17	32	197	30000	81,10 €
PAMF120-20-200/SS	120	M20	200	47	17	32	247	30000	85,04 €
PAMF120-20-250/SS	120	M20	250	47	17	32	297	30000	89,94 €
PAMF120-24-150/SS	120	M24	150	49	20	32	199	30000	89,94 €
PAMF120-24-200/SS	120	M24	200	49	20	32	249	30000	94,51 €
PAMF120-24-250/SS	120	M24	250	49	20	32	299	30000	101,91 €

Dimensions in mm