

- Light coloured Polyamide wheel
- Smooth central bore
- Working temperature range: -30°C to +80°C

Advantages

- Shock and abrasion resistant
- Does not stain floors
- Does not mark floors
- Resists most chemical agents
- Low rolling resistance
- For solid and hard floors
- Ideal for use in wet and dirty environments (fish markets, butcher shops, canneries)



For smooth surfaces



ØD



B



C



ØA

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	C	ØA	Maximum load (kg)	Stock*	Price each 1 to 9
RPC60-31/ML	60	31	40	12	200	✓	2,50 €
RPC80-32/ML	80	32	40	12	250	✓	2,72 €
RPC100-32/ML	100	32	40	12	300	✓	3,77 €
RPC100-35/ML	100	35	48	15	350	-	11,29 €
RPC125-36/ML	125	36	50	15	350	-	6,88 €
RPC125-41/ML	125	41	59	20	400	-	13,27 €
RPC150-37/ML	150	37	49	15	400	-	9,96 €
RPC160-40/ML	160	40	58	20	500	-	27,31 €
RPC200-50/ML	200	50	58	20	600	-	29,65 €

*Depending on availability -Dimensions in mm

Polyamide castor with mounting plate Stock

RPCPL For heavy loads up to 600kg

- Industrial wheel suitable for loads up to 600kg
- Swivel system uses two ball races
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Smooth central bore
- Materials:
Top plate: pressed steel sheet, protected by bright zinc plating
Polyamide wheel **RPC (tome 5 p.51)**
- Working temperature range: - 30°C to + 80°C



Fixed



Swivel



Swivel with double brake

Advantages

- Light
- Will not mark or stain floor
- Low rolling resistance
- For solid, hard floors



ØD



B



H



L



M



ØT



ØK

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	L	M	ØT	ØK	Swivel interference	Max. load (kg)	Stock*	Price each 1 to 9
Fixed											
RPC60/PL/F	60	30	100	110x85	80x60	8	-	200	-		8,25 €
RPC80/PL/F	80	32	109	110x85	80x60	8	-	250	✓		8,06 €
RPC100/PL/F	100	32	126	110x85	80x60	8	-	300	✓		8,34 €
RPC125/PL/F	125	36	154	110x85	80x60	8	-	350	-		13,47 €
RPC150/PL/F	150	37	182	110x85	80x60	8	-	400	-		18,38 €
RPC160/PL/F	160	40	196	135x110	105x80	11	-	500	-		32,06 €
RPC200/PL/F	200	50	241	135x110	105x80	11	-	600	-		37,99 €
Swivel											
RPC60/PL/P	60	30	100	110x85	80x60	8	140	200	-		11,43 €
RPC80/PL/P	80	32	109	110x85	80x60	8	160	250	✓		9,48 €
RPC100/PL/P	100	32	126	110x85	80x60	8	184	300	✓		9,72 €
RPC125/PL/P	125	36	154	110x85	80x60	8	210	350	-		14,45 €
RPC150/PL/P	150	37	182	110x85	80x60	8	246	400	-		23,01 €
RPC160/PL/P	160	40	196	135x110	105x80	11	268	500	-		35,54 €
RPC200/PL/P	200	50	241	135x110	105x80	11	318	600	-		40,63 €
Swivel with double brake											
RPC80/PL/PDB	80	32	109	110x85	80x60	8	290	250	✓		12,49 €
RPC100/PL/PDB	100	32	126	110x85	80x60	8	290	300	✓		13,41 €
RPC125/PL/PDB	125	36	154	110x85	80x60	8	290	350	✓		18,60 €
RPC150/PL/PDB	150	37	182	110x85	80x60	8	290	400	-		27,97 €
RPC160/PL/PDB	160	40	196	135x110	105x80	11	268	500	-		39,76 €
RPC200/PL/PDB	200	50	241	135x110	105x80	11	318	600	-		45,49 €

*Depending on availability - Dimensions in mm

- Industrial wheel suitable for loads up to 600kg
- Swivel system uses two ball races
- Swivel castor with double locks:
simple to lock/unlock using foot operated pedal
- Smooth central bore
- Materials:
Top plate: pressed steel sheet, protected by bright zinc plating
Polyamide wheel **RPC (tome 5 p.51)**
- Working temperature range: - 30°C to + 80°C




Swivel



Swivel with double brake

Advantages

- Light
- Will not mark or stain floor
- Low rolling resistance
- For solid, hard floors



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Max load (kg)	Stock*	Price each 1 to 9
Swivel								
RPC60/TC/P	60	30	97	12	140	200	-	11,12 €
RPC80/TC/P	80	32	106	12	160	250	✓	12,04 €
RPC100/TC/P	100	32	124	12	184	300	✓	12,96 €
RPC125/TC/P	125	36	152	12	210	350	-	17,57 €
RPC150/TC/P	150	37	181	12	246	400	-	24,69 €
RPC160/TC/P	160	40	189	12,5	268	500	-	49,94 €
RPC200/TC/P	200	50	232	12,5	318	600	-	57,40 €
Swivel with double brake								
RPC80/TC/PDB	80	32	106	12	290	250	✓	17,79 €
RPC100/TC/PDB	100	32	124	12	290	300	✓	18,67 €
RPC125/TC/PDB	125	36	152	12	290	350	-	23,74 €
RPC150/TC/PDB	150	37	181	12	290	400	-	31,19 €
RPC160/TC/PDB	160	40	189	12,5	268	500	-	62,99 €
RPC200/TC/PDB	200	50	232	12,5	318	600	-	65,35 €

*Depending on availability - Dimensions in mm

RPCPLSS

For heavy loads up to 600kg

- Industrial wheel suitable for loads up to 600kg
- Swivel system uses two ball races
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Smooth central bore
- Materials:
 - Top plate: pressed stainless steel sheet
 - Polyamide wheel **RPC (tome 5 p.51)**
- Working temperature range: - 30°C to + 80°C



Fixed



Swivel

Stainless steel

Advantages

- Light
- Will not mark or stain floor
- Low rolling resistance
- For solid, hard floors
- Ideal for use in wet and dirty environments (fish markets, butcher shops, canneries)



ØD



B



H



L



M



ØT



ØK



Swivel with double brake

DISCOUNTS

Qty	1+	5+	15+
Disc.	List	-5%	On request

Part number	ØD	B	H	L	M	ØT	ØK	Swivel interference	Max load (kg)	Price each 1 to 4
Fixed										
RPC60/PL/F/SS	60	31	96	115x83	80x60	11x9	-	200	-	20,52 €
RPC80/PL/F/SS	80	32	105	115x83	80x60	11x9	-	250	✓	21,50 €
RPC100/PL/F/SS	100	32	124	115x83	80x60	11x9	-	300	✓	22,00 €
RPC125/PL/F/SS	125	36	152	115x83	80x60	11x9	-	350	-	29,35 €
RPC150/PL/F/SS	150	37	179	115x83	80x60	11x9	-	400	-	57,46 €
RPC160/PL/F/SS	160	40	197	135x105	105x80	11	-	600	-	79,45 €
RPC200/PL/F/SS	200	50	240	135x105	105x80	11	-	700	-	84,60 €
Swivel										
RPC60/PL/P/SS	60	31	96	115x83	80x60	11x9	155	200	-	30,61 €
RPC80/PL/P/SS	80	32	105	115x83	80x60	11x9	173	250	✓	30,54 €
RPC100/PL/P/SS	100	32	124	115x83	80x60	11x9	193	300	✓	32,77 €
RPC125/PL/P/SS	125	36	152	115x83	80x60	11x9	221	350	-	38,23 €
RPC150/PL/P/SS	150	37	179	115x83	80x60	11x9	257	400	-	77,85 €
RPC160/PL/P/SS	160	40	197	135x105	105x80	11	268	600	-	89,60 €
RPC200/PL/P/SS	200	50	240	135x105	105x80	11	318	700	-	96,15 €
Swivel with double brake										
RPC80/PL/PDB/SS	80	32	105	115x83	80x60	11x9	293	250	✓	39,86 €
RPC100/PL/PDB/SS	100	32	124	115x83	80x60	11x9	293	300	✓	42,01 €
RPC125/PL/PDB/SS	125	36	152	115x83	80x60	11x9	293	350	-	49,28 €
RPC150/PL/PDB/SS	150	37	179	115x83	80x60	11x9	293	400	-	100,19 €
RPC160/PL/PDB/SS	160	40	197	135x105	105x80	11	268	600	-	108,90 €
RPC200/PL/PDB/SS	200	50	240	135x105	105x80	11	318	700	-	121,62 €

*Depending on availability - Dimensions in mm

Polyamide castor with central hole, **stainless steel**

RPC TCSS

For heavy loads up to 600kg

- **Industrial wheel suitable for loads up to 600kg**
- Swivel system uses two ball races
- Swivel castor with double locks:
simple to lock/unlock using foot operated pedal
- Smooth central bore
- Materials:
Top plate: pressed stainless steel sheet
Polyamide wheel **RPC (tome 5 p.51)**
- Working temperature range: - 30°C to + 80°C



Swivel




Swivel with double brake

Advantages

- Light
- Will not mark or stain floor
- Low rolling resistance
- For solid, hard floors
- Ideal for use in wet and dirty environments
(fish markets, butcher shops, canneries)

Stainless steel



DISCOUNTS

Qty	1+	5+	15+
Disc. List	-5%	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Max load (kg)	Price each 1 to 4
Swivel							
RPC60/TC/P/SS	60	31	96	12	155	200	29,15 €
RPC80/TC/P/SS	80	32	109	12	173	250	30,54 €
RPC100/TC/P/SS	100	32	124	12	193	300	31,21 €
RPC125/TC/P/SS	125	36	152	12	221	350	38,23 €
RPC150/TC/P/SS	150	37	179	12	257	400	77,85 €
RPC160/TC/P/SS	160	40	197	16	268	600	88,20 €
RPC200/TC/P/SS	200	50	240	16	318	700	94,03 €
Swivel with double brake							
RPC80/TC/PDB/SS	80	32	109	12	173	250	39,86 €
RPC100/TC/PDB/SS	100	32	124	12	193	300	42,01 €
RPC125/TC/PDB/SS	125	36	152	12	221	350	49,28 €
RPC150/TC/PDB/SS	150	37	179	12	257	400	100,19 €
RPC160/TC/PDB/SS	160	40	197	16	268	600	107,58 €
RPC200/TC/PDB/SS	200	50	240	16	318	700	120,27 €

Dimensions in mm

Grey rubber wheel

Stock

RBG

For medium loads up to 120kg

- **Light industrial wheel with a semi-elastic solid rubber tyre**

- **Material:**

85° Shore vulcanised grey rubber tyre

Polypropylene core

- **Smooth central bore**

- **Working temperature range - 20°C to + 60°C**

Advantages

- Soft and silent

- Absorbs shock and vibration

- Will not damage floors



Noise absorbing



Wheel and castor



ØD



B



C



ØA

DISCOUNTS

Qty	1+	10+	30+
Disc. List	-5%	On request	

Part number	ØD	B	C	ØA	Maximum load (kg)	Stock*	Price each 1 to 9
RBG50-22/ML	50	22	28	8	40	✓	1,79 €
RBG60-24/ML	60	24	28	8	50	-	2,29 €
RBG80-23/ML	80	23	28	8	65	✓	3,61 €
RBG100-26/ML	100	26	28	8	75	✓	4,28 €
RBG100-32/ML	100	32	34	10	100	-	5,43 €
RBG125-32/ML	125	32	34	10	120	-	6,71 €

*Depending on availability - Dimensions in mm

- **Light industrial swivel castor with central hole**
- Swivel system uses two ball races
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Materials:

Top plate: pressed steel sheet, protected by bright zinc plating

Grey vulcanized rubber wheel 85°Shore

RBG (tome 5 p.56)

Smooth central bore

- Working temperature range: - 20°C to + 60°C

Advantages

- Soft, silent wheel
- Absorbs shock and vibration
- Will not damage floors




Fixed



Swivel



Swivel with double brake



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	L	M	ØT	Swivel interference ØK	Max load (kg)	Stock*	Price each 1 to 9
Fixed										
RBG50/PL/F	50	22	76	52x67	36x50	6	-	45	✓	3,72 €
RBG60/PL/F	60	24	85	52x67	36x50	6	-	55	✓	3,99 €
RBG80/PL/F	80	23	106	52x67	36x50	6	-	65	✓	5,21 €
RBG100/PL/F	100	26	122	52x67	36x50	6	-	75	✓	7,00 €
RBG125/PL/F	125	32	157	68x95	44x73	8	-	110	✓	13,69 €
Swivel										
RBG50/PL/P	50	22	76	48x64	36x50	6	98	45	✓	4,96 €
RBG60/PL/P	60	24	85	48x64	36x50	6	110	55	✓	5,87 €
RBG80/PL/P	80	23	106	48x64	36x50	6	138	65	✓	7,52 €
RBG100/PL/P	100	26	123	48x64	36x50	6	166	75	✓	9,03 €
RBG125/PL/P	125	32	161	70x90	50x70	8	216	110	✓	17,33 €
Swivel with double lock										
RBG50/PL/PDB	50	22	76	48x64	36x50	6	172	45	✓	6,90 €
RBG60/PL/PDB	60	24	85	48x64	36x50	6	172	55	✓	7,35 €
RBG80/PL/PDB	80	23	106	48x64	36x50	6	188	65	✓	9,23 €
RBG100/PL/PDB	100	26	123	48x64	36x50	6	188	75	✓	10,78 €
RBG125/PL/PDB	125	32	161	70x90	50x70	8	220	110	✓	19,25 €

* Depending on availability - Dimensions in mm

Castor with central hole

Stock

RBGTC For medium loads up to 110kg

- **Light industrial swivel castor with central hole**
- Swivel system uses two ball races
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Materials:

Top plate: pressed steel sheet, protected by bright zinc plating

Grey vulcanized rubber wheel 85°Shore

RBG (tome 5 p.56)

Smooth central bore

- Working temperature range: - 20°C to + 60°C

Advantages

- Soft, silent wheel
- Absorbs shock and vibration
- Will not damage floors



Swivel



Swivel with double brake



ØD




B



H



ØE



ØK

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Max load (kg)	Stock*	Price each 1 to 9
Swivel								
RBG50/TC/P	50	22	76	10	98	45	✓	4,67 €
RBG60/TC/P	60	24	85	10	110	55	✓	5,29 €
RBG80/TC/P	80	23	105	10	138	65	✓	6,80 €
RBG100/TC/P	100	26	121	10	166	75	✓	8,30 €
RBG125/TC/P	125	32	158	13	216	110	✓	12,73 €
Swivel with double lock								
RBG50/TC/PDB	50	22	76	10	172	45	✓	6,90 €
RBG60/TC/PDB	60	24	85	10	172	55	✓	7,14 €
RBG80/TC/PDB	80	23	105	10	188	65	✓	8,56 €
RBG100/TC/PDB	100	26	121	10	188	75	✓	12,15 €
RBG125/TC/PDB	125	32	158	13	220	110	✓	17,81 €

*Depending on availability -Dimensions in mm

- Industrial castor with a semi-elastic solid rubber tyre
- Material:
 - 85° Shore vulcanised black rubber tyre
 - Polypropylene core
- Smooth central bore
- Working temperature range: - 20°C to + 60°C

Advantages

- Soft and silent
- Absorbs shock and vibration
- Will not damage floors



Noise absorbing



ØD



B



C



ØA

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	C	ØA	Maximum load (kg)	Stock*	Price each 1 to 9
RBN80-34/ML	80	34	40	12	75	✓	3,56 €
RBN100-35/ML	100	35	39	12	100	✓	4,20 €
RBN125-38/ML	125	38	45	15	125	✓	6,61 €
RBN150-40/ML	150	40	45	15	150	-	9,36 €
RBN160-38/ML	160	38	60	20	150	-	9,76 €
RBN200-47/ML	200	47	60	20	215	-	12,78 €

*Depending on availability -Dimensions in mm

Rubber castor with mounting plate Stock

RBNPL

For heavy loads up to 215kg

- Industrial wheel suitable for loads up to 215kg

- Swivel system uses two sets of ball bearings

- Swivel castor with double locks: simple to lock/unlock using foot operated pedal

- Materials:

Baseplate: pressed steel sheet, protected by bright zinc plating

Black vulcanized rubber wheel,

85° Shore

RBN (tome 5 p.65)

- Smooth central bore

- Working temperature range: - 20°C to + 60°C



Fixed



Swivel



Swivel with double brake

Advantages

- Soft, silent wheel

- Absorbs shock and vibration

- Will not damage floors



ØD



B



H



L



M



ØT



ØK

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	L	M	ØT	ØK	Swivel interference	Max. load (kg)	Price each 1 to 9
Fixed										
RBN80/PL/F	80	30	109	110x85	80x60	8	-	75	-	8,53 €
RBN100/PL/F	100	35	126	110x85	80x60	8	-	100	-	9,71 €
RBN125/PL/F	125	38	153	110x85	80x60	8	-	125	-	13,54 €
RBN150/PL/F	150	40	180	110x85	80x60	8	-	150	-	17,36 €
RBN160/PL/F	160	38	180	135x110	105x80	11	-	150	✓	23,81 €
RBN200/PL/F	200	47	241	135x110	105x80	11	-	215	-	31,27 €
Swivel										
RBN80/PL/P	80	30	109	110x85	80x60	8	158	75	✓	11,37 €
RBN100/PL/P	100	35	126	110x85	80x60	8	182	100	✓	12,55 €
RBN125/PL/P	125	38	153	110x85	80x60	8	210	125	-	15,82 €
RBN150/PL/P	150	40	180	110x85	80x60	8	242	150	✓	20,23 €
RBN160/PL/P	160	38	180	135x110	105x80	11	267	150	-	30,62 €
RBN200/PL/P	200	47	241	135x110	105x80	11	320	215	-	37,42 €
Swivel with double lock										
RBN80/PL/PDB	80	30	109	110x85	80x60	8	290	75	✓	16,98 €
RBN100/PL/PDB	100	35	126	110x85	80x60	8	290	100	-	18,17 €
RBN125/PL/PDB	125	38	153	110x85	80x60	8	290	125	✓	22,60 €
RBN150/PL/PDB	150	40	180	110x85	80x60	8	290	150	-	26,41 €
RBN160/PL/PDB	160	38	180	135x110	105x80	11	267	150	-	39,07 €
RBN200/PL/PDB	200	47	241	135x110	105x80	11	320	215	-	46,80 €

*Depending on availability - Dimensions in mm

Rubber castor with central hole

For heavy loads up to 215kg

RBNTC

- Industrial wheel suitable for loads up to 215kg
- Swivel system uses two ball races
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Materials:
 - Baseplate: pressed steel sheet, protected by bright zinc plating
 - Black vulcanized rubber wheel 85°Shore
 - RBN (tome 5 p.65)**
- Smooth central bore
- Working temperature range: - 20°C to + 60°C




Swivel



Swivel with double brake

Advantages

- Soft and silent
- Absorbs shock and vibration
- Will not damage floors



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Maximum load (kg)	Price each 1 to 9
Swivel							
RBN80/TC/P	80	30	105	12	158	75	11,29 €
RBN100/TC/P	100	35	125	12	182	100	12,45 €
RBN125/TC/P	125	38	152	12	210	125	16,17 €
RBN150/TC/P	150	40	179	12	242	150	20,87 €
RBN160/TC/P	160	38	188	12,5	267	150	29,51 €
RBN200/TC/P	200	47	232	12,5	320	215	35,90 €
Swivel with double lock							
RBN80/TC/PDB	80	30	105	12	290	75	17,31 €
RBN100/TC/PDB	100	35	125	12	290	100	18,27 €
RBN125/TC/PDB	125	38	152	12	290	125	22,35 €
RBN150/TC/PDB	150	40	179	12	290	150	28,29 €
RBN160/TC/PDB	160	38	188	12,5	267	150	44,23 €
RBN200/TC/PDB	200	47	232	12,5	320	215	51,19 €

Dimensions in mm

Free running wheel

Stock

RUR

For loads up to 275kg

- Light industrial wheel for loads up to 275kg
- Ball bearing hub
- Materials:
 - Polyurethane covered wheel 85 Shore
 - Aluminium core
- Working temperature range: -30 to +80°C

For rough floors



Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



ØD



B



C



ØA

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	A	F	Max load (kg)	Stock*	Price each 1 to 9
RUR80	80	40	41	12	175	✓	20,58 €
RUR100	100	40	41	12	220	-	23,30 €
RUR125	125	38	50	15	250	-	26,62 €
RUR150	150	40	50	20	275	-	37,75 €

*Depending on availability -Dimensions in mm

Free running wheel with mounting plate

For loads up to 275kg

RURP

- Light industrial castor for loads up to 275kg
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Hub with ball bearing
- Materials:
 - Top bracket/plate: Plated steel sheet
 - Polyurethane covered wheel 85 Shore
 - Aluminium core, (see RUR tome 5 p.62)
- Working temperature range: -30 to +80°C



Fixed



Swivel

Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



ØD



B



H



L



M



ØT



ØK

For rough floors



Swivel with double brake

DISCOUNTS

Qty	1+	10+	30+
Disc. List	-5%		On request

Part number	ØD	B	H	L	M	ØT	Swivel interference ØK	Max load (kg)	Price each 1 to 9
Fixed									
RURP80/F	80	40	110	110x85	80x60	8	-	175	31,10 €
RURP100/F	100	40	127	110x85	80x60	8	-	220	34,16 €
RURP125/F	125	38	155	110x85	80x60	8	-	250	38,38 €
RURP150/F	150	40	181	110x85	80x60	8	-	275	49,59 €
Swivel									
RURP80/P	80	40	110	110x85	80x60	8	162	175	35,76 €
RURP100/P	100	40	127	110x85	80x60	8	184	220	39,07 €
RURP125/P	125	38	155	110x85	80x60	8	216	250	43,74 €
RURP150/P	150	40	181	110x85	80x60	8	244	275	54,75 €
Swivel with double brake									
RURP80/PDB	80	40	110	110x85	80x60	8	290	175	27,46 €
RURP100/PDB	100	40	127	110x85	80x60	8	290	220	30,33 €
RURP125/PDB	125	38	155	110x85	80x60	8	290	250	35,01 €
RURP150/PDB	150	40	181	110x85	80x60	8	290	275	48,92 €

Dimensions in mm

Free running wheel with central hole

RURT

For loads up to 275kg

- Light industrial castor for loads up to 275kg
- Swivel castor with double locks: simple to lock/unlock using foot operated pedal
- Hub with ball bearing
- Materials:
 - Top bracket/plate: Plated steel sheet
 - Polyurethane covered wheel, 85 Shore
 - Aluminium core (see RUR tome 5 p.62)
- Working temperature range: -30 to +80°C

For rough floors



Swivel



Swivel with double brake

Advantages

- Smooth and quiet running
- Resists wear
- Very strong
- Recommended for its exceptional resistance and its long-term service
- Low risk of flat spots developing if the wheel is not used

Applications

- Rough floors
- Can be used where metal chips, solvents, oil or grease is present



ØD



B



H



ØE



ØK

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Max load (kg)	Price each 1 to 9
Swivel							
RURT80/P	80	40	106	12	162	175	30,18 €
RURT100/P	100	40	126	12	184	220	32,89 €
RURT125/P	125	38	153	12	216	250	37,38 €
RURT150/P	150	40	180	12	244	275	37,38 €
Swivel with double brake							
RURT80/PDB	80	40	106	12	290	175	36,10 €
RURT100/PDB	100	40	126	12	290	220	39,15 €
RURT125/PDB	125	38	153	12	290	250	43,58 €
RURT150/PDB	150	40	180	12	290	275	58,08 €

Dimensions in mm



High temperature wheel


Load up to 200kg

RHT


- Phenolic resin castor wheel
- Slide bearings
- Working temp.: -30°C to +280°C

Advantages


- Large storage capacity
- Resists high temperatures




ØD



B



C



ØA

DISCOUNTS

Qty	1+	5+	15+
Disc. Price		-5%	On request

Part number	ØD	B	C	ØA	Load capacity (kg)	Price per unit
						1 to 4
RHT80-35/ML	80	35	40	12	125	19,39 €
RHT100-35/ML	100	35	40	12	150	19,63 €
RHT125-40/ML	125	40	48	15	200	71,40 €

Dimensions in mm

High Temperature Castors with plate

RHT_{PLSS}

Load up to 200kg

- **High temperature industrial castor**
- Swivel system on 2 crowns of balls
- Double-locking swivel castor:
use the foot pedal to lock and unlock.
- Slide bearings
- Materials:
304 stainless steel sheet
Polyamide wheel **RHT**
(**tome 5 p.65**)
- Working temp.: -30°C to +280°C



Fixed



Swivel



Swivel with double broke

Advantages

- Large storage capacity
- Resists high temperatures



ØD



B



H



L



M



ØT



ØK

DISCOUNTS

Qty	1+	5+	15+
Disc. Price	-	-5%	On request

Part number	ØD	B	H	L	M	ØT	Swivel interference ØK	Load maximum (kg)	Price per unit 1 to 4
Fixed									
RHT80/PL/F/SS	80	35	105	115x83	80x60	11x9	-	125	37,11 €
RHT100/PL/F/SS	100	35	126	115x83	80x60	11x9	-	150	37,82 €
RHT125/PL/F/SS	125	40	153	115x83	80x60	11x9	-	200	86,29 €
Swivel									
RHT80/PL/P/SS	80	35	105	115x83	80x60	11x9	173	125	46,27 €
RHT100/PL/P/SS	100	35	126	115x83	80x60	11x9	193	150	47,58 €
RHT125/PL/P/SS	125	40	153	115x83	80x60	11x9	221	200	96,78 €
Double locking swivel									
RHT80/PL/PDB/SS	80	35	105	115x83	80x60	11x9	293	125	55,98 €
RHT100/PL/PDB/SS	100	35	126	115x83	80x60	11x9	293	150	57,30 €
RHT125/PL/PDB/SS	125	40	153	115x83	80x60	11x9	293	200	106,49 €

Dimensions in mm



High Temperature Castor with central hole

Load up to 200kg

RHTTCSS

- High temperature industrial castor
- Swivel system on 2 crowns of balls
- Double-locking swivel castor:
use the foot pedal to lock and unlock.
- Slide bearings
- Materials:
304 stainless steel sheet
Polyamide wheel (see RHT (tome 5 p.65)
Working temp. range: -30°C to +280°C

Advantages

- Large storage capacity
- Resists high temperatures



Swivel



Double locking swivel



ØD



B



H



ØE



ØK

DISCOUNTS

Qty	1+	5+	15+
Disc. Price	-5%	-5%	On request

Part number	ØD	B	H	ØE	Swivel interference ØK	Load maximum (kg)	Price per unit 1 to 4
Swivel							
RHT80/TC/P/SS	80	35	105	12	173	125	46,27 €
RHT100/TC/P/SS	100	35	126	12	193	150	47,58 €
RHT125/TC/P/SS	125	40	153	12	221	200	96,78 €
Double locking swivel							
RHT80/PL/P/SS	80	35	105	12	173	125	55,99 €
RHT100/PL/P/SS	100	35	126	12	193	150	57,30 €
RHT125/PL/P/SS	125	40	153	12	221	200	106,49 €

Dimensions in mm

Stem support for caster

New

TSRTC For swivel caster with central hole

- Threaded stem for swivel castor with central hole

- Material:

Stem: Stainless steel 304

Washer: Stainless steel 304


Mounting

- Pass the $\varnothing F$ thread through the center hole of the castor plate and secure with a washer and a M12 lock nut (not supplied)
- If necessary, the length A can be shortened by yourself.
- The protection of the caster can be improved with the stainless steel protective washer **TSR-ROND**


Accessories

- Swivel castor with central hole **RPC/TC** Tome 5 (p. 53), **RBN/TC** 5 (p. 61), **RHT/TC** 5 (p. 67) et **RURT** 5 (p. 64)

Example of assembly with protective washer



TSR-ROND



DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØD	ØF	A	B	H	A/F	ØD1	Price each 1 to 9
Threaded stem								
TSR16-150/TC/SS	M16x2	M12x1,75	37	150	171	13	-	18,69 €
TSR16-200/TC/SS	M16x2	M12x1,75	37	200	221	13	-	22,21 €
TSR20-150/TC/SS	M20x2,5	M12x1,75	37	150	172	17	-	24,74 €
TSR20-200/TC/SS	M20x2,5	M12x1,75	37	200	222	17	-	30,30 €
TSR24-150/TC/SS	M24x3	M12x1,75	37	150	172	20	-	32,31 €
TSR24-200/TC/SS	M24x3	M12x1,75	37	200	222	20	-	39,89 €
Protective washer								
TSR-ROND12-60/SS	-	-	-	-	-	-	60	14,84 €
TSR-ROND12-80/SS	-	-	-	-	-	-	80	19,79 €

Dimensions in mm

Retractable castor for aluminum section

Load up to 200kg

RESC



- Retractable castor with foot, allowing easy transition from a rolling position to a fixed position.
- Materials:
 - Black PU tread
 - Wheel centre PA grey sim. RAL7001
 - Die-cast aluminium base plate
 - Steel wheel support

Advantages

- Allows the wheel to be shifted effortlessly into a fixed position thanks to the lever arm.
- Standing position more stable than a caster with brake.
- Prevents deformation of the tread under prolonged load.
- Can be mounted with the aluminium section in several different combinations.

Accessories

- Compatible with sections that have a width of 45mm PRF4545 and 90mm PRF4590 (tome 5 p.299)
- Compatible with section widths measuring 40mm, 80mm and 90mm
- CHC8-40/SS/B screw (tome 1 p.559)
- PRF-ECL-M8 nut (tome 5 p.315)



Application examples

DISCOUNTS

Qty	1+	10+	30+
Disc.	Price	-5%	On request

Part number	ØD	E	H	L1	L2	Max load (N)	Weight (kg)	Price per unit 1 to 9
RESC80-125	80	25.3	125	117	153	1500	1.64	192.56 €
RESC100-145	100	25.3	145	117	153	2000	1.94	195.13 €

Dimensions in mm

Locking castor with central hole



RIM

For loads up to 1000kg



- A combination of a swivel castor and an adjustable locking support
- Used to easily support and moving machines or other heavy equipment and then positioning them in a very stable manner.
- Installation starts by lowering the locking support using a nut.
- With the wheel no longer resting on the ground, the supported unit can be levelled despite any irregularities in the floor.
- Operating temperature range: -30 to +80°C

Materials

- Polyamide central control cross nut
- Anti-skid rubber mount allowing absorption of vibration and noise
- Body: Moulded cast aluminium body, hammered ivory paint finish
- Swivel system provided by 2 ball rings
- Mounting plate has a threaded central hole, threaded rod and nut supplied.
- Wheel: Black polyamide Shore D 70



Adjusting nut



DISCOUNTS

Qty	1+	5+	14+
Disc.	List	-5%	On request

Part number	ØA	B	H1	H2	ØT	Swivel interference ØK	Load (kg)	Price each 1 to 4
RIM42-60/TCE	42	20	71	81	M8	84	60	43,46 €
RIM50-280/TCE	50	25	82	92	M12	101	280	69,03 €
RIM63-550/TCE	63	28	103	118	M12	125	550	93,81 €
RIM75-800/TCE	75	30	120	132	M16	142	800	126,19 €
RIM75-1000/TCE	75	30	120	132	M16	142	1000	123,65 €

Dimensions in mm

Locking castor with mounting plate

For loads up to 1000kg

RIM



- A combination of a swivel castor and an adjustable locking support
- Used to easily support and moving machines or other heavy equipment and then positioning them in a very stable manner.
- Installation starts by lowering the locking support using a nut.
- With the wheel no longer resting on the ground, the supported unit can be levelled despite any irregularities in the floor.
- Operating temperature range: -30 to +80°C



Adjusting nut

Materials

- Polyamide central control cross nut
- Anti-skid rubber mount allowing absorption of vibration and noise
- Body: Moulded cast aluminium body, hammered ivory paint finish
- Swivel system provided by 2 ball rings
- Mounting plate square
- Wheel: Black polyamide Shore D 70



DISCOUNTS

Qty	1+	5+	14+
Disc.	List	-5%	On request

Part number	ØA	B	H1	H2	L	M	ØT	Swivel interference ØK	Load (kg)	Price each 1 to 4
RIM42-60/PLE	42	20	71	81	55x55	42x42	6,5	84	60	43,46 €
RIM50-280/PLE	50	25	82	92	73x73	58x58	7	101	280	69,03 €
RIM63-550/PLE	63	28	103	118	90x90	70x70	9	125	550	93,81 €
RIM75-800/PLE	75	30	120	132	95x95	70x70	11	142	800	126,19 €
RIM75-1000/PLE	75	30	120	132	95x95	70x70	11	142	1000	123,65 €

Dimensions in mm