

Lifting sling with 2 eyelinks

New


SGL1

Purple range SWL 1000kg

- **Lifting element**
- High quality polyester lifting slings according to European Industry regulations UNI EN 1492-1
- Flat sling
- Wide 30mm
- SWL: safe working load



F Max
1000kg



0°



F

0°



F x 0,8

≤6°



F x 2

0° to 45°



F x 1,4

45° to 60°



F

0° to 45°



F x 1,4

0° to 45°



F x 1,12

45° to 60°



F

45° to 60°



F x 0,8


DISCOUNTS

Qty	1+	4+	10+	15+
Disc.	List	-5%	-10%	On request


Part number	Fmax (kg)	Length L	W	E	L1	W2	Price each 1 to 3
SGL1-1000	1000	1000	30	7	200	15	
SGL1-1500	1000	1500	30	7	200	15	
SGL1-2000	1000	2000	30	7	200	15	
SGL1-2500	1000	2500	30	7	200	15	
SGL1-3000	1000	3000	30	7	200	15	
SGL1-4000	1000	4000	30	7	200	15	

Dimensions in mm

- **Lifting element**
- High quality polyester lifting slings according to European Industry regulations UNI EN 1492-1
- Flat sling
- Wide 60mm
- SWL: safe working load



F Max
2000kg



0°



F

0°



F x 0,8

≤6°



F x 2

0° to 45°



F x 1,4

45° to 60°



F

0° to 45°



F x 1,4

0° to 45°



F x 1,12

45° to 60°



F

45° to 60°



F x 0,8

DISCOUNTS

Qty	1+	4+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	Fmax (kg)	Length L	W	E	L1	W2	Price each 1 to 3
SGL2-1000	2000	1000	60	7	300	30	
SGL2-1500	2000	1500	60	7	300	30	
SGL2-2000	2000	2000	60	7	300	30	
SGL2-2500	2000	2500	60	7	300	30	
SGL2-3000	2000	3000	60	7	300	30	
SGL2-4000	2000	4000	60	7	300	30	
SGL2-5000	2000	5000	60	7	300	30	
SGL2-6000	2000	6000	60	7	300	30	
SGL2-8000	2000	8000	60	7	300	30	
SGL2-10000	2000	10000	60	7	300	30	
SGL2-12000	2000	12000	60	7	300	30	

Dimensions in mm

Lifting sling with 2 eyelinks

New

SGL3

Yellow range SWL 3000kg


- Lifting element

- High quality polyester lifting slings according to European Industry regulations UNI EN 1492-1
- Flat sling
- Wide 90mm
- SWL: safe working load



F Max
3000kg

F



0°



F

0°



F x 0,8

≤6°



F x 2

0° to 45°



F x 1,4

45° to 60°



F

0° to 45°



F x 1,4

0° to 45°



F x 1,12

45° to 60°



F

45° to 60°



F x 0,8

DISCOUNTS

Qty	1+	4+	10+	15+
Disc.	List	-5%	-10%	On request


Part number	Fmax (kg)	Length L	W	E	L1	W2	Price each 1 to 3
SGL3-1000	3000	1000	90	7	350	30	
SGL3-2000	3000	2000	90	7	350	30	
SGL3-3000	3000	3000	90	7	350	30	
SGL3-4000	3000	4000	90	7	350	30	
SGL3-5000	3000	5000	90	7	350	30	
SGL3-6000	3000	6000	90	7	350	30	
SGL3-8000	3000	8000	90	7	350	30	
SGL3-10000	3000	10000	90	7	350	30	
SGL3-12000	3000	12000	90	7	350	30	

Dimensions in mm

- **Lifting element**
- High quality polyester lifting slings according to European Industry regulations UNI EN 1492-1
- Flat sling
- Wide 120mm
- SWL: safe working load



F Max
4000kg



0°



F

0°



F x 0,8

≤6°



F x 2

0° to 45°



F x 1,4

45° to 60°



F

0° to 45°



F x 1,4

0° to 45°



F x 1,12

45° to 60°



F

45° to 60°



F x 0,8

DISCOUNTS

Qty	1+	4+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	Fmax (kg)	Length L	W	E	L1	W2	Price each 1 to 3
SGL4-1000	4000	1000	120	7	425	40	
SGL4-1500	4000	1500	120	7	425	40	
SGL4-2000	4000	2000	120	7	425	40	
SGL4-2500	4000	2500	120	7	425	40	
SGL4-3000	4000	3000	120	7	425	40	
SGL4-4000	4000	4000	120	7	425	40	
SGL4-5000	4000	5000	120	7	425	40	
SGL4-6000	4000	6000	120	7	425	40	
SGL4-8000	4000	8000	120	7	425	40	
SGL4-10000	4000	10000	120	7	425	40	
SGL4-12000	4000	12000	120	7	425	40	

Dimensions in mm

Lifting sling with 2 eyelinks


New

SGL5

Red range SWL 5000kg



- Lifting element

- High quality polyester lifting slings according to European Industry regulations UNI EN 1492-1
- Flat sling
- Wide 150mm
- SWL: safe working load



F Max
5000kg

F



0°



F

0°



F x 0,8

≤6°



F x 2

0° to 45°



F x 1,4

45° to 60°



F

0° to 45°



F x 1,4

0° to 45°



F x 1,12

45° to 60°



F

45° to 60°



F x 0,8

DISCOUNTS

Qty	1+	4+	10+	15+
Disc.	List	-5%	-10%	On request

Part number	Fmax (kg)	Length L	W	E	L1	W2	Price each 1 to 3
SGL5-1000	5000	1000	150	7	500	50	
SGL5-1500	5000	1500	150	7	500	50	
SGL5-2000	5000	2000	150	7	500	50	
SGL5-2500	5000	2500	150	7	500	50	
SGL5-3000	5000	3000	150	7	500	50	
SGL5-4000	5000	4000	150	7	500	50	

Dimensions in mm

Our other products



MSP23

Masterplate® glueable insert Ø23, Cylindrical Ø23 with threaded s...



J64

Spur gear coaxial gearbox, from 0.57 to 2.25 Nm - Inline



PSPE22

Conical flexible shaft handle Ø22, Black PVC



LVT

Miniature motorised actuator 2A, 2 ampers



BLHM40

Right angled gearbox, double output shafts, up to 10.3 Nm



NTMdl

Set screw delrin tip, Delrin-point



PTMR

Telescopic furniture foot, threaded stud



HSSss

Stainless steel shoulder screw ISO7379, Stainless steel ISO 7379




KON

Conical elasto buffer, Stainless steel



DHX

Dowel pin internal thread, Extractable



H3

Crossed helical gear crossed axis at 90°,



MDB_MTB

Moulded plastic bevel gear (nylon), 3:1

Complementary products