

Steel spur gear




Module

Steel 20NCD2

0.8



- Precision class 9
- Pressure angle 20°
- Linear speed 300m/min



Torque and power indication

For 50 teeth at 1000 rpm

	20NCD2	20NCD2 Z10CNF18.09 hardened	brass
Nm	1	5	0.54
kW	0.104	0.522	0.06

DISCOUNTS

Qty	1+	6+	20+	50+
Disc. List	-12%	-25%	On request	

Part number	Teeth Z	PCD ØP	External ØD	Boss ØM	Bore ØA	Weight (kg)			Price each 1 to 5	
						G	PG		G	PG
G0.8-12	12	9,60	11,20	11,20	5	0,009	0,004	✓	28,89	€
G0.8-13	13	10,40	12,00	12,00	5	0,011	0,005	-	29,67	€
G0.8-14	14	11,20	12,80	12,00	5	0,012	0,006	-	30,25	€
G0.8-15	15	12,00	13,60	12,00	5	0,013	0,007	✓	30,99	€
G0.8-16	16	12,80	14,40	12,00	5	0,014	0,008	✓	31,77	€
G0.8-17	17	13,60	15,20	12,00	5	0,015	0,010	-	32,78	€
G0.8-18	18	14,40	16,00	12,00	5	0,017	0,011	✓	33,42	€
G0.8-19	19	15,20	16,80	12,00	5	0,018	0,012	-	34,03	€
G0.8-20	20	16,00	17,60	12,00	5	0,020	0,014	✓	34,13	€
G0.8-21	21	16,80	18,40	12,00	5	0,021	0,015	-	34,49	€
G0.8-22	22	17,60	19,20	12,00	5	0,023	0,017	✓	34,88	€
G0.8-23	23	18,40	20,00	12,00	5	0,025	0,019	-	35,26	€
G0.8-24	24	19,20	20,80	12,00	5	0,026	0,021	✓	35,50	€
G0.8-25	25	20,00	21,60	12,00	5	0,028	0,023	✓	35,90	€
G0.8-26	26	20,80	22,40	12,00	5	0,030	0,024	-	36,29	€
G0.8-27	27	21,60	23,20	12,00	5	0,032	0,027	-	36,60	€
G0.8-28	28	22,40	24,00	12,00	5	0,034	0,029	-	36,77	€
G0.8-29	29	23,20	24,80	12,00	5	0,037	0,031	-	37,06	€
G0.8-30	30	24,00	25,60	16,00	6	0,043	0,032	✓	37,37	€
G0.8-31	31	24,80	26,40	16,00	6	0,045	0,035	-	37,39	€
G0.8-32	32	25,60	27,20	16,00	6	0,048	0,037	✓	37,46	€

On request

*Depending on availability - Dimensions in mm

Part number	Teeth Z	PCD ØP	External ØD	Boss ØM	Bore ØA	Weight (kg)		Price each 1 to 5 G	PG
						G	PG		
G0.8-33	33	26,40	28,00	16,00	6	0,050	0,040	-	37,62 €
G0.8-34	34	27,20	28,80	16,00	6	0,053	0,042	-	37,64 €
G0.8-35	35	28,00	29,60	16,00	6	0,056	0,045	-	37,68 €
G0.8-36	36	28,80	30,40	16,00	6	0,058	0,048	✓	37,80 €
G0.8-37	37	29,60	31,20	16,00	6	0,061	0,050	-	37,88 €
G0.8-38	38	30,40	32,00	16,00	6	0,064	0,053	-	38,00 €
G0.8-39	39	31,20	32,80	16,00	6	0,067	0,056	-	38,00 €
G0.8-40	40	32,00	33,60	16,00	6	0,070	0,059	✓	38,29 €
G0.8-41	41	32,80	34,40	16,00	6	0,073	0,062	-	38,32 €
G0.8-42	42	33,60	35,20	16,00	6	0,076	0,066	-	38,41 €
G0.8-43	43	34,40	36,00	16,00	6	0,080	0,069	-	38,47 €
G0.8-44	44	35,20	36,80	16,00	6	0,083	0,072	✓	38,53 €
G0.8-45	45	36,00	37,60	16,00	6	0,086	0,076	-	38,65 €
G0.8-46	46	36,80	38,40	16,00	6	0,090	0,079	-	38,82 €
G0.8-47	47	37,60	39,20	16,00	6	0,093	0,083	-	38,92 €
G0.8-48	48	38,40	40,00	16,00	6	0,097	0,086	-	39,05 €
G0.8-49	49	39,20	40,80	16,00	6	0,101	0,090	-	39,14 €
G0.8-50	50	40,00	41,60	16,00	6	0,105	0,094	✓	39,21 €
G0.8-51	51	40,80	42,40	16,00	6	0,108	0,098	-	39,47 €
G0.8-52	52	41,60	43,20	16,00	6	0,112	0,102	-	36,68 €
G0.8-53	53	42,40	44,00	16,00	6	0,116	0,106	-	39,78 €
G0.8-54	54	43,20	44,80	16,00	6	0,121	0,110	-	39,97 €
G0.8-55	55	44,00	45,60	16,00	6	0,125	0,114	-	40,11 €
G0.8-56	56	44,80	46,40	16,00	6	0,129	0,118	-	40,29 €
G0.8-57	57	45,60	47,20	16,00	6	0,133	0,123	-	40,50 €
G0.8-58	58	46,40	48,00	16,00	6	0,138	0,127	-	40,59 €
G0.8-59	59	47,20	48,80	16,00	6	0,142	0,132	-	40,84 €
G0.8-60	60	48,00	49,60	16,00	8	0,144	0,135	✓	41,04 €
G0.8-61	61	48,80	50,40	16,00	8	0,149	0,139	-	41,17 €
G0.8-62	62	49,60	51,20	16,00	8	0,153	0,144	-	41,38 €
G0.8-63	63	50,40	52,00	16,00	8	0,158	0,149	✓	41,47 €
G0.8-64	64	51,20	52,80	16,00	8	0,163	0,154	-	On request
G0.8-66	66	52,80	54,40	16,00	8	0,173	0,164	-	41,85 €
G0.8-68	68	54,40	56,00	16,00	8	0,183	0,174	-	42,04 €
G0.8-70	70	56,00	57,60	16,00	8	0,194	0,185	-	42,36 €
G0.8-75	75	60,00	61,60	16,00	8	0,222	0,213	-	42,88 €
G0.8-76	76	60,80	62,40	16,00	8	0,228	0,218	-	43,99 €
G0.8-80	80	64,00	65,60	16,00	8	0,252	0,242	-	45,16 €
G0.8-86	86	68,80	70,40	16,00	8	0,290	0,281	-	45,92 €
G0.8-88	88	70,40	72,00	16,00	8	0,303	0,294	-	46,58 €
G0.8-90	90	72,00	73,60	20,00	8	0,324	0,308	✓	47,57 €
G0.8-96	96	76,80	78,40	20,00	8	0,367	0,351	-	48,46 €
G0.8-100	100	80,00	81,60	20,00	8	0,397	0,381	✓	53,04 €
G0.8-112	112	89,60	91,20	20,00	8	0,495	0,479	-	61,50 €
G0.8-120	120	96,00	97,60	20,00	8	0,566	0,550	-	70,02 €
G0.8-127	127	101,60	103,20	25,00	10	0,633	0,617	-	84,12 €
G0.8-128	128	102,40	104,00	25,00	10	0,653	0,626	-	86,78 €
G0.8-140	140	112,00	113,60	25,00	10	0,777	0,750	-	91,63 €
G0.8-150	150	120,00	121,60	25,00	12	0,889	0,862	-	106,02 €

On request

↓ **Gears available up to this size**

G0.8-173 173 138,40 140,00 Dimensions : contact us

*Depending on availability - Dimensions in mm

Module

Steel 35NCD6

0.8




- Higher torque
- Precision class 9
- Pressure angle 20°
- Linear speed 300m/min

Options

- Material :
20NCD2 case-hardened

Torque and power indication				
For 50 teeth at 1000 rpm				
	35NCD6	35NCD6 hardened	20NCD2	20NCD2 hardened
Nm	4.000	5.800	4.000	11.000
kW	0.418	0.612	0.418	1.119



DISCOUNTS

Qty	1+	6+	20+	40+
Disc. List	-12%	-25%	On request	

Part number	Teeth Z	PCD ØP	External ØD	Boss ØM	Bore ØA	Weight (kg) YG	Weight (kg) XG	Stock*	Price each 1 to 5	
									YG	XG
YG0.8-12	12	9,60	11,20	11,20	5	0,011	0,004	-	On request	
YG0.8-13	13	10,40	12,00	12,40	5	0,014	0,005	✓	36,98	€
YG0.8-14	14	11,20	12,80	12,80	5	0,015	0,006	-	37,68	€
YG0.8-15	15	12,00	13,60	13,60	5	0,017	0,007	✓	38,65	€
YG0.8-16	16	12,80	14,40	14,00	5	0,019	0,008	-	39,63	€
YG0.8-17	17	13,60	15,20	14,00	5	0,020	0,010	-	40,84	€
YG0.8-18	18	14,40	16,00	14,00	5	0,022	0,011	✓	41,68	€
YG0.8-19	19	15,20	16,80	14,00	5	0,023	0,012	-	42,22	€
YG0.8-20	20	16,00	17,60	14,00	5	0,025	0,014	✓	42,67	€
YG0.8-21	21	16,80	18,40	14,00	5	0,026	0,015	-	42,91	€
YG0.8-22	22	17,60	19,20	14,00	5	0,028	0,017	-	43,52	€
YG0.8-23	23	18,40	20,00	14,00	5	0,030	0,019	-	43,99	€
YG0.8-24	24	19,20	20,80	14,00	5	0,031	0,021	-	44,22	€
YG0.8-25	25	20,00	21,60	14,00	5	0,033	0,023	✓	44,81	€
YG0.8-26	26	20,80	22,40	14,00	5	0,035	0,024	-	45,22	€
YG0.8-27	27	21,60	23,20	14,00	5	0,037	0,027	-	45,62	€
YG0.8-28	28	22,40	24,00	14,00	5	0,039	0,029	-	45,92	€
YG0.8-29	29	23,20	24,80	14,00	5	0,042	0,031	-	46,22	€
YG0.8-30	30	24,00	25,60	20,00	6	0,054	0,032	✓	46,48	€
YG0.8-31	31	24,80	26,40	20,00	6	0,056	0,035	-	46,58	€
YG0.8-33	33	26,40	28,00	20,00	6	0,061	0,040	-	47,01	€

On request

*Depending on availability - Dimensions in mm

Part number	Teeth Z	PCD ØP	External ØD	Boss ØM	Bore ØA	Weight (kg)		Stock ¹	Price each 1 to 5	
						YG	XG		YG	XG
YG0.8-34	34	27,20	28,80	20,00	6	0,063	0,042	-	47,03 €	
YG0.8-35	35	28,00	29,60	20,00	6	0,066	0,045	✓	47,13 €	
YG0.8-36	36	28,80	30,40	20,00	6	0,069	0,048	-	47,18 €	
YG0.8-37	37	29,60	31,20	20,00	6	0,072	0,050	-	47,29 €	
YG0.8-38	38	30,40	32,00	20,00	6	0,075	0,053	✓	47,44 €	
YG0.8-39	39	31,20	32,80	20,00	6	0,078	0,056	-	47,54 €	
YG0.8-40	40	32,00	33,60	20,00	6	0,081	0,059	✓	47,57 €	
YG0.8-41	41	32,80	34,40	20,00	6	0,084	0,062	-	47,67 €	
YG0.8-42	42	33,60	35,20	20,00	6	0,087	0,066	-	47,76 €	
YG0.8-43	43	34,40	36,00	20,00	6	0,090	0,069	-	47,84 €	
YG0.8-44	44	35,20	36,80	20,00	6	0,093	0,072	-	48,08 €	
YG0.8-45	45	36,00	37,60	20,00	6	0,097	0,076	-	48,30 €	
YG0.8-46	46	36,80	38,40	20,00	6	0,100	0,079	-	48,47 €	
YG0.8-47	47	37,60	39,20	20,00	6	0,104	0,083	-	48,55 €	
YG0.8-48	48	38,40	40,00	20,00	6	0,108	0,086	-	48,76 €	
YG0.8-49	49	39,20	40,80	20,00	6	0,111	0,090	-	48,79 €	
YG0.8-50	50	40,00	41,60	20,00	6	0,115	0,094	✓	48,83 €	
YG0.8-51	51	40,80	42,40	20,00	6	0,119	0,098	-	49,24 €	
YG0.8-52	52	41,60	43,20	20,00	6	0,123	0,102	-	49,43 €	
YG0.8-53	53	42,40	44,00	20,00	6	0,127	0,106	-	49,58 €	
YG0.8-54	54	43,20	44,80	20,00	6	0,131	0,110	-	49,78 €	
YG0.8-55	55	44,00	45,60	20,00	6	0,135	0,114	-	50,09 €	
YG0.8-56	56	44,80	46,40	20,00	6	0,140	0,118	-	50,21 €	
YG0.8-57	57	45,60	47,20	20,00	6	0,144	0,123	-	50,57 €	
YG0.8-58	58	46,40	48,00	20,00	6	0,148	0,127	-	50,71 €	
YG0.8-59	59	47,20	48,80	20,00	6	0,153	0,132	-	50,86 €	
YG0.8-60	60	48,00	49,60	20,00	6	0,157	0,136	-	51,09 €	
YG0.8-61	61	48,80	50,40	20,00	6	0,162	0,141	-	51,37 €	
YG0.8-62	62	49,60	51,20	20,00	6	0,167	0,146	-	51,58 €	
YG0.8-63	63	50,40	52,00	20,00	6	0,172	0,151	-	51,88 €	
YG0.8-64	64	51,20	52,80	20,00	6	0,177	0,155	-	52,05 €	
YG0.8-66	66	52,80	54,40	30,00	8	0,210	0,164	-	52,16 €	
YG0.8-68	68	54,40	56,00	40,00	8	0,254	0,174	-	52,44 €	
YG0.8-70	70	56,00	57,60	40,00	8	0,265	0,185	-	52,85 €	
YG0.8-75	75	60,00	61,60	40,00	8	0,293	0,213	-	53,51 €	
YG0.8-76	76	60,80	62,40	40,00	8	0,299	0,218	✓	54,72 €	
YG0.8-80	80	64,00	65,60	40,00	8	0,323	0,242	-	56,33 €	
YG0.8-86	86	68,80	70,40	40,00	8	0,361	0,281	-	57,11 €	
YG0.8-88	88	70,40	72,00	40,00	8	0,374	0,294	-	58,13 €	
YG0.8-90	90	72,00	73,60	40,00	8	0,388	0,308	-	59,33 €	
YG0.8-96	96	76,80	78,40	40,00	8	0,431	0,351	-	60,29 €	
YG0.8-100	100	80,00	81,60	40,00	8	0,461	0,381	✓	66,20 €	
YG0.8-112	112	89,60	91,20	40,00	8	0,559	0,479	-	76,81 €	
YG0.8-120	120	96,00	97,60	40,00	8	0,630	0,550	-	87,27 €	
YG0.8-127	127	101,60	103,20	40,00	10	0,697	0,617	-	104,81 €	
YG0.8-128	128	102,40	104,00	50,00	10	0,750	0,624	-	108,20 €	
YG0.8-140	140	112,00	113,60	50,00	10	0,873	0,748	-	114,34 €	
YG0.8-150	150	120,00	121,60	50,00	12	0,985	0,859	-	132,17 €	

On request

↓ **Gears available up to this size**

YG0.8-173	173	138,40	140,00	Dimensions : contact us
------------------	-----	--------	--------	-------------------------

¹Depending on availability - Dimensions in mm

Brass CuZn39Pb3



Module

0,8

- Spur gear with JIS grade Steeth (JISB1702-1:1998)
- Pressure angle 20°
- Material:
Brass CuZn39Pb3 (C6304)

Info

- *Torque (bending strength)



DISCOUNTS

Qty	1+	6+	10+
Disc.	Price	-12%	On request

Part number	Teeth		ØP	ØD	ØM	ØA (H7)	E	F	G	ØT	J	Torque* (Nm)	Weight (kg)	Price each 1 to 5
	Z	ØP												
GB0.8-15-RA04T	15	12,0	13,6	9,0	4	4	8	12	M3	4	0,20	0,007	On request	
GB0.8-16-RA04T	16	12,8	14,4	10,0	4	4	8	12	M3	4	0,22	0,008	On request	
GB0.8-20-RA05	20	16,0	17,6	13,5	5	4	8	12	-	-	0,31	0,014	30,36 €	
GB0.8-20-RA04T	20	16,0	17,6	12,0	4	4	8	12	M3	4	0,31	0,013	On request	
GB0.8-24-RA05T	24	19,2	20,8	16,0	5	4	8	12	M4	4	0,40	0,021	37,74 €	
GB0.8-25-RA05	25	20,0	21,6	17,0	5	4	8	12	-	-	0,43	0,024	37,38 €	
GB0.8-30-RA04T	30	24,0	25,6	20,0	4	4	8	12	M3	4	0,55	0,035	45,35 €	
GB0.8-30-RA05	30	24,0	25,6	20,0	5	4	8	12	-	-	0,55	0,034	43,39 €	
GB0.8-40-RA05	40	32,0	33,6	20,0	5	4	8	12	-	-	0,79	0,046	55,17 €	

Dimensions in mm

Plastic spur gear



Module


Machined Delrin

0.8



- Machined parts
- Quality standard 9
- Pressure angle 20°
- Working temp. -50°C to +80°C

Torque indication	
For 50 teeth at 1000 rpm	
	Delrin
Nm	0.3



DISCOUNTS

Qty.	1+	6+	30+
Disc.	List -22%	On request	

Part number	Teeth Z	PCD ØP	External ØD	Boss ØM	Bore ØA	Weight (kg)		Price each 1 to 5	
						ZG	ZPG	ZG	ZPG
ZG0.8-12	12	9,60	11,20	11,20	3	0,0012	0,0005	14,42 €	
ZG0.8-13	13	10,40	12,00	12,00	3	0,0014	0,0006	14,89 €	
ZG0.8-14	14	11,20	12,80	12,80	3	0,0016	0,0007	15,09 €	
ZG0.8-15	15	12,00	13,60	13,60	3	0,0019	0,0008	15,57 €	
ZG0.8-16	16	12,80	14,40	14,40	3	0,0021	0,0009	15,87 €	
ZG0.8-17	17	13,60	15,20	15,20	3	0,0024	0,0011	16,27 €	
ZG0.8-18	18	14,40	16,00	14,00	4	0,0023	0,0012	16,80 €	
ZG0.8-19	19	15,20	16,80	14,00	4	0,0024	0,0013	16,90 €	
ZG0.8-20	20	16,00	17,60	14,00	4	0,0025	0,0015	17,08 €	
ZG0.8-21	21	16,80	18,40	14,00	4	0,0027	0,0016	17,23 €	
ZG0.8-22	22	17,60	19,20	14,00	4	0,0029	0,0018	17,48 €	
ZG0.8-23	23	18,40	20,00	14,00	4	0,0030	0,0020	17,65 €	
ZG0.8-24	24	19,20	20,80	14,00	4	0,0032	0,0021	17,73 €	
ZG0.8-25	25	20,00	21,60	14,00	4	0,0034	0,0023	17,88 €	
ZG0.8-26	26	20,80	22,40	14,00	4	0,0036	0,0025	18,17 €	
ZG0.8-27	27	21,60	23,20	14,00	4	0,0038	0,0027	18,38 €	
ZG0.8-28	28	22,40	24,00	14,00	4	0,0040	0,0029	18,42 €	
ZG0.8-29	29	23,20	24,80	14,00	4	0,0043	0,0032	18,54 €	
ZG0.8-30	30	24,00	25,60	15,00	5	0,0046	0,0033	18,70 €	
ZG0.8-31	31	24,80	26,40	15,00	5	0,0048	0,0036	18,70 €	

On request

Dimensions in mm

DISCOUNTS

Qty.	1+	6+	30+
Disc.	List	-22%	On request

Part number	Teeth Z	PCD ØP	External ØD	Boss ØM	Bore ØA	Weight (kg)		Price each 1 to 5	
						ZG	ZPG	ZG	ZPG
ZG0.8-32	32	25,60	27,20	15,00	5	0,0050	0,0038	18,76 €	
ZG0.8-33	33	26,40	28,00	15,00	5	0,0053	0,0041	18,76 €	
ZG0.8-34	34	27,20	28,80	15,00	5	0,0055	0,0043	18,76 €	
ZG0.8-35	35	28,00	29,60	15,00	5	0,0058	0,0046	18,91 €	
ZG0.8-36	36	28,80	30,40	15,00	5	0,0061	0,0049	20,86 €	
ZG0.8-38	38	30,40	32,00	15,00	5	0,0067	0,0054	21,03 €	
ZG0.8-39	39	31,20	32,80	15,00	5	0,0070	0,0057	21,03 €	
ZG0.8-40	40	32,00	33,60	15,00	5	0,0073	0,0061	21,14 €	
ZG0.8-41	41	32,80	34,40	15,00	5	0,0076	0,0064	21,14 €	
ZG0.8-42	42	33,60	35,20	15,00	5	0,0079	0,0067	21,14 €	
ZG0.8-43	43	34,40	36,00	15,00	5	0,0082	0,0070	21,16 €	
ZG0.8-44	44	35,20	36,80	15,00	5	0,0086	0,0074	21,16 €	
ZG0.8-45	45	36,00	37,60	15,00	5	0,0089	0,0077	21,35 €	
ZG0.8-46	46	36,80	38,40	15,00	5	0,0093	0,0081	21,35 €	
ZG0.8-47	47	37,60	39,20	15,00	5	0,0096	0,0084	21,53 €	
ZG0.8-48	48	38,40	40,00	15,00	5	0,0100	0,0088	24,52 €	
ZG0.8-49	49	39,20	40,80	15,00	5	0,0104	0,0092	24,52 €	
ZG0.8-50	50	40,00	41,60	15,00	5	0,0108	0,0095	24,52 €	
ZG0.8-51	51	40,80	42,40	15,00	5	0,0111	0,0099	24,81 €	
ZG0.8-52	52	41,60	43,20	15,00	5	0,0115	0,0103	24,85 €	
ZG0.8-53	53	42,40	44,00	15,00	5	0,0120	0,0107	25,02 €	
ZG0.8-54	54	43,20	44,80	15,00	5	0,0124	0,0112	25,12 €	
ZG0.8-55	55	44,00	45,60	15,00	5	0,0128	0,0116	25,26 €	
ZG0.8-57	57	45,60	47,20	18,00	6	0,0141	0,0124	25,38 €	
ZG0.8-58	58	46,40	48,00	18,00	6	0,0146	0,0128	25,48 €	
ZG0.8-59	59	47,20	48,80	18,00	6	0,0150	0,0133	25,68 €	
ZG0.8-60	60	48,00	49,60	18,00	6	0,0155	0,0137	25,72 €	
ZG0.8-61	61	48,80	50,40	18,00	6	0,0160	0,0142	31,13 €	
ZG0.8-62	62	49,60	51,20	18,00	6	0,0164	0,0147	31,28 €	
ZG0.8-63	63	50,40	52,00	18,00	6	0,0169	0,0152	31,32 €	
ZG0.8-64	64	51,20	52,80	18,00	6	0,0174	0,0157	31,51 €	
ZG0.8-66	66	52,80	54,40	18,00	6	0,0184	0,0167	31,62 €	
ZG0.8-68	68	54,40	56,00	18,00	6	0,0195	0,0177	31,77 €	
ZG0.8-70	70	56,00	57,60	18,00	6	0,0205	0,0188	On request	
ZG0.8-75	75	60,00	61,60	18,00	6	0,0233	0,0216	36,77 €	
ZG0.8-76	76	60,80	62,40	18,00	6	0,0239	0,0222	38,65 €	
ZG0.8-80	80	64,00	65,60	18,00	6	0,0263	0,0246	39,22 €	
ZG0.8-86	86	68,80	70,40	18,00	6	0,0302	0,0285	40,00 €	
ZG0.8-88	88	70,40	72,00	18,00	6	0,0316	0,0298	40,71 €	
ZG0.8-90	90	72,00	73,60	22,00	6	0,0339	0,0312	40,71 €	
ZG0.8-96	96	76,80	78,40	22,00	6	0,0382	0,0355	44,02 €	
ZG0.8-100	100	80,00	81,60	22,00	8	0,0413	0,0386	48,08 €	
ZG0.8-112	112	89,60	91,20	22,00	8	0,0511	0,0484	62,18 €	
ZG0.8-120	120	96,00	97,60	30,00	10	0,0583	0,0556	70,62 €	
ZG0.8-140	140	112,00	113,60	30,00	10	0,0785	0,0758	83,27 €	
ZG0.8-150	150	120,00	121,60	30,00	12	0,0898	0,0870	102,52 €	

On request



Gears available up to this size

ZG0.8-173 173 138,40 140,00 Dimensions : contact us

Dimensions in mm