Diabolo-shaped elasto mount

AT-ZY

Male / male mounting

- ***Radial elasticity greater than axial elasticity***
- *Cylinder worked under compression or shearing*
- *Materials:*
  core: Steel plates
  cylinder: Rubber
- ***Hardness: NK 55-60 shore A***
- *Working temp: -40°C to +70°C*



Uses

- *Dampens sound and vibrations*





DISCOUNTS

Qty	1+	6+	20+	40+	100+	200+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	ØG	ØD	H	L	Stock*	Price each 1 to 5
AT-ZY4-10-10	M4	10	10	10	✔	1,85 €
AT-ZY6-20-15	M6	20	15	18	✔	3,71 €
AT-ZY6-20-30	M6	20	30	12	✔	3,71 €
AT-ZY6-25-20	M6	25	20	12	✔	3,99 €
AT-ZY8-30-20	M8	30	20	20	✔	5,45 €
AT-ZY8-40-30	M8	40	30	20	✔	7,30 €
AT-ZY8-40-48	M8	40	48	23	✔	10,98 €
AT-ZY10-40-28	M10	40	28	20	-	8,08 €
AT-ZY10-46-25	M10	46	25	20	-	11,77 €
AT-ZY10-50-30	M10	50	30	33	✔	13,45 €
AT-ZY12-75-40	M12	75	40	37	-	20,20 €
AT-ZY16-100-55	M16	100	55	45	-	66,95 €

**Depending on availability - Dimensions in mm*

Our other products


SA_SAKH

Housing for linear bearing, Closed - light load


BFD

Locking pin for bush, +180°C


PRF4532

Standard aluminium profile, 45 x 32 mm


H0

Crossed helical gear crossed axis at 90°, Steel 20NCD2


SEV

Vertical stirrup toggle clamp, Vertical Latch Clamp - steel


HW_HT

Half-rail guide, Rail


TCLar__

Automatic chain tensioner, With wide guide


CHA138

Screwed hinge with threaded insert, 138 degrees


PSPT

Flexible tube handle, PVC


PTA100

Articulated levelling foot, pressed base


CFC

Spring loaded position switch, Electric


SLB

Indexing plunger, steel class 5.8

Complementary products


ATZYSS

Stainless steel diabolo shaped elasto mount, Stainless steel


CTZY

Diabolo shaped elasto mount, Steel


AZY

Cylindrical elasto mount, Steel


BZY

Cylindrical elasto mount, Steel