- ***Universal support arm***
- *Material :*
  Aluminium with steel screws

Advantages

- *Reliable operation*
- *Flexible mounting*





BDP20-50/R



BAN20/U

Typical application

DISCOUNTS

Qty	1+	10+	30+
Disc.	List	-5%	On request

Part number	ØA	B	ØC	L	⍁F	N	Weight (g)	Price each 1 to 9
BDP20-50/R	20	15	20	50	25	35	61	36,48 €
BDP20-100/R	20	15	20	100	25	35	80	44,62 €
BDP20-150/R	20	15	20	150	25	35	95	46,82 €
BDP30-200/R	30	17	30	200	35	42	95	57,49 €

Dimensions in mm

Our other products



NK40

Drylin®N miniature guiding system, Witdh 40 mm



CPAS-H

Folding bracket, For heavy loads



CCLSS

Stainless steel wire thimble, Stainless steel



HRV

V- rail guidance Simple Select® system, Rail with carriage



NKXR

Combined bearing without inner ring, Needle and cylindrical rollers



DQG319

Motor-gearbox 12V and 24V DC, from 4 to 9 Nm



TM_CTM_CTF

Suction cup threaded insert, Insert for suction cup - Tread click-in



INS

Self tapping steel insert, Steel



VAP

Magnetic stud with central hole, With central hole



TTQ

Self centering Hexagonal locking assembly, Medium



AZY_SS

Stainless steel cylindrical elasto mount, Stainless steel



DOMI50

Domino 50 adjustable slide, Slide DOMILINE 50

Complementary products



BDP1R

Adjustable support arm, Single clamp



BDP2R

Adjustable support arm, Increased grip