


# Clavette rectangulaire **DIN 6885** **Aci** **DIN** **Stock**

## KK

## Acier

- Liaison par obstacle
- Forme A
- Nécessite l'usinage de rainures de clavette
- Matière : acier C45  
60 daN/mm<sup>2</sup>
- Vendu par multiple, nous contacter



### Options

- Existe en inox (316) et cote pouce

### REMISES

Qté	1+	6+	20+	50+	100+	200+	500+
Rem. Prix	-15%	-45%	-55%	-65%	-70%	Sur demande	

Références	W (h9)	H (h11)	L	Stock*	Prix Uni. 1 à 5
KK2-10	2	2	10	✓	0,50 €
KK2-14	2	2	14	✓	0,50 €
KK2-20	2	2	20	✓	0,50 €
KK2-22	2	2	22	✓	0,50 €
KK3-8	3	3	8	✓	0,38 €
KK3-10	3	3	10	✓	0,42 €
KK3-12	3	3	12	✓	0,38 €
KK3-15	3	3	15	✓	0,38 €
KK3-20	3	3	20	✓	0,39 €
KK3-30	3	3	30	✓	0,38 €
KK3-40	3	3	40	✓	0,38 €
KK4-8	4	4	8	✓	0,38 €
KK4-10	4	4	10	✓	0,38 €
KK4-12	4	4	12	✓	0,38 €
KK4-15	4	4	15	✓	0,38 €
KK4-16	4	4	16	✓	0,38 €
KK4-20	4	4	20	✓	0,38 €
KK4-25	4	4	25	✓	0,39 €
KK5-10	5	5	10	✓	0,38 €
KK5-12	5	5	12	✓	0,38 €
KK5-14	5	5	14	✓	0,38 €
KK5-16	5	5	16	✓	0,38 €
KK5-18	5	5	18	✓	0,38 €
KK5-20	5	5	20	✓	0,40 €
KK5-25	5	5	25	✓	0,38 €
KK5-30	5	5	30	✓	0,42 €
KK5-35	5	5	35	✓	0,50 €
KK5-40	5	5	40	✓	0,50 €
KK5-50	5	5	50	✓	0,46 €
KK6-12	6	6	12	✓	0,50 €
KK6-14	6	6	14	✓	0,50 €
KK6-16	6	6	16	✓	0,50 €

Références	W (h9)	H (h11)	L	Stock*	Prix Uni. 1 à 5
KK6-18	6	6	18	✓	0,50 €
KK6-20	6	6	20	✓	0,50 €
KK6-25	6	6	25	✓	0,50 €
KK6-28	6	6	28	✓	0,50 €
KK6-30	6	6	30	✓	0,50 €
KK6-32	6	6	32	✓	0,50 €
KK6-36	6	6	36	✓	0,53 €
KK6-45	6	6	45	✓	0,66 €
KK6-50	6	6	50	✓	0,61 €
KK8-7-18	8	7	18	✓	0,66 €
KK8-7-20	8	7	20	✓	0,66 €
KK8-7-22	8	7	22	✓	0,66 €
KK8-7-25	8	7	25	✓	0,68 €
KK8-7-30	8	7	30	✓	0,66 €
KK8-7-40	8	7	40	✓	0,76 €
KK8-7-45	8	7	45	✓	1,51 €
KK8-7-50	8	7	50	✓	0,82 €
KK10-8-20	10	8	20	✓	0,81 €
KK10-8-28	10	8	28	✓	0,81 €
KK10-8-30	10	8	30	✓	0,94 €
KK10-8-36	10	8	36	✓	0,94 €
KK10-8-40	10	8	40	✓	0,94 €
KK10-8-45	10	8	45	✓	1,09 €
KK10-8-50	10	8	50	✓	1,09 €
KK12-8-36	12	8	36	✓	1,23 €
KK12-8-40	12	8	40	✓	1,23 €
KK12-8-45	12	8	45	✓	1,37 €
KK12-8-50	12	8	50	✓	1,41 €
KK12-8-56	12	8	56	-	1,51 €
KK12-8-60	12	8	60	✓	1,51 €
KK14-9-50	14	9	50	✓	1,68 €
KK14-9-70	14	9	70	✓	2,35 €

\*Dans la limite du disponible