


- Bague de blocage pour butée sur arbre avec obstacle

Grand choix d'alésages



REMISES

Qté	1+	6+	20+	40+
Rem. Prix	-15%	-20%	Sur demande	

Références	ØA	L	Vis	Matière	Alésage ØD	Stock*	Prix Uni. 1 à 5
CT3-3	16	5	M3	Inox 303	3	-	52,83 €
CT3-4	16	5	M3	Inox 303	4	-	26,54 €
CT3-5	16	5	M3	Inox 303	5	-	26,54 €
CT3-6	16	5	M3	Inox 303	6	-	26,22 €
CT5-5	22	5	M3	Inox 303	5	-	30,47 €
CT5-6	22	5	M3	Inox 303	6	-	30,47 €
CT5-7	22	5	M3	Inox 303	7	-	30,47 €
CT5-8	22	5	M3	Inox 303	8	-	30,09 €
CT8-8	25	8	M4	Inox 303	8	-	33,69 €
CT8-9	25	8	M4	Inox 303	9	-	33,69 €
CT8-10	25	8	M4	Inox 303	10	✓	33,69 €
CT10-10	30	8	M4	Inox 303	10	-	33,69 €
CT10-11	30	8	M4	Inox 303	11	-	33,69 €
CT10-12	30	8	M4	Inox 303	12	✓	33,69 €
CT10-13	30	8	M4	Inox 303	13	-	33,69 €
CT12-12	32	10	M5	Inox 303	12	-	37,87 €
CT12-13	32	10	M5	Inox 303	13	-	37,87 €
CT12-14	32	10	M5	Inox 303	14	✓	37,87 €
CT12-15	32	10	M5	Inox 303	15	-	37,87 €
CT15-15	38	10	M5	Inox 303	15	-	40,32 €
CT15-16	38	10	M5	Inox 303	16	-	40,32 €
CT15-17	38	10	M5	Inox 303	17	-	40,32 €
CT15-18	38	10	M5	Inox 303	18	-	40,32 €
CT17-17	40	10	M5	Inox 303	17	-	43,87 €
CT17-18	40	10	M5	Inox 303	18	-	43,87 €
CT17-19	40	10	M5	Inox 303	19	-	43,87 €
CT17-20	40	10	M5	Inox 303	20	-	43,87 €
CT20-19	43	10	M5	Inox 303	19	-	48,74 €
CT20-20	43	10	M5	Inox 303	20	✓	48,74 €
CT20-22	43	10	M5	Inox 303	22	-	48,74 €
CT20-23	43	10	M5	Inox 303	23	-	48,74 €
CT25-25	48	15	M6	Acier	25	-	62,13 €
CT30-30	55	15	M6	Acier	30	-	75,38 €
CT35-35	60	15	M6	Acier	35	-	88,21 €
CT40-40	65	15	M6	Acier	40	--	101,44 €

*Dans la limite du disponible - Dimensions en mm