DOMIMD For precise rotary positioning

- ***Manually operated rotary table***
- *Fast and accurate adjustment*
- *High position repeatability*
- *Principle: High-precision worm and wheel*
- *Fix using CHC4 screws*
- *Locking torque 10Nm*
- *Ratio: 55/1*

Precise and rapid adjustment



DOMI-MD55

Accessories

- **DOMI-M** *mounting plate required when attaching to adjustable slides*









DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-20%	On request

Part number	Rotation range	Max. torque input (Nm)	Max. torque on table (Nm)	Tolerance Concentricity (mm)	Tolerance Flatness (mm)	Weight (kg)	Price each
DOMI-MDV55	0 to + ∞	1,5	5	+/- 0,02	+/- 0,02	0,61	873,93 €

Dimensions in mm

For precise rotary positioning

DOMIMD

- ***Manually operated rotary table***
- *Fast and accurate adjustment*
- *High position repeatability*
- *Principle: High-precision worm and wheel*
- *Fix using CHC4 screws*
- *Locking torque 10Nm*
- *Ratio: 40/1*

Precise and rapid adjustment



Accessories

- **DOMI-M** *mounting plate required when attaching to adjustable slides*





DISCOUNTS

Qty	1+	2+	3+
Disc.	List	-20%	On request

Part number	Rotation range	Max. torque input (Nm)	Max. torque on table (Nm)	Tolerance Concentricity (mm)	Tolerance Flatness (mm)	Weight (kg)	Price each
DOMI-MDV80	0 to + ∞	2,5	5	+/- 0,03	+/- 0,03	1,60	1 495,11 €

Dimensions in mm

Our other products

CHAE4080PA

Symetrical decorative screwed hinge, Polyamide

PW_PWG25

Worm - precision range, Stainless steel

AC

Strike for toggle latch, 18mm

PRF-CHAR-POU

Tool holder for aluminium profile, Moveable tool holder

BPM

Slotted spring plunger with ball tip, Steel

RCC_RCX

Spherical tilt washer - DIN6319, convex

B

Steel bevel gear, 1:1

CHA35

Hinge for aluminium profile, Hinge

LWH

High rigidity linear slide, Rail - from 9320 N to 71300 N

PTAF80-PAMF80

Articulated fixable foot with pressed base Ø80, Ø 80

DIV

Locking bolt, With grip - Steel

PRF-SRA-78

Lock for aluminium profile, Quick fitting, self locking door lock

Complementary products

DOMI_MD

Domino rotary table, 55/1

DOMI120

Domino 120 adjustable slide, Slide DOMILINE 120