

Long hinge in steel or aluminium **AluSte**

CHAL

Piano type hinge

- Long hing with a small pin diameter
- Rolled joint
- Hinge is not drilled
- Materials:
 - Untreated steel
 - Aluminium

Economical





Applications

- Woodworking, industrial joinery, workstations...

Advantages

- Compact design
- Possibility of cutting to the length desired



Typical application

DISCOUNTS

| | | | |
|------------|----|-----|------------|
| Qty | 1+ | 6+ | 20+ |
| Disc. List | | -5% | On request |

| Part number | A | L | P | E | ØN | Weight per metre (kg/m) | Stock* | Price each 1 to 5 |
|------------------|----|------|----|-----|----|-------------------------|--------|-------------------|
| Steel | | | | | | | | |
| CHAL3-40-1000 | 40 | 1000 | 20 | 1,2 | 3 | 0,530 | ✓ | 12,33 € |
| CHAL3-50-1000 | 50 | 1000 | 20 | 1,2 | 3 | 0,610 | ✓ | 12,98 € |
| Aluminium | | | | | | | | |
| CHAL3-35-1000/A | 35 | 1000 | 20 | 1,0 | 3 | 0,175 | ✓ | 14,37 € |
| CHAL3-40-1000/A | 40 | 1000 | 20 | 1,0 | 3 | 0,208 | ✓ | 14,56 € |
| CHAL4-50-1000/A | 50 | 1000 | 30 | 1,5 | 4 | 0,300 | ✓ | 18,95 € |

*Depending on availability - Dimensions in mm

- Long hinge with a small pin diameter
- Rolled joint
- Hinge is not drilled
- Material:
304 stainless steel

Economical





Applications

- Woodworking, industrial joinery, workstations...

Advantages

- Compact design
- Possibility of cutting to the length desired



Typical application

DISCOUNTS

| | | | |
|-------|------|-----|------------|
| Qty | 1+ | 6+ | 20+ |
| Disc. | List | -5% | On request |

| Part number | A | L | P | E | ØN | Weight per metre (kg/m) | Stock* | Price each 1 to 5 |
|------------------|----|------|----|-----|-----|-------------------------|--------|-------------------|
| | | | | | | | | |
| CHAL2-20-1000/SS | 20 | 1000 | 15 | 0,6 | 2,5 | 0,140 | ✓ | 17,09 € |
| CHAL2-25-1000/SS | 25 | 1000 | 15 | 0,6 | 2,5 | 0,165 | - | 17,11 € |
| CHAL2-30-1000/SS | 30 | 1000 | 15 | 0,6 | 2,5 | 0,190 | - | 18,10 € |
| CHAL3-25-1000/SS | 25 | 1000 | 20 | 1,0 | 3,0 | 0,325 | ✓ | 18,26 € |
| CHAL3-40-1000/SS | 40 | 1000 | 20 | 1,2 | 3,0 | 0,520 | ✓ | 24,88 € |
| CHAL3-50-1000/SS | 50 | 1000 | 20 | 1,2 | 3,0 | 0,620 | ✓ | 26,87 € |
| CHAL6-60-1000/SS | 60 | 1000 | 30 | 2,0 | 6,0 | 1,470 | ✓ | 66,33 € |
| CHAL6-80-1000/SS | 80 | 1000 | 30 | 2,0 | 6,0 | 1,700 | - | 75,93 € |

*Depending on availability - Dimensions in mm