

1 right hand start, 1 left hand start LRHss

- ***Lead screw with 1 right hand thread and 1 left hand thread***
- *Machined trapezoidal thread conforming to DIN 103*
- *Thread tolerance: 7e class 100*
- *Machined*
- *Material: Stainless steel 304*

stainless steel


NEW !







Uses

- *Machine tools*
- *Lathe main screw*







DISCOUNTS

Qty	1+	2+	4+
Disc.	List	-5%	On request

Part number	ØD	Pitch P (mm)	A (mm)	B (mm)	Prix each
Length 1000mm					
LRH164-1/SS	16	4	20	490	
LRH184-1/SS	18	4	20	490	
LRH204-1/SS	20	4	20	490	
LRH245-1/SS	24	5	20	490	
LRH306-1/SS	30	6	20	490	
LRH326-1/SS	36	6	20	490	
Length 2000mm					
LRH164-2/SS	16	4	20	990	
LRH184-2/SS	18	4	20	990	
LRH204-2/SS	20	4	20	990	
LRH245-2/SS	24	5	20	990	
LRH306-2/SS	30	6	20	990	
LRH326-2/SS	36	6	20	990	

Dimensions in mm

Our other products



Crossed helical gear crossed axis at 90°, Steel 20NCD2



Worm and wheel gear reducer, up to 57 Nm



Worm and wheel set, Non hardened steel



Motor-gearbox 12V and 24V DC, from 1.5 to 2 Nm



Idler chain sprocket, For standard applications



Self-centering locking Assembly, Medium/low torque



Connecting plate for AT type timing belts, AT10



End support, Surface mounting



Self-locking ball pin lifting ring for threaded hole, Self-



Manual bevel gearbox, Bevel



Shaft for linear guides, Hardened ground stainless steel



Worm and wheel gear reducer, up to 298 Nm

Complementary products




Trapezoidal bronze nut, Bronze - 1 thread



Flanged bronze nut, Bronze - 1 thread



Lead screw clamping collar, Aluminium



Square steel nut, Steel - 1 thread