Plastic chain sprocket

New Eco Nyl

DIN 06B-1 3/8"

Moulded Nylon PA6





- **Pitch 3/8" (9,525mm) (DIN 06B-1)**
- Roll diameter 6.35mm
- Material
  Glass-fibre reinforced nylon PA6
  Grey colour

Application

- Low coefficient of friction
- Requires little lubrication
- Quiet
- Resistant to aqueous and aggressive environments

Option

- Bore + keyway on request from 10 pieces upwards

Info

- Rough pilot bore after moulding
- **Pilot bore dimension given as a guide only



DISCOUNTS

Qty	1+	10+	20+	50+	100+
Disc.	List	-10%	-15%	-25%	On request

Part number	Z teeth	ØD	ØP	ØM	Pre bore ØA**	E	ØF	Price each 1 to 9
PCS37-12/PA6	12	40,5	36,8	25	8	25	-	3,25 €
PCS37-13/PA6	13	43,5	39,8	28	8	25	-	3,93 €
PCS37-14/PA6	14	46,5	42,8	30	8	25	-	4,28 €
PCS37-15/PA6	15	49,5	45,8	34	8	25	-	4,85 €
PCS37-17/PA6	17	55,5	51,8	35	10	28	-	5,13 €
PCS37-18/PA6	18	58,6	54,9	40	10	28	-	5,87 €
PCS37-19/PA6	19	61,6	57,9	44	12	28	-	6,26 €
PCS37-20/PA6	20	64,6	60,9	44	12	28	-	6,79 €
PCS37-21/PA6	21	67,6	63,9	48	12	28	-	6,83 €
PCS37-25/PA6	25	79,7	76,0	57	12	28	-	7,92 €
PCS37-30/PA6	30	94,8	91,12	40	12	28	-	9,73 €
PCS37-36/PA6	36	113,0	109,2	70	16	30	-	10,18 €

Dimensions in mm

Plastic chain sprocket

Moulded Nylon PA6

DIN 08B-1

1/2"





- **Pitch 1/2" (12,7mm) (DIN 08B-1)**
- Roller diameter 8,51mm
- Material :
  Glass-fibre reinforced nylon PA6
  Grey colour

Application

- Low coefficient of friction
- Requires little lubrication
- Quiet
- Resistant to aqueous and aggressive environments

Option

- Bore + keyway on request from 10 pieces upwards

Info

- Rough pilot bore after moulding
- **Pilot bore dimension given as a guide only



DISCOUNTS

Qty	1+	10+	20+	50+	100+
Disc.	List	-10%	-15%	-25%	On request

Part number	Z teeth	ØD	ØP	ØM	Pre bore ØA**	E	ØF	Price each 1 to 9
PCS50-9/PA6	9	42,0	37,13	24	10	28	-	4,74 €
PCS50-10/PA6	10	45,9	41,10	26	10	28	-	5,09 €
PCS50-12/PA6	12	54,6	49,07	32	10	28	-	5,13 €
PCS50-14/PA6	14	63,2	57,07	41	10	28	-	5,16 €
PCS50-15/PA6	15	65,9	61,09	45	10	28	-	5,20 €
PCS50-16/PA6	16	69,9	65,10	45	10	28	-	5,23 €
PCS50-17/PA6	17	74,0	69,11	50	11	28	-	6,19 €
PCS50-18/PA6	18	78,0	73,13	50	11	28	-	6,33 €
PCS50-20/PA6	20	86,0	81,19	50	11	28	-	8,48 €
PCS50-21/PA6	21	91,3	85,22	50	11	29	-	8,88 €
PCS50-28/PA6	28	118,3	113,40	60	16	29	-	11,31 €
PCS50-30/PA6	30	126,3	121,50	60	16	30	-	12,20 €
PCS50-36/PA6	36	150,6	145,70	60	16	30	125	14,25 €
PCS50-38/PA6	38	158,6	153,80	60	16	30	125	15,24 €
PCS50-40/PA6	40	166,8	161,87	60	16	30	135	17,15 €

Dimensions in mm

Our other products


RFK38C

Hypoid gearbox - Stainless steel, up to 200 Nm


PPS

Lifting ring, Universal threaded


FDS

Flexible drive shaft, Masterflex® Steel, with PVC casing


BAG0

Locking rings in steel , Steel


QN

Single row cylindrical roller bearing, Free outer ring


BHC

Socket head button screw, Stainless steel A2


YG0

HEAVY DUTY spur gear, Steel 35NCD6


BH02

Single housed bearing assembly, Bearing secured with circlips


PW_PWG1

Worm - precision range, Steel


MFBC

Flexible Bellows coupling, Aluminium and Bronze - with


DGSI

Female rod ends, Steel / steel - Economy range


PSG25

Spur gear - precision range, Pre-hardened Steel 35NCD6

Complementary products


PCS37

Chain sprocket - steel, 9.525mm (DIN06B-1)


PCS37SS

Chain sprocket - Stainless steel, 9.525 (DIN 06B-1)


PCS37K

Chain sprocket with hardened teeth, 9.525mm (DIN06B-1)