Stock Aluminium profile with extendable slot

Section: 45x45 mm MiniTec PRF4545P

- **Profile for creating modular structures**
- Slots of the required length can be opened on any face
- To be cut to length once supplied
- Material: anodised aluminium
- **Covers are not sold individually, please contact us for details**



Accessories


- Universal fastener **PRF-FIX-UNI**
- Right angle **PRF19-E, PRF25-E, PRF45-E, PRF4590-E**
- Standard fastener **PRF-FIX-STD**
- Screwed-in assemblies

Tools


- Stripper **PRF-TOOL-OR**
- Trimmer **PRF-TOOL-EB**

Uses


- All types of construction, especially where strict hygiene rules must be adhered to, such as the food or pharmaceutical industries
- Central of the profile can be used as a channel for a counterweight



PRF4545-3/P



PRF4545-C



DISCOUNTS profile

Qty	1+	5+	10+
Disc.	List	-5%	On request

DISCOUNTS cover

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Ix (cm⁴)	Iy (cm⁴)	Length (mm)	Weight (kg/m)	Stock*	Price each
Profile						
PRF4545-3/P	14,095	14,095	3000	2,01	✔	92,91 €
Cover						
PRF4545-C			End cap		✔	1,04 €
PRF45-EG			Fixing cover		-	0,72 €
Tools						
PRF-TOOL-OR			Stripper		✔	25,89 €
PRF-TOOL-EB			Deburring tool		-	134,74 €

**Depending on availability - Dimensions in mm*

Our other products



EZYSS

Stainless steel cylindrical stop, stainless steel



ECF

Well nut, Chloroprene elastomer



PRF4545_P

Stripp Aluminium profile with extendable slot, 45 x 45 mm



PITAss

Locking bolt, with T handle



ZHG6

Plastic spur gear, Machined plastic (delrin)



E20

Right angle helical reducers, from 0.60 to 3.84 Nm



RPP

Connecting plate for RPP type timing belts, RPP14



DSF

Slip friction clutch, 4 to 2800 Nm



BAG0

Locking rings in steel , Steel



SH2

Parallel axis helical gear, Steel 20NCD2



PTAF100-PAMF100

Articulated fixable foot with pressed



CHAFR-MINI

Miniature friction hinge, Friction

Complementary products



PRF_FIX_UNI

Universal fastener for aluminium profile, Universal