Closed polymer DryLin®R bearing

Unaffected by dirt

RJUM01
RJZM01

- ***Closed bearing with polymer slide surface***
- *Max. speed*
  Dry working 8m/s
  With lubrication >10 m/s
- *Working temperature from -60°C to +100°C*
  (wear increases if temperature >80°C)
- *Max. load 35 N/mm²*
- *Recommended load 5N/mm² (linear)*
- *Material:*
  Housing: Aluminium
  Bearing: DryLin®R

Fast and silent

Advantages

- *Maintenance free*
- *Self lubricating*
- *20% of weight of equivalent steel version*
- *Silent in operation*

Accessories

- ***AWM** aluminium shaft*

Until -22%**





DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	List	-10%	-15%	-20%	On request

Part number	Ød1	Tolerance	Ød2 (h7)	B (h10)	B1 (H10)	s (H10)	Ødn	Stock*	Price each 1 to 5
RJZM01-05	5	0,02 - 0,05	12	22	14,20	1,10	11,50	✔	14,68 €
RJZM01-08	8	0,02 - 0,05	16	25	16,20	1,10	15,20	✔	14,98 €
RJUM01-10	10	0,02 - 0,05	19	29	21,60	1,30	17,50	✔	16,13 €
RJUM01-12	12	0,02 - 0,05	22	32	22,60	1,30	20,50	✔	19,22 €
RJUM01-16	16	0,02 - 0,05	26	36	24,60	1,30	24,20	✔	21,07 €
RJUM01-20	20	0,02 - 0,06	32	45	31,20	1,60	29,60	✔	26,40 €
RJUM01-25	25	0,02 - 0,06	40	58	43,70	1,85	36,50	✔	34,02 €
RJUM01-30	30	0,02 - 0,07	47	68	51,70	1,85	43,50	✔	43,62 €
RJUM01-40	40	0,02 - 0,07	62	80	60,30	2,15	57,80	-	71,43 €
RJUM01-50	50	0,02 - 0,09	75	100	77,30	2,65	70,50	-	104,89 €

**Depending on availability - Dimensions in mm*

Our other products

Fixed cylindrical handle, Fixed non-turning handle

Molded polyamide face-mounted hinge, Black polyamide

Machined plastic bevel gear , 1:1



Threaded spherical knob, Stainless steel 304

Internal gear, Machined plastic (delrin)

Panel mounting block for aluminium structures, Support block



T type timing belt per metre, T10 Steel cored polyurethane

Miniature motorised actuator 4A, 4 ampers

Stainless/Polymer pillow block bearing, Polymer and stainless

Single housed bearing assembly, Bearing secured with circlips

Deep groove ball bearing, Stainless steel

Hi-Klik TM indent hinge, Hi-Klik™ - Detent hinge

Complementary products