Positioning sleeve for indexing pin New

SDC For pin Ø4 to Ø12

- ***Suitable for indexing pins and indexing locks***
- *Low wear due to hardened cone*
- *Materials:*
  Hardened and burnished steel
  Hardened stainless steel



Accessories

- *Compatible with the **SDA** and **SDB** locating bolt support bracket **(tome 1 p.68-69)***
- *Compatible with the HPC range of indexing pins.*



Application example



DISCOUNTS

Qty	1+	6+	20+
Disc.	Price	-10%	On request

Part number	ØD	ØD3 (+0,1)	ØD2	ØD4 (-0,05)	L1	L2	L3	L4	L5 (+0,5)	For pin diam	SW	Weight (g)	Price each 1 to 5
Steel													
SDC12F-4	M12X1,5	4,2	24	12	10	16	11	5	1,5	4	4	17	9,49 €
SDC12F-5	M12X1,5	5,2	24	12	10	16	11	5	1,5	5	4	16	9,55 €
SDC12F-6	M12X1,5	6,2	24	12	10	16	11	5	1,5	6	4	16	9,55 €
SDC16F-8	M16X1,5	8,2	32	16	12	20	13	7	1,5	8	6	32	11,46 €
SDC16F-10	M16X1,5	10,2	32	16	12	20	13	7	1,5	10	6	33	11,38 €
SDC16F-12	M16X1,5	12,2	32	16	12	20	13	7	1,5	12	6	33	11,46 €
Stainless steel													
SDC12F-4/SS	M12X1,5	4,2	24	12	10	16	11	5	1,5	4	4	17	12,75 €
SDC12F-5/SS	M12X1,5	5,2	24	12	10	16	11	5	1,5	5	4	16	12,75 €
SDC12F-6/SS	M12X1,5	6,2	24	12	10	16	11	5	1,5	6	4	16	12,75 €
SDC16F-8/SS	M16X1,5	8,2	32	16	12	20	13	7	1,5	8	6	32	18,53 €
SDC16F-10/SS	M16X1,5	10,2	32	16	12	20	13	7	1,5	10	6	33	18,53 €
SDC16F-12/SS	M16X1,5	12,2	32	16	12	20	13	7	1,5	12	6	33	18,53 €

Dimensions in mm

Our other products



Connecting kits, XZ linking kit



Doorstop for aluminium profile, Swing door stop



Plastic slotted spring plunger with ball tip, Plastic body + stainle...



Accessories, Clamping lever



Cylindrical holding magnets, Cylindrical holding magnet



Bi-directional leadscrew, Bi-directional - 1 thread



Adjustable latch clamp with strike plate, Stroke from 106,7mm to 121...



Parallel axis helical gear, Steel 20NCD2



Diabolo shaped elasto mount, Steel



Spur gear - precision range, Case hardened steel 20NCD2



Lifting sling, 2 eyelinks



Chain sprocket - Stainless steel, 9.525 (DIN 06B-1)

Complementary products



Positioning sleeve for indexing pin, For pin Ø4 to Ø12



Locking bolt support bracket, Mounting holes parallel to locating bolt



Locking bolt support bracket, Mounting holes at 90° to locating bolt



Indexing plunger, steel class 5.8