- ***For guiding profile***
- *Materials:*
  Body: stainless steel 304
  Nut/washer: stainless steel

stainless steel



Typical application





DISCOUNTS

Qty.	1+	10+	20+
Disc.	List	-5%	On request

Part number	ØD	For Axis	H	W	Weight (kg)	Price each 1 to 9
TOL12-40/SS	12,5	APB12	40	55	0,28	27,48 €
TOL12-60/SS	12,5	APB12	60	75	0,38	33,57 €
TOL12-90/SS	12,5	APB12	90	105	0,55	36,86 €
TOL12-130/SS	12,5	APB12	130	145	0,77	49,17 €
TOL14-40/SS	14,5	APB14	40	56	0,28	49,17 €
TOL14-60/SS	14,5	APB14	60	76	0,38	27,48 €
TOL14-90/SS	14,5	APB14	90	106	0,55	31,79 €
TOL14-130/SS	14,5	APB14	130	146	0,77	35,09 €
TOL16-40/SS	16,5	APB16	40	57	0,28	49,17 €
TOL16-60/SS	16,5	APB16	60	77	0,38	27,48 €
TOL16-90/SS	16,5	APB16	90	107	0,55	36,86 €
TOL16-130/SS	16,5	APB16	130	147	0,77	49,17 €

**Depending on availability - Dimensions in mm*

Our other products



ETQ

Magnetic label holder for aluminium profile, Label holder



BH01

Single housed bearing, Bearing fitted with adhesive



MLY

Bow shackle with eye bolt, Steel



RDS

Safety washer Hygienic Usit®, Stainless steel



PSG125S

Spur gear - precision range, Stainless steel 316



NK40

Drylin®N miniature guiding system, Witdh 40 mm



DER80

Stainless steel AC asynchronous motor 0.55 - 0.75kW, 0.55 to 0.75kW



DCG

Suction cup, 2.5 bellows, nitrile



MSP23

Masterplate® glueable insert Ø23,



BPLE

Ball transfer unit push fit, Light



HRV

V- rail guidance Simple Select®



DB

Steel bevel gear, 2:1

Complementary products



TOC

Short swivel head, Short



APB_F

Adjusting rod for clamp - Male, Threaded



APB_T

Adjusting rod for clamp - Female, Bored



RAG

Roller guide,