Round spur rack

Steel

Module 1.0–4.0

- ***Pressure angle 20°***
- *Diameter tolerance h11*
- *Material:*
  drawn steel A60







DISCOUNTS

Qty	1+	3+	6+
Disc.	List	-10%	On request

Part number	Module	h (mm)	ØD (mm)	L (mm)	Stock*	Price each 1 to 2
TRM1-1000	1	9,00	10	999	✔	96,77 €
TRM1.5-1000	1,5	13,50	15	999	✔	131,68 €
TRM2-1000	2	18,00	20	999	✔	132,83 €
TRM2.5-1000	2,5	22,50	25	997	✔	176,48 €
TRM3-1000	3	27,00	30	999	✔	168,88 €
TRM4-1000	4	36,00	40	1005	✔	204,94 €

**Depending on availability - Dimensions in mm*

Our other products

YG1

HEAVY DUTY spur gear, Steel 35NCD6

HLA24

Right angle spiro bevel gearbox, Up to 78Nm

TM_CTM_CTF

Suction cup threaded insert, Insert for suction cup - Tread click-in

ACL-APB

Closing system for aluminium profile, Magnetic door stop

CAP881

Side flexing slim slat top chain stainless steel, Narrow range 881

GGB

Female wing knob, With blind thread

TK

Topball self-aligning linear bearing, Topball self-aligning

PRF_ROUL_F

Castor for aluminium profile, With brake

VRBS

Folding lifting ring for welding, Folding - for welding

DGSI

Female rod ends, Steel / steel - Economy range

PSG2S

Spur gear - precision range, Stainless steel 303

S2O

Short housing for open linear bearing, Opened - slim

Complementary products


TR

Spur round rack, Stainless steel - module 0,25-1,5

TRMSS

Spur round rack, Stainless steel - module 1-5

G1

Steel spur gear, Steel 20NCD2