


- Manchon mâle/femelle
- Matières :
Acier zingué
Inox
- Conditionnés par lot



REMISES

Qté	1+	5+	20+	50+
Rem.	Prix	-5%	-10%	Sur demande

Références	ØF	ØT	S	L	X	Y	Qté par lot	Prix Uni. 1 à 4
Acier								
MHX6-8-19/B	M6	M8	13	19	7	7	20	15,12 €
MHX8-6-20/B	M8	M6	13	20	8	7	20	15,12 €
MHX8-10-23/B	M8	M10	13	23	8	9	20	15,12 €
MHX8-12-23/B	M8	M12	17	23	8	8	20	21,26 €
MHX10-6-21/B	M10	M6	13	21	8	7	20	15,12 €
MHX10-8-21/B	M10	M8	13	21	8	7	20	15,12 €
MHX10-12-25/B	M10	M12	17	25	10	8	20	21,26 €
MHX10-16-32/B	M10	M16	24	32	10	13	20	54,97 €
MHX12-8-23/B	M12	M8	13	23	10	7	20	15,12 €
MHX12-10-23/B	M12	M10	13	23	10	8	20	15,12 €
MHX12-16-32/B	M12	M16	24	32	10	13	20	54,97 €
MHX16-10-32/B	M16	M10	19	32	14	9	20	32,99 €
MHX16-12-32/B	M16	M12	19	32	14	10	20	32,99 €
Inox								
MHX6-8-19/SS/B	M6	M8	13	19	7	7	20	64,55 €
MHX8-6-20/SS/B	M8	M6	13	20	8	7	20	64,55 €
MHX8-10-23/SS/B	M8	M10	13	23	8	9	20	64,55 €
MHX8-12-23/SS/B	M8	M12	17	23	8	8	20	83,53 €
MHX10-6-21/SS/B	M10	M6	13	21	8	7	20	64,55 €
MHX10-8-21/SS/B	M10	M8	13	21	8	7	20	64,55 €
MHX10-12-25/SS/B	M10	M12	17	25	10	8	20	83,53 €
MHX10-16-32/SS/B	M10	M16	24	32	10	13	20	135,18 €
MHX12-8-23/SS/B	M12	M8	13	23	10	7	20	64,55 €
MHX12-10-23/SS/B	M12	M10	13	23	10	8	20	64,55 €
MHX12-16-32/SS/B	M12	M16	24	32	10	13	20	135,18 €
MHX16-10-32/SS/B	M16	M10	19	32	14	9	20	95,78 €
MHX16-12-32/SS/B	M16	M12	19	32	14	10	20	95,78 €

Dimensions en mm

0 825 88 6000
Service 0,15 € / min
+ prix appel