

Small 6 lobe female handle



GLB

Technopolymer, with brass insert

with brass
or stainless
steel insert

- Small 6 lobe female handle with a female tapped insert (blind or fully threaded)


- Material :

Matt black polyamide with
brass or stainless steel insert



Info.

- Not sold individually,
please contact us
for details



DISCOUNTS

Qty	1+	10+	20+	50+	100+	200+
Disc.	List	-5%	-10%	-15%	-20%	On request

Part number									Stock* Steel	Price each 1 to 9		
Steel	S/steel	A	B	C	F	ØD	E	Ød		Steel	Steel	S/steel
Handle, blind thread												
GLB30-M6	GLB30-M6/SS	30	14	24	15	M6	13	-	✓	2,41 €	6,07 €	
GLB30-M8	-	30	14	24	15	M8	13	-	✓	2,55 €	-	
GLB40-M6	GLB40-M6/SS	40	16	28	18	M6	13	-	✓	2,83 €	6,86 €	
GLB40-M8	GLB40-M8/SS	40	16	28	18	M8	13	-	✓	2,83 €	6,90 €	
GLB50-M8	GLB50-M8/SS	50	18	32	20	M8	15	-	✓	3,32 €	8,70 €	
GLB50-M10	GLB50-M10/SS	50	18	32	20	M10	16	-	✓	3,56 €	8,70 €	
GLB60-M12	GLB60-M12/SS	60	20	36	22	M12	18	-	✓	4,79 €	14,06 €	
GLB70-M12	-	70	23	40	24	M12	18	-	✓	5,99 €	-	
GLB70-M14	-	70	23	40	24	M14	20	-	✓	7,47 €	-	
GLB70-M16	-	70	23	40	24	M16	20	-	✓	7,99 €	-	
Handle fully threaded												
GLB30-M6/FP	GLB30-M6/FP/SS	30	14	24	15	M6	11	8	✓	2,98 €	10,27 €	
GLB30-M8/FP	-	30	14	24	15	M8	11	10	✓	3,27 €	-	
GLB40-M6/FP	GLB40-M6/FP/SS	40	16	28	18	M6	15	7	✓	3,65 €	11,42 €	
GLB40-M8/FP	GLB40-M8/FP/SS	40	16	28	18	M8	15	11	✓	3,90 €	12,16 €	
GLB50-M8/FP	GLB50-M8/FP/SS	50	18	32	20	M8	18	11	✓	4,70 €	13,33 €	
GLB50-M10/FP	GLB50-M10/FP/SS	50	18	32	20	M10	18	11	✓	4,83 €	14,06 €	
GLB60-M12/FP	-	60	20	36	22	M12	25	13	✓	6,46 €	-	
GLB70-M12/FP	-	70	23	40	24	M12	25	14	✓	8,04 €	-	
GLB70-M14/FP	-	70	23	40	24	M14	25	15	✓	9,82 €	-	
GLB70-M16/FP	-	70	23	40	24	M16	25	17	✓	11,43 €	-	

*Depending on availability - Dimensions in mm