


KSM 1 trapezoidal right or left-hand thread KSM_{LH}

- Right or left-hand thread
- Thread conforms to NFE 03.616
- Machined nut
- Thread tolerance: 7H
- Material: Steel 11SMnPb37



Accessories

- LFM steel leadscrew or LSM stainless steel leadscrew

DISCOUNTS A

Qty	1+	10+	20+	40+
Disc.	List	-30%	-40%	On request

DISCOUNTS B

Qty	1+	5+	10+
Disc.	List	-5%	On request

Part number	Ød	Pitch P	D	C	Weight (kg)	Stock*	Price each	
							1 to 9	20 to 39**
Right-hand thread								
KSM102	10	2	22	15	0,035	✓	A 3,76 €	A 2,25 €
KSM123	12	3	26	18	0,055	✓	A 4,07 €	A 2,45 €
KSM143	14	3	30	21	0,090	✓	A 5,09 €	A 3,06 €
KSM164	16	4	36	24	0,155	✓	A 6,67 €	A 4,00 €
KSM184	18	4	40	27	0,215	✓	A 7,57 €	A 4,55 €
KSM204	20	4	45	30	0,305	✓	A 9,47 €	A 5,68 €
KSM225	22	5	45	33	0,322	✓	A 10,25 €	A 6,15 €
KSM245	24	5	50	36	0,440	✓	A 12,04 €	A 7,23 €
KSM285	28	5	60	42	0,740	✓	A 18,99 €	A 11,40 €
KSM306	30	6	60	45	0,765	✓	A 19,84 €	A 11,91 €
KSM326	32	6	60	48	0,790	-	A 20,75 €	A 12,44 €
KSM366	36	6	75	54	1,470	-	B 25,67 €	B On request
KSM407	40	7	80	60	1,830	✓	B 30,76 €	B On request
KSM447	44	7	80	66	1,890	-	B 40,41 €	B On request
KSM508	50	8	90	75	2,695	-	B 86,91 €	B On request
KSM609	60	9	100	90	3,865	-	B 107,84 €	B On request
KSM7010	70	10	110	100	5,115	-	B 133,58 €	B On request
KSM8010	80	10	120	110	6,000	-	B 173,83 €	B On request
Left-hand thread								
KSM102/LH	10	2	22	15	0,035	-	A 7,53 €	A 4,52 €
KSM123/LH	12	3	26	18	0,055	✓	A 6,64 €	A 3,98 €
KSM143/LH	14	3	30	21	0,090	✓	A 11,42 €	A 6,85 €
KSM164/LH	16	4	36	24	0,155	✓	A 9,20 €	A 5,52 €
KSM184/LH	18	4	40	27	0,215	-	A 8,45 €	A 5,08 €
KSM204/LH	20	4	45	30	0,305	✓	A 10,32 €	A 6,19 €
KSM225/LH	22	5	45	33	0,322	-	A 16,64 €	A 9,98 €
KSM245/LH	24	5	50	36	0,440	-	A 15,80 €	A 9,48 €
KSM285/LH	28	5	60	42	0,740	✓	A 25,10 €	A 15,06 €
KSM306/LH	30	6	60	45	0,765	-	A 24,44 €	A 14,67 €
KSM326/LH	32	6	60	48	0,790	-	A 27,36 €	A 16,42 €
KSM366/LH	36	6	75	54	1,470	-	B 28,14 €	B On request
KSM407/LH	40	7	80	60	1,830	-	B 34,91 €	B On request
KSM447/LH	44	7	80	66	1,890	-	B 46,86 €	B On request
KSM508/LH	50	8	90	75	2,695	-	B 154,95 €	B On request
KSM609/LH	60	9	100	90	3,865	-	B 175,81 €	B On request
KSM7010/LH	70	10	110	100	5,115	-	B 201,50 €	B On request
KSM8010/LH	80	10	120	100	6,000	-	B 230,23 €	B On request

*Depending on availability - Dimensions in mm

** refer to discounts