

Digital position indicator

Size XS Stock

OP3DX
OP3SX

4 digit display

Stainless steel version available on request


- 4 digit display (9999) with red digits for tenths/hundredths
- Shaft driven position indicator
- Displays linear or angular movement by use of mechanism driven by a rotating shaft
- Nonflammable polycarbonate case Protection IP64
- Max. temperature 80°C
- Colour: orange
- Height of digits: 5mm
- Standard bore for shaft 14H7, smaller bores will require use of reducing sleeve



Gasket supplied



Clamp spacer OP3-BE




Options

- Version with stainless steel parts available
- Anti-rotation pin $\varnothing 6$ mm





Assembly

- Insert the indicator on to the shaft ensuring that the torque pin is inserted into the 5mm hole that should have been provided. Reset the display to zero and secure the fixing screw.

Shaft hole max. $\varnothing 14$



OP3DX OP3SX



DISCOUNTS

Qty	1+	5+	+10
Disc.	List	-15%	On request

Part number	View	Pitch (mm)	Display after one turn (mm)	Max. speed (rpm)	Counting direction	Stock*	Price each 1 to 4
OP3-A10-DX	A	1	001 0	300	clockwise	✓	66,11 €
OP3-A20-DX	A	2	002 0	300	clockwise	✓	66,11 €
OP3-A40-DX	A	4	004 0	250	clockwise	✓	66,11 €
OP3-A50-DX	A	5	005 0	200	clockwise	✓	66,11 €
OP3-A100-DX	A	10	010 0	150	clockwise	✓	66,11 €
OP3-B10-DX	B	1	001 0	300	clockwise	✓	66,11 €
OP3-B20-DX	B	2	002 0	300	clockwise	✓	66,11 €
OP3-B40-DX	B	4	004 0	250	clockwise	✓	66,11 €
OP3-B50-DX	B	5	005 0	200	clockwise	-	66,11 €
OP3-B100-DX	B	10	010 0	150	clockwise	-	66,11 €
OP3-A10-SX	A	1	001 0	300	anticlockwise	✓	66,11 €
OP3-A20-SX	A	2	002 0	300	anticlockwise	-	66,11 €
OP3-A40-SX	A	4	004 0	250	anticlockwise	✓	66,11 €
OP3-A50-SX	A	5	005 0	200	anticlockwise	-	66,11 €
OP3-A100-SX	A	10	010 0	150	anticlockwise	✓	66,11 €
OP3-B10-SX	B	1	001 0	300	anticlockwise	-	66,11 €
OP3-B20-SX	B	2	002 0	300	anticlockwise	-	66,11 €
OP3-B40-SX	B	4	004 0	250	anticlockwise	-	66,11 €
OP3-B50-SX	B	5	005 0	200	anticlockwise	-	66,11 €
OP3-B100-SX	B	10	010 0	150	anticlockwise	-	66,11 €

*Depending on availability - Dimensions in mm