Hook for latch

Stock Sta Ste

ACZB
ACSS

15mm wide versions

- **Hook fastening**
- Material: White zinc steel or stainless steel 303


Selection

- Choose your own hook/latch combination by simply verifying the interior width of the ring and selecting a hook with a smaller width


Info.

- **Not sold individually, please contact us for details**







AC101



AC106-ZB



AC109-ZB



AC111-ZB

DISCOUNTS

Qty	1+	51+	101+	250+	400+	500+
Disc.	List	-10%	-15%	-20%	-25%	On request

Part number	Suitable for latch	Weight (g)	Stock*	Price each 1 to 50
Steel				
AC101-ZB	GE14-ZB	4,7	✔	0,59 €
AC106-ZB	GE14-ZB	5,2	✔	0,95 €
AC109-ZB	GE14-ZB	6,2	✔	0,82 €
AC111-ZB	GE14-ZB	6,8	✔	1,28 €
Stainless steel				
AC101-SS	GE1006-SS	4,7	✔	0,59 €

*Subject to availability - Dimensions in mm

Size XS Stock Sta Ste

Hook for latch

Widths: 12, 13, 18 and 20mm

ACZB
ACSS

- **Hook fastening**
- Material: White zinc steel or stainless steel 303

steel or stainless steel




Selection


- Choose your own hook/latch combination by simply verifying the interior width of the ring and selecting a hook with a smaller width

Info.


- **Not sold individually, please contact us for details**




AC122



AC103-ZB



AC118



AC121

DISCOUNTS

Qty	1+	51+	101+	250+	400+	500+
Disc.	List	-10%	-15%	-20%	-25%	On request


Part number	Suitable for latch	Weight (g)	Stock*	Price each 1 to 50
Steel				
AC103-ZB	-	3,4	-	0,27 €
AC118-ZB	GE18-ZB	1,5	✔	0,20 €
AC121-ZB	GE5-ZB	9,4	✔	0,44 €
AC122-ZB	GP22-ZB and GP23-ZB	1,9	✔	0,82 €
Stainless steel				
AC118-SS	GE18-SS	1,5	✔	0,37 €
AC121-SS	GE5-SS	9,4	✔	1,18 €
AC122-SS	GP22-SS and GP23-SS	1,9	✔	2,29 €

*Subject to availability - Dimensions in mm

Our other products


AT10-32ECO

AT type timing pulley, Economy range - AT10 aluminium


TC1rp

Automatic chain tensioner, With 180° guide


BCH_SS

Mushroom headed button, M3 to M8


PP60

Worm and wheel gear reducer, from 17.80 to 34 Nm


ZBconique

Machined plastic bevel gear, 1:1


PGNT

Thermoplastic T handle, With threaded insert


VB

Small 6 lobe threaded handle - female, Duroplast - Stainless steel


KON

Conical elasto buffer, Stainless steel


CLM

Male clevis end, Stainless steel short


BRI

Panel holder, Panel holder


FB_ECO

Eco. range steel bevel gear, 4:1


S_ZZ

Deep groove ball bearing, Stainless steel

Complementary products


GP

Spring loaded toggle latch, Standard


GP

Spring loaded toggle latch, With padlock-holder