

Right angled bracket for aluminium profiles

ACLEPP

Connecting bracket for connecting 2 profiles

- To join 2 profiles at 90°
- Material
Anodised aluminium
For use with single slot profiles

Advantages

- Suitable for use with PRF aluminium profiles

Info


- No mounting screws supplied





ACL-EPP2-4545




ACL-EPP4-4590



ACL-EPP2- 4545



ACL-EPP4-4590



 **INCREASED STOCK**

DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Version	L	B	H	A	C	ØD	Weight (g)	Stock*	Price each 1 to 49
ACL-EPP2-4545	2 trous	45	41	6	-	22,5	9	55	✓	2,84 €
ACL-EPP4-4590	4 trous	90	41	6	45	22,5	9	112	✓	5,66 €

*Depending on availability - Dimensions in mm

Right angled bracket for aluminium profiles

Connecting bracket for connecting 2 profiles

ACLEPP

- To join 2 profiles at 90°
- Material
Anodised aluminium
For use with dual slot profilest

Advantages

- Suitable for use with PRF4590 aluminium profiles

Info



- No mounting screws supplied





ACL-EPP4-9045



ACL-EPP8-9090



ACL-EPP4-9045



ACL-EPP8-9090



DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	Version	L	B	H	A	C	ØD	Weight (g)	Stock*	Price each 1 to 49
ACL-EPP4-9045	4 trous	45	86	6	45	22,5	9	112	✓	5,85 €
ACL-EPP8-9090	8 trous	90	86	6	45	22,5	9	235	✓	10,50 €

*Depending on availability - Dimensions in mm

Our other products



VAP

Magnetic stud with central hole, With central hole



CQA30

Adjustment slide-system miniature, 30



BOX-TOR-H

Box set of Nitrile O-rings in nitrile, 3.00 x 2.00mm to 45.20 x 4.00



PP35

Worm and wheel gear reducer, from 2.20 to 4.10 Nm



BOX-CS

Hose clamp, Box set of steel hose clamps



PRFSRAD

Dual lock for aluminium profile, Quick fitting, self locking door du...



SBF

Sealed flange bearing unit for Food Industry, cover



PRF-P

Aluminium profile feet support, For feet or casters



NSA

Adjustable clamp, Articulated



BVR

Adjustable screw stop, Steel



BMM

Knurled knob - male, Knurled



DIV_SS

Stainless steel locking bolt, With grip - Stainless steel

Complementary products



PRF4545

Standard aluminium profile, 45 x 45 mm