

Aluminium

Pitch
AT10

For 25mm belts





- For use with AT10 belts
- Pitch 10mm
- Material:
Aluminium

Accessories

- AT10 belts
- GTC tension rollers

Info

- *Pilot bore given as indication, may vary between batches.
- Will require re-machining by customer
- **We are unable to modify this product**



Economy range

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-12%	On request

Part number	No of teeth	ØP PDC	ØD external	ØE flange	ØM	F	L	Pilot bore		Price each 1 to 5
								not guaranteed	ØA*	
15AT10-25/ECO	15	47,75	45,90	51	32	30	40	8		10,52 €
16AT10-25/ECO	16	50,93	49,05	54	35	30	40	8		11,78 €
18AT10-25/ECO	18	57,29	55,45	60	40	30	40	8		14,08 €
19AT10-25/ECO	19	60,48	58,60	66,5	44	30	40	8		15,75 €
20AT10-25/ECO	20	63,66	61,80	66,5	46	30	40	8		16,88 €
22AT10-25/ECO	22	70,03	68,15	75	52	30	40	8		21,12 €
24AT10-25/ECO	24	76,39	74,55	83	58	30	40	8		23,74 €
25AT10-25/ECO	25	79,58	77,70	83	60	30	40	8		23,98 €
26AT10-25/ECO	26	82,76	80,90	87	60	30	40	8		26,60 €
27AT10-25/ECO	27	85,95	84,10	91	60	30	40	8		29,29 €
28AT10-25/ECO	28	89,12	87,25	93	60	30	40	8		29,35 €
30AT10-25/ECO	30	95,49	93,65	102	60	30	40	8		35,19 €
32AT10-25/ECO	32	101,86	100,00	106	65	30	40	10		38,22 €
36AT10-25/ECO	36	114,59	112,75	119	70	30	40	10		45,18 €
40AT10-25/ECO	40	127,32	125,45	131	80	30	40	10		56,20 €
44AT10-25/ECO	44	140,05	138,20	-	88	30	40	10		71,51 €
48AT10-25/ECO	48	152,78	150,95	-	95	30	40	16		76,80 €
60AT10-25/ECO	60	190,98	189,10	-	110	30	40	16		126,64 €


Dimensions in mm

Our other products



AXTR

Axle for tensioner pulley, Shaft



PF15

Worm and wheel gear reducer, up to 3,75 Nm



DOMI50

Connecting kits, XZ linking kit



GMK17_BR

Clamp for guiding profile, Rounded only - single



GBSz

Cylindrical ballscrew nut, Cylindrical leadscrew nut



DPAR_DKON

Conical elasto buffer, Steel




H2

Crossed helical gear crossed axis at 90°, Steel 20NCD2



CFS

Miniature cam follower, Miniature



ACLBT5

Closing system for aluminium profile, 90°



CHAK

Hi-Klik TM indent hinge, Hi-Klik™ -



EKGS

Backlash free coupling Gerwah®,



GG2

Ground spur gear, Heat treated steel

Complementary products



GTC

Belt tensioner, For standard applications



AT10courrie

AT type timing belt, AT10 Steel cored polyurethane



AT10-BAR

AT type tooth bar stock, AT10



AT5M AT10M

AT type timing belt per metre, AT10 Steel cored polyurethane