



- For use with AT10 belts
- Pitch 10mm
- Material:
Aluminium

Accessories

- AT10 belts
- GTC tension rollers

Info

- *Pilot bore given as indication, may vary between batches.
- Will require re-machining by customer
- We are unable to modify this product



Economy range

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-12%	On request

Part number	No of teeth	Ø PCD	ØD external	ØE flange	ØM	F	L	Pilot bore	Price each
								not guaranteed	
									1 to 5
18AT10-50/ECO	18	57,29	55,45	60	40	56	66	10	20,66 €
19AT10-50/ECO	19	60,48	58,60	66,5	44	56	66	10	23,13 €
20AT10-50/ECO	20	63,66	61,80	66,5	46	56	66	12	24,90 €
22AT10-50/ECO	22	70,03	68,15	75	52	56	66	12	31,59 €
24AT10-50/ECO	24	76,39	74,55	83	58	56	66	12	35,60 €
25AT10-50/ECO	25	79,58	77,70	83	60	56	66	12	35,94 €
26AT10-50/ECO	26	82,76	80,90	87	60	56	66	12	39,98 €
27AT10-50/ECO	27	85,95	84,10	91	60	56	66	12	44,02 €
28AT10-50/ECO	28	89,12	87,25	93	60	56	66	12	44,33 €
30AT10-50/ECO	30	95,49	93,65	102	60	56	66	12	52,98 €
32AT10-50/ECO	32	101,86	100,00	106	65	56	66	12	58,36 €
36AT10-50/ECO	36	114,59	112,75	119	70	56	66	16	69,14 €
40AT10-50/ECO	40	127,32	125,45	131	80	56	66	16	86,38 €
44AT10-50/ECO	44	140,05	138,20	-	88	56	66	16	110,56 €
48AT10-50/ECO	48	152,78	150,95	-	95	56	66	16	119,08 €
60AT10-50/ECO	60	190,98	189,10	-	110	56	66	16	194,88 €

Dimensions in mm

Our other products



HRV

V- rail guidance
Simple Select®
system, Rail with
carriage



BS2

Panamech, Multi-
Beam, Aluminium -
with set screw



RTTss

Locking assembly,
Medium/high torque



ETP

Modular handle for
aluminium profile,
Modular handle




CHA1056_U4

Screw-in hinge,
Section 40X40



CAP882

Flexible slat top chain
acetabular, Large range
882



PM4

Worm and wheel set,
Machined plastic
(delrin)



RPCpl

Swivel castor with
double brake, Steel -
Polyamide




ZG0

Plastic spur gear,
Machined plastic
(delrin)



PLM-16A

Magnetic stud with
threaded hole, With
threaded hole



AC

Strike for toggle latch,
15mm



ACLBDB

Closing mechanism
for aluminium profile,
Dual ball catch

Complementary products



GTC

Belt tensioner, For
standard applications



AT10courroie

AT type timing belt,
AT10 Steel cored
polyurethane



AT10-BAR

AT type tooth bar
stock, AT10



AT5M AT10M

AT type timing belt
per metre, AT10 Steel
cored polyurethane