

AT-type timing pulley



Pitch AT5

Aluminium



For 10mm belts



- For use with AT5 belts
- Pitch 5mm
- Material:
Aluminium

Accessories

- AT5 belts
- GTC tension rollers

Info

- *Pilot bore size given as a indication, may vary between batches
- Will require re-machining by customer
- **We are unable to modify this product**



Economy range

DISCOUNTS

Qty	1+	6+	20+
Disc.	List	-12%	On request

Part number	No of teeth	ØP PCD	ØD external	ØE flange	ØM	F	L	Pilot bore not guaranteed	
								ØA*	Price each 1 to 5
12AT5-10/ECO	12	19,10	17,85	23	11	15	21	-	2,95 €
14AT5-10/ECO	14	22,29	21,05	25	13	15	21	-	3,24 €
15AT5-10/ECO	15	23,88	22,65	28	16	15	21	6	3,47 €
16AT5-10/ECO	16	25,47	24,20	32	18	15	21	6	3,84 €
18AT5-10/ECO	18	28,65	27,40	32	20	15	21	6	4,06 €
19AT5-10/ECO	19	30,25	29,00	36	22	15	21	6	4,49 €
20AT5-10/ECO	20	31,83	30,60	36	23	15	21	6	4,74 €
22AT5-10/ECO	22	35,02	33,85	38	24	15	21	6	5,38 €
24AT5-10/ECO	24	38,21	37,00	42	26	15	21	6	5,76 €
25AT5-10/ECO	25	39,80	38,60	44	26	15	21	6	6,13 €
26AT5-10/ECO	26	41,39	40,20	44	26	15	21	6	6,66 €
27AT5-10/ECO	27	42,98	41,80	48	30	15	21	8	6,88 €
28AT5-10/ECO	28	44,58	43,35	48	32	15	21	8	7,34 €
30AT5-10/ECO	30	47,76	46,55	51	34	15	21	8	7,85 €
32AT5-10/ECO	32	50,94	49,70	54	38	15	21	8	8,84 €
36AT5-10/ECO	36	57,31	56,05	64	38	15	21	8	10,24 €
40AT5-10/ECO	40	63,66	62,45	66,5	40	15	21	8	11,63 €
42AT5-10/ECO	42	66,86	65,60	70	40	15	21	8	12,54 €
44AT5-10/ECO	44	70,05	68,80	-	45	15	21	8	12,58 €
48AT5-10/ECO	48	76,42	75,15	-	50	15	21	8	14,16 €
60AT5-10/ECO	60	95,52	94,25	-	65	15	21	8	21,12 €

Dimensions in mm

Our other products



CHAFR-MINI
Miniature friction
hinge, Friction



LBE
Miniature closed
linear bearing,
Miniature




ABL100005
Antistatic brush,
Standard




CHASb28
Roll of hinge without
pin, Plastic hinge



DB
Steel bevel gear, 2:1



PM4
Worm and wheel set,
Machined plastic
(delrin)



PRF45 GOU
Chute profile,
Accessories



SHSS
Shoulder screw
stainless steel 416,
Pre-treated 416
stainless steel



WS16
Drylin® W rail, Rail



DILC
Indexing plunger with
cam, with cam



MAC
Carabiner DIN5299
steel, Steel



UGCG
Actuator guide kit,
Long housing

Complementary products



GTC
Belt tensioner, For
standard applications



AT5courroie
AT type timing belt,
AT5 Steel cored
polyurethane



AT5-BAR
AT type tooth bar
stock, AT5



AT5M AT10M
AT type timing belt
per metre, AT5 Steel
cored polyurethane