


- Bar stock to be cut to length by the customer
- The overall length is the same as the maximum length
- Material : Aluminium suitable for hard anodic oxidation
- Finish : Supplied not-treated



Info.

- We are unable to modify this product



DISCOUNTS

Qty	1+	2+	4+
Disc. List	-20%		On request

Part number	Z Teeth	ØD External	Length of teeth L _D	Total length L _T	Price each
15AT10-BAR	15	45,90	160	160	30,93 €
16AT10-BAR	16	49,14	160	160	35,15 €
18AT10-BAR	18	55,45	160	160	42,21 €
19AT10-BAR	19	58,65	160	160	47,31 €
20AT10-BAR	20	61,80	160	160	51,41 €
21AT10-BAR	21	65,00	160	160	55,66 €
22AT10-BAR	22	68,20	160	160	65,98 €
23AT10-BAR	23	71,35	160	160	66,28 €
24AT10-BAR	24	74,55	160	160	74,32 €
25AT10-BAR	25	77,75	160	160	74,88 €
26AT10-BAR	26	80,90	160	160	83,42 €
28AT10-BAR	28	87,25	160	160	92,83 €
30AT10-BAR	30	93,65	160	160	112,55 €
32AT10-BAR	32	100,00	160	160	123,56 €
34AT10-BAR	34	106,40	160	160	135,20 €
36AT10-BAR	36	112,75	160	160	148,54 €
38AT10-BAR	38	119,10	160	160	172,13 €
40AT10-BAR	40	125,45	160	160	185,77 €
42AT10-BAR	42	131,85	160	160	210,24 €
44AT10-BAR	44	138,20	160	160	230,17 €
46AT10-BAR	46	144,55	160	160	247,96 €
48AT10-BAR	48	150,95	160	160	262,35 €
52AT10-BAR	52	163,65	160	160	317,75 €
56AT10-BAR	56	176,40	160	160	365,45 €
60AT10-BAR	60	189,15	160	160	432,22 €

Dimensions in mm


Our other products



Articulated fixable foot with pressed base Ø100, Ø 100



Knurled knob - male, Knurled



Carrying handle, back-plated



Motor-gearbox 12V and 24V DC, from 4 to 9 Nm



Roller guide,



Ground spur gear, Heat treated steel



Worm and wheel set, Non hardened steel



Dual-thread screw wood/metal, Steel



60mm rubber wheel for conveyor belt, Rubber



T type timing pulley, Economy range - T10 moulded plastic



Shock Absorber - stop collar, Universal flange



Fixed castor with plate, Steel - grey rubber

Complementary products



AT type tooth bar stock, AT5



AT type timing pulley, Economy range - AT10 aluminium



AT type timing pulley, Economy range - AT10 aluminium



AT type timing pulley, Economy range - AT10 aluminium