





- Low cost clip
- Made from zinc plated steel
- Supplied by the packet

### Advantages

- Manual assembly/disassembly



Typical applications

### DISCOUNTS

Qty	1+	5+	10+	21+
Disc. List	-10%	-20%	On request	

Part number	ØD	L	B	For shaft	Weight per 100 (kg)	Quantity per pack	Stock*	Price each 1 to 4
BETA-2/B	2	53	12	9-11	0,5	100	✓	8,01 €
BETA-2.5/B	2,5	52	10	11-13	0,6	100	✓	10,06 €
BETA-3/B	3	66	15	13-17	0,9	100	✓	12,95 €
BETA-4/B	4	83	22	17-20	2,3	100	✓	24,84 €
BETA-4.5/B	4,5	68	24	20-23	2,5	100	✓	33,03 €
BETA-5/B	5	100	23	23-26	3,9	100	✓	42,28 €
BETA-6/B	6	105	26	26-30	6,0	50	✓	29,50 €
BETA-7/B	7	125	26	30-34	9,1	25	-	41,30 €
BETA-8/B	8	142	29	34-45	13,6	25	✓	51,68 €

\*Depending on availability - Dimensions in mm


- Low cost clip
- Made from stainless steel AISI 304
- Supplied by the packet

### Advantages

- Manual assembly/disassembly



stainless steel



Typical applications

### DISCOUNTS

Qty	1+	5+	10+	15+
Disc.	List	-10%	-20%	On request

Part number	ØD	L	B	Weight per 100 (kg)	Quantity per pack	Price each 1 to 4
BETA-2/SS/B	2	53	12	0,32	100	35,11 €
BETA-3/SS/B	3	66	15	0,88	50	31,33 €
BETA-4/SS/B	4	83	22	1,49	25	32,09 €
BETA-5/SS/B	5	100	23	3,62	20	43,71 €
BETA-6/SS/B	6	105	26	5,56	10	34,21 €

\*Depending on availability - Dimensions in mm

## Our other products



BABtss

303 Stainless steel ball pin, 303 Stainless steel



NJM

Multiple junction clamp, Multiple



DER90

Stainless steel AC asynchronous motor 1.1 - 1.5kW, 1.1 to 1.5kW



RHTtcss

High Temperature Castor, up to 200kg



SH1

Parallel axis helical gear, Machined plastic (delrin)



PRS100

Stainless steel articulated foot Ø100, Ø 100



PNA\_R

PERIFLEX elastic coupling, Replacement tyre



RFVfp

Stainless steel worm and wheel gearboxes, Mounting bracket



ZBconique

Machined plastic bevel gear, 1:1



CHTRP

Single and dual output gearboxes, Up to 34,5 Nm



DKGS

Backlash free coupling Gerwah®, from 0.5 to 3Nm



NT63

Spur gear coaxial gearbox, from 8 to 20 Nm - In-line

**Complementary products**