



- Flange with tight fitting, glued bearing
- ZZ bearing (with protective shields)
- Materials:  
Housing: zinc plated steel (60C40), natural finish  
Bearing: steel




### Options

- Flange with bearing retained by circlips (BH02)



Part number			ØB	ØD	ØC	L	ØA
Round	Double flat	Square					
BH0100-40-623	BH0101-40-623	BH0102-40-623	3	Ø10x4 deep	Ø8,5	8	40
BH0100-40-634	BH0101-40-634	BH0102-40-634	4	Ø16x5 deep	Ø14,0	8	40
BH0100-40-625	BH0101-40-625	BH0102-40-625	5	Ø16x5 deep	Ø14,0	8	40
BH0100-40-606	BH0101-40-606	BH0102-40-606	6	Ø17x6 deep	Ø15,0	8	40
BH0100-58-608	BH0101-58-608	BH0102-58-608	8	Ø22x7 deep	Ø19,5	12	58
BH0100-58-6000	BH0101-58-6000	BH0102-58-6000	10	Ø26x8 deep	Ø24,0	12	58
BH0100-58-6201	BH0101-58-6201	BH0102-58-6201	12	Ø32x10 deep	Ø28,0	12	58
BH0100-94-6202	BH0101-94-6202	BH0102-94-6202	15	Ø35x11 deep	Ø33,0	18	94
BH0100-94-6003	BH0101-94-6003	BH0102-94-6003	17	Ø35x10 deep	Ø33,0	18	94
BH0100-94-6004	BH0101-94-6004	BH0102-94-6004	20	Ø42x12 deep	Ø38,0	18	94
BH0100-94-6005	BH0101-94-6005	BH0102-94-6005	25	Ø47x12 deep	Ø43,0	18	94
BH0100-94-6006	BH0101-94-6006	BH0102-94-6006	30	Ø55x13 deep	Ø50,0	18	94

Dimensions in mm



## DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-15%	-20%	On request

OP	ØH	THD	K	Bearing	N	Price each 1 to 5		
						Round	Double flat	Square
30	Ø7,5x4,5 Deep (M4 Screw)	Ø4,20 (M5)	30	623ZZ	24	71,33 €	80,73 €	84,45 €
30	Ø7,5x4,5 Deep (M4 Screw)	Ø4,20 (M5)	30	634ZZ	24	71,33 €	80,73 €	84,45 €
30	Ø7,5x4,5 Deep (M4 Screw)	Ø4,20 (M5)	30	625ZZ	24	71,33 €	80,73 €	84,45 €
30	Ø7,5x4,5 Deep (M4 Screw)	Ø4,20 (M5)	30	606ZZ	24	71,33 €	80,73 €	84,45 €
46	Ø9,5x5,5 Deep (M5 Screw)	Ø5,20 (M6)	44	608ZZ	40	118,39 €	100,16 €	105,70 €
46	Ø9,5x5,5 Deep (M5 Screw)	Ø5,20 (M6)	44	6000ZZ	40	118,39 €	100,16 €	105,70 €
46	Ø9,5x5,5 Deep (M5 Screw)	Ø5,20 (M6)	44	6201ZZ	40	118,39 €	100,16 €	105,70 €
78	Ø15,0x8,5 Deep (M8 Screw)	Ø8,50 (M10)	77	6202ZZ	67	187,79 €	212,08 €	225,62 €
78	Ø15,0x8,5 Deep (M8 Screw)	Ø8,50 (M10)	77	6003ZZ	67	187,79 €	212,08 €	225,62 €
78	Ø15,0x8,5 Deep (M8 Screw)	Ø8,50 (M10)	77	6004ZZ	67	187,79 €	212,08 €	225,62 €
78	Ø15,0x8,5 Deep (M8 Screw)	Ø8,50 (M10)	77	6005ZZ	67	187,79 €	212,08 €	225,62 €
78	Ø15,0x8,5 Deep (M8 Screw)	Ø8,50 (M10)	77	6006ZZ	67	187,79 €	212,08 €	225,62 €

Dimensions in mm

# Flange with bearing



## BH02


## Bearing retained

- Flange with bearing secured by Circlips
- Housing supplied with ZZ bearing (with protective shields)
- Materials:  
Housing: zinc plated steel (60C40), natural finish  
Bearing: steel  
Circlips: steel





### Options

- Flange with bearing glued in (BH01)



Part number			ØB	ØD	ØC	L	ØA	ØP
Round	Double flat	Square						
BH0200-40-623	BH0201-40-623	BH0202-40-623	3	Ø10x7 deep	Ø8,5	11	40	30
BH0200-40-634	BH0201-40-634	BH0202-40-634	4	Ø16x8 deep	Ø14,0	11	40	30
BH0200-40-625	BH0201-40-625	BH0202-40-625	5	Ø16x8 deep	Ø14,0	11	40	30
BH0200-40-606	BH0201-40-606	BH0202-40-606	6	Ø17x9 deep	Ø15,0	11	40	30
BH0200-58-608	BH0201-58-608	BH0202-58-608	8	Ø22x11 deep	Ø19,5	16	58	46
BH0200-58-6000	BH0201-58-6000	BH0202-58-6000	10	Ø26x12 deep	Ø24,0	16	58	46
BH0200-58-6201	BH0201-58-6201	BH0202-58-6201	12	Ø32x14 deep	Ø28,0	16	58	46
BH0200-94-6202	BH0201-94-6202	BH0202-94-6202	15	Ø35x18 deep	Ø33,0	25	94	78
BH0200-94-6003	BH0201-94-6003	BH0202-94-6003	17	Ø35x17 deep	Ø33,0	25	94	78
BH0200-94-6004	BH0201-94-6004	BH0202-94-6004	20	Ø42x19 deep	Ø38,0	25	94	78
BH0200-94-6005	BH0201-94-6005	BH0202-94-6005	25	Ø47x19 deep	Ø43,0	25	94	78
BH0200-94-6006	BH0201-94-6006	BH0202-94-6006	30	Ø55x20 deep	Ø50,0	25	94	78

Dimensions in mm



## DISCOUNTS

Qty	1+	6+	20+	40+
Disc.	List	-15%	-20%	On request

Price each 1 to 5									
ØH	THD	K	Bearing	N	ØJ	F	Round	Double flat	Square
07,5x4,5 Deep (M4 Screw)	Ø4,20 (M5)	30	623ZZ	24	Ø22x3	3	77,87 €	88,05 €	92,22 €
07,5x4,5 Deep (M4 Screw)	Ø4,20 (M5)	30	634ZZ	24	Ø22x3	3	77,87 €	88,05 €	92,22 €
07,5x4,5 Deep (M4 Screw)	Ø4,20 (M5)	30	625ZZ	24	Ø22x3	3	77,87 €	88,05 €	92,22 €
07,5x4,5 Deep (M4 Screw)	Ø4,20 (M5)	30	606ZZ	24	Ø22x3	3	77,87 €	88,05 €	92,22 €
09,5x5,5 Deep (M5 Screw)	Ø5,20 (M6)	44	608ZZ	40	Ø36x4	4	105,95 €	109,25 €	153,75 €
09,5x5,5 Deep (M5 Screw)	Ø5,20 (M6)	44	6000ZZ	40	Ø36x4	4	105,95 €	109,25 €	153,75 €
015,0x8,5 Deep (M8 Screw)	Ø5,20 (M6)	44	6201ZZ	40	Ø36x4	4	105,95 €	109,25 €	153,75 €
015,0x8,5 Deep (M8 Screw)	Ø8,50 (M10)	77	6202ZZ	67	Ø66x6	7	153,69 €	173,44 €	246,17 €
015,0x8,5 Deep (M8 Screw)	Ø8,50 (M10)	77	6003ZZ	67	Ø66x6	7	153,69 €	173,44 €	246,17 €
015,0x8,5 Deep (M8 Screw)	Ø8,50 (M10)	77	6004ZZ	67	Ø66x6	7	153,64 €	173,44 €	246,17 €
015,0x8,5 Deep (M8 Screw)	Ø8,50 (M10)	77	6005ZZ	67	Ø66x6	7	153,69 €	173,44 €	246,17 €
015,0x8,5 Deep (M8 Screw)	Ø8,50 (M10)	77	6006ZZ	67	Ø66x6	7	153,69 €	173,44 €	246,17 €

Dimensions in mm