

Spring loaded plunger

Stock DelSta

BLM

Ball tip


- **Plunger for positioning and locating**

- **Materials :**

Body: Stainless steel or thermosetting plastic

Spring: Stainless steel

Ball: Stainless steel or Delrin



Ball stainless steel or Delrin

DISCOUNTS

Qty	1+	6+	20+	50+	100+	250+	400+
Disc.	List	-5%	-10%	-15%	-20%	-25%	On request

Part number	Ball	ØD	ØD1	ØD2	L	L1	H	Contact Pressure		Weight (g)	Stock*	Price each 1 to 5
								Initial F1 (N)	Final F2 (N)			
Stainless steel body												
BLM5SS	Stainless steel	5	4	5,6	6	1	1,0	4	7	0,60	✓	1,68 €
BLM6SS	Stainless steel	6	5	6,5	7	1	1,5	6	12	1,00	✓	1,80 €
BLM8SS	Stainless steel	8	6,5	8,5	9	1	1,8	6	12	2,00	✓	2,23 €
BLM10SS	Stainless steel	10	8	12,0	13,5	2,5	2,7	10	20	6,00	✓	2,88 €
BLM5P	Delrin	5	4	5,6	6	1	0,6	4	7	0,60	✓	1,96 €
BLM6P	Delrin	6	5	6,5	7	1	1,1	6	12	1,00	✓	2,00 €
BLM8P	Delrin	8	6,5	8,5	9	1	1,5	6	12	2,00	✓	2,52 €
BLM10P	Delrin	10	8	12,0	13,5	2,5	2,3	10	20	6,00	✓	3,16 €
Plastic body												
BLM5PP	Stainless steel	5	4	5,6	6	1	1,0	4	7	0,40	-	1,03 €
BLM6PS	Stainless steel	6	5	6,5	7	1	1,5	6	12	0,70	✓	1,15 €
BLM8PS	Stainless steel	8	6,5	8,5	9	1	1,8	6	12	1,50	✓	1,34 €
BLM10PS	Stainless steel	10	8	12,0	13,5	2,5	2,7	10	20	3,14	✓	2,52 €
BLM5PP	Delrin	5	4	5,6	6	1	1,2	4	7	0,35	✓	1,20 €
BLM6PP	Delrin	6	5	6,5	7	1	1,5	6	12	0,66	✓	1,30 €
BLM8PP	Delrin	8	6,5	8,5	9	1	2	6	12	1,46	✓	1,55 €
BLM10PP	Delrin	10	8	12,0	13,5	2,5	2,7	10	20	1,44	✓	2,94 €

*Depending on availability - Dimensions in mm

Our other products



RTE

Rotex®, jaw coupling,
Aluminium



PR125

Articulated foot Ø123,
Ø 123



GTCSS

Belt tensioner, For use
in hostile
environments



KB_UU

Closed linear
precision bearing,
Precision - steel



TBD

Manual leadscrew
table with opposing
threads, 40kg



KKB-AR

Linear bearing with
inclined ball tracks,
Standard loads / -20°
+20...



SHA_PT

Handwheel with
handle, Polyamide



VTAP

Magnetic head screw,
With rubber coating
With rubber coating



DEP

Tools Hygienic Usit®
and Hygienic
Design®, Socket for



HFL

One way needle
bearing, Needle
bearing



METC

Flanged sintered
bronze bush, Self-
lubricating sintered



VELM6

Screw-on base for
hook-and-loop strip,
Polyamide

Complementary products



BLM

Spring loaded plunger
with ball tip, Stainless
steel body



BPM_LOK

Long-Lok slotted
spring plunger with
ball tip, LONG-LOK -
Stainless ...



BPM-Z

Plastic slotted spring
plunger with ball tip,
Plastic body +
plastic...