


## Single or two part assembly

## BAG1ss BAG2ss


- Solid fixing onto any type of shaft
- Do not separate the two pieces
- Materials:  
Clamp + screw: stainless steel  
Screw: steel alloy
- 2-part clamps offer a 20% stronger fixing
- Dimensions  $\varnothing D$  and L are given as an indication only and are subject to change



stainless steel



Typical application




### DISCOUNTS

| Qty  | 1+   | 5+  | 10+  | 25+  | 50+        |
|------|------|-----|------|------|------------|
| Disc | List | -6% | -12% | -18% | On request |

| Part number |             | $\varnothing A$ | $\varnothing D$ | L  | Screw    | Stock* | Stock*  | Price each 1 to 4 |          |
|-------------|-------------|-----------------|-----------------|----|----------|--------|---------|-------------------|----------|
| 1 part      | 2 parts     |                 |                 |    |          | 1 part | 2 parts | 1 part            | 2 parts  |
| BAG1-004/SS | BAG2-004/SS | 4               | 16              | 9  | M3 x 8   | ✓      | ✓       | 8,19 €            | 10,47 €  |
| BAG1-005/SS | BAG2-005/SS | 5               | 16              | 9  | M3 x 8   | ✓      | ✓       | 8,19 €            | 10,47 €  |
| BAG1-006/SS | BAG2-006/SS | 6               | 16              | 9  | M3 x 8   | ✓      | ✓       | 8,19 €            | 10,47 €  |
| BAG1-008/SS | BAG2-008/SS | 8               | 18              | 9  | M3 x 8   | ✓      | ✓       | 9,11 €            | 10,67 €  |
| BAG1-010/SS | BAG2-010/SS | 10              | 24              | 9  | M3 x 10  | ✓      | ✓       | 11,27 €           | 13,31 €  |
| BAG1-012/SS | BAG2-012/SS | 12              | 28              | 11 | M4 x 12  | ✓      | ✓       | 11,64 €           | 13,81 €  |
| BAG1-015/SS | BAG2-015/SS | 15              | 34              | 13 | M5 x 16  | ✓      | ✓       | 13,93 €           | 16,92 €  |
| BAG1-016/SS | BAG2-016/SS | 16              | 34              | 13 | M5 x 16  | ✓      | ✓       | 13,93 €           | 16,92 €  |
| BAG1-018/SS | BAG2-018/SS | 18              | 36              | 13 | M5 x 16  | ✓      | ✓       | 15,92 €           | 19,01 €  |
| BAG1-020/SS | BAG2-020/SS | 20              | 40              | 15 | M6 x 16  | ✓      | ✓       | 19,40 €           | 20,24 €  |
| BAG1-025/SS | BAG2-025/SS | 25              | 45              | 15 | M6 x 16  | ✓      | ✓       | 21,44 €           | 23,01 €  |
| BAG1-030/SS | BAG2-030/SS | 30              | 54              | 15 | M6 x 18  | ✓      | ✓       | 24,76 €           | 27,59 €  |
| BAG1-040/SS | BAG2-040/SS | 40              | 60              | 15 | M6 x 18  | ✓      | ✓       | 30,93 €           | 38,38 €  |
| BAG1-050/SS | BAG2-050/SS | 50              | 78              | 19 | M8 x 25  | ✓      | ✓       | 58,29 €           | 84,96 €  |
| BAG1-055/SS | BAG2-055/SS | 55              | 90              | 16 | M8 x 20  | -      | -       | 84,02 €           | 88,99 €  |
| BAG1-060/SS | BAG2-060/SS | 60              | 100             | 16 | M8 x 20  | -      | ✓       | 96,82 €           | 101,91 € |
| BAG1-070/SS | BAG2-070/SS | 70              | 110             | 20 | M10 x 25 | -      | -       | 107,85 €          | 113,61 € |
| BAG1-075/SS | BAG2-075/SS | 75              | 125             | 20 | M10 x 25 | -      | -       | 138,32 €          | 144,27 € |
| BAG1-080/SS | BAG2-080/SS | 80              | 125             | 20 | M10 x 25 | -      | -       | 131,65 €          | 137,52 € |

\*Depending on availability - Dimensions in mm

## Our other products



Crossed helical gear  
crossed axis at 90°,  
Machined plastic  
(delrin)



Flexible drive shaft,  
Masterflex® Steel,  
with PVC casing



Crossed helical gear  
crossed axis at 90°,  
Steel 20NCD2



Masterplate®  
glueable insert  
rectangular,  
rectangular with



Closed linear  
precision bearing,  
Precision - steel



T type timing pulley,  
Economy range - T5  
aluminium



Jaw coupling,  
economy range,  
Aluminium



3 lobed handle,  
Polyamide - Brass



Strike for toggle latch,  
13mm



Adjusting rod for  
clamp - Female, Bored



Stainless steel garnet  
hinge, To be welded



HEAVY DUTY spur  
gear, Steel 35NCD6

## Complementary products



Stainless steel  
Clamping collar,  
Stainless steel



Steel Clamping collar,  
Steel