

Mushroom knob with male thread and high head

BCFHUSS

Hygienic Usit®


- Mushroom knob with a male thread and high head for use with Hygienic Usit® sealing washers®
- The high head makes this mushroom knob ideal for manual lateral movements.
- Fully polished surface with a roughness much lower than Ra0.8µm.
- Material:
Stainless steel 1.4404 (316L)
Mirror polished finish

Advantages

- Regardless of the mounting position of the mushroom knob, dirt and residue from product or cleaning material will not adhere. This guarantees easy cleaning.
- USIT® Hygienic sealing washers are used to seal the screwed connection.
- The stem of the mushroom knob is specially designed to ensure an almost cavity free seal thus meeting hygiene requirements.

Accessory

- RDE sealing washers (see pages 37 à 39)



DISCOUNTS

Qty	1+	6+	10+	25+
Disc.	Prix	-5%	-10%	On request

Part N°	ØD	ØD1	ØD2	H	H1	L	L1	R	R1	Price each
										1 to 4
BCFH-4/HUSS	M4	20	10,8	19	8	8	7	3	0,45	13,02 €
BCFH-5/HUSS	M5	21	11,8	21	10	10	9	3	0,50	14,10 €
BCFH-6/HUSS	M6	25	14,2	25	12	12	11	3	0,55	15,68 €
BCFH-8/HUSS	M8	33	18,0	33	15	16	15	4	0,60	26,40 €
BCFH-10/HUSS	M10	40	22,3	40	19	20	19	4	0,75	28,18 €

All dimensions in mm

Our other products



CHM50

Worm and wheel gear reducer, up to 107 Nm



VTAP

Magnetic head screw, With rubber coating



GE

Toggle latches, Standard



MFB_MHB

Moulded plastic bevel gear (nylon), 4:1



PW_PWG2

Worm - precision range, Steel



AT5M AT10M

AT type timing belt per metre, AT10 Steel cored polyurethane



LVT

Miniature motorised actuator 2A, 2 amperes



PITAss

Locking bolt, with T handle



ERC

Quick fitting cable terminal, Fork



DOMI80

Domino 80 adjustable slide, Slide DOMILINE



HLU


Spoked handwheel without handle,



RTT

Locking Assembly, Medium/high torque

Complementary products



RDE-W

Sealing washer Hygienic Usit®, Stainless steel - White EPDM



RDE-B

Sealing washer Hygienic Usit®, Stainless steel - Blue EPDM



BCTH

Mushroom headed button Hygienic Usit®, With female thread and high ...