

Box set of Nitrile O-rings

Diameters 3,00x2,00mm à 45,20x4,00mm **BOX-TOR-H**


- Box set of Nitrile O-rings
- 30 different sizes
- Material:
Nitrile NBR 70 Shore A
- Working temperature: -30 to +110°C

Uses

- Suitable for:
- Hydraulic oils
 - HFA fluids
 - HFB fluids
 - HFC fluids
 - Air

Info

- Ideal for the maintenance department



Box contents

| Quantity | ØD1 | ØD2 |
|----------|-------|------|
| 18 | 3,00 | 2,00 |
| 18 | 4,00 | 2,00 |
| 18 | 5,00 | 2,00 |
| 18 | 6,00 | 2,00 |
| 17 | 7,00 | 2,00 |
| 17 | 8,00 | 2,00 |
| 17 | 10,00 | 2,00 |
| 14 | 10,00 | 2,50 |
| 14 | 11,00 | 2,50 |
| 14 | 12,00 | 2,50 |

| Quantity | ØD1 | ØD2 |
|----------|-------|------|
| 14 | 14,00 | 2,50 |
| 14 | 16,00 | 2,50 |
| 14 | 17,00 | 2,50 |
| 14 | 19,00 | 2,50 |
| 12 | 19,00 | 3,00 |
| 12 | 20,00 | 3,00 |
| 12 | 22,00 | 3,00 |
| 12 | 24,00 | 3,00 |
| 12 | 25,00 | 3,00 |
| 12 | 27,00 | 3,00 |

| Quantity | ØD1 | ØD2 |
|----------|-------|------|
| 12 | 28,00 | 3,00 |
| 12 | 30,00 | 3,00 |
| 12 | 32,00 | 3,00 |
| 12 | 33,00 | 3,00 |
| 12 | 35,00 | 3,00 |
| 12 | 36,00 | 3,00 |
| 12 | 38,00 | 3,00 |
| 9 | 38,00 | 4,00 |
| 9 | 42,00 | 4,00 |
| 9 | 45,00 | 4,00 |

DISCOUNTS

| Qty | 1+ | 3+ | 5+ |
|-------|-----|-----|------------|
| Disc. | Net | -5% | On request |

| Part N° | Material | Quantity per box | Stock* | Price each 1 to 2 |
|-----------|-------------|------------------|--------|-------------------|
| BOX-TOR-H | NBR 70 Sh A | 404 o-rings | ✓ | 27,73 € |

All dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel

Fax

Our other products



BFD

Locking pin for bush,
+180°C



PARF110

Pressed steel base
rigid foot, Swivelling
Ø110



ZG2

Plastic spur gear,
Machined plastic
(delrin)



HG6

Steel spur gear, Steel
20NCD2



CHB

Worm and wheel gear
reducer, up to 41 Nm



AT10-50ECO

AT type timing pulley,
Economy range -
AT10 aluminium



GG2

Ground spur gear,
Heat treated steel



MDB_MTB

Moulded plastic bevel
gear (nylon), 3:1



PSP

Support profile, Panel
support



PNA_R

PERIFLEX elastic
coupling,
Replacement tyre



BEK

Bearing housing for
miniature ballscrew,
Bearing housing



ZG1

Plastic spur gear,
Machined plastic
(delrin)

Complementary products



BOX-TOR-TOOL

Box set of tool for
Nitrile O-rings,
Extraction tools