





- Low cost clip
- Made from zinc plated steel
- Supplied by the packet

Advantages

- Manual assembly/disassembly



Typical applications

DISCOUNTS

Qty	1+	5+	10+	21+
Disc. List	-10%	-20%	On request	

Part number	ØD	L	B	For shaft	Weight per 100 (kg)	Quantity per pack	Stock*	Price each 1 to 4
BETA-2/B	2	53	12	9-11	0,5	100	✓	8,01 €
BETA-2.5/B	2,5	52	10	11-13	0,6	100	✓	10,06 €
BETA-3/B	3	66	15	13-17	0,9	100	✓	12,95 €
BETA-4/B	4	83	22	17-20	2,3	100	✓	24,84 €
BETA-4.5/B	4,5	68	24	20-23	2,5	100	✓	33,03 €
BETA-5/B	5	100	23	23-26	3,9	100	✓	42,28 €
BETA-6/B	6	105	26	26-30	6,0	50	✓	29,50 €
BETA-7/B	7	125	26	30-34	9,1	25	-	41,30 €
BETA-8/B	8	142	29	34-45	13,6	25	✓	51,68 €

*Depending on availability - Dimensions in mm


- Low cost clip
- Made from stainless steel AISI 304
- Supplied by the packet

Advantages

- Manual assembly/disassembly



stainless steel



Typical applications

DISCOUNTS

Qty	1+	5+	10+	15+
Disc.	List	-10%	-20%	On request

Part number	ØD	L	B	Weight per 100 (kg)	Quantity per pack	Price each 1 to 4
BETA-2/SS/B	2	53	12	0,32	100	35,11 €
BETA-3/SS/B	3	66	15	0,88	50	31,33 €
BETA-4/SS/B	4	83	22	1,49	25	32,09 €
BETA-5/SS/B	5	100	23	3,62	20	43,71 €
BETA-6/SS/B	6	105	26	5,56	10	34,21 €

*Depending on availability - Dimensions in mm


Our other products




Tools Hygienic Usit® and Hygienic Design®, Protective insert for s...



Free roller, Steel



Wear strip for slat top chain, Z profile to be clipped



Telescopic universal joint, Normal duty



Steel spur gear, Steel 20NCD2



Latch with locking system, Aluminium



Parallel axis helical gear, Steel 20NCD2



Articulated levelling foot, pressed base Ø150, Ø 150



Rotating bent lever with spring, Increased fitting tolerances



Quick fitting cable terminal, Eye version



Moulded plastic spur gear, Moulded plastic (nylon)



Square hinge with riveted pin, drilled, Square with riveted pin, dri...

Complementary products