

Flush fitting ball transfer unit

For light loads

BPLE

- **Pressed steel ball transfer unit**
- Push fit for rapid installation & replacement where only single-sided access to the mounting surface is available
- For light loads
- Housing made from pressed steel
- With drainage hole and felt seal
- Orientation: horizontal with ball upwards
- Max. speed: 1m/s
- Working temperature range: -20 to +70°C
- Materials:


BPL : galvanised steel body and steel balls

BPL/SS : stainless steel body and stainless steel 420 balls



Advantages

- Optional clips compensate for irregularities in seat bore diameter



DISCOUNTS

Qty	1+	6+	20+	40+	60+
Disc.	Net	-10%	-15%	-20%	On request

Part N°	Ødw ball	ØA	B	C	ØD	E	F	Carrying capacity (kg)	Weight (g)	Stock*	Price each
											1 to 5
Steel body, steel balls											
BPLE15-24	15	24	9,5	4,6	31	21,0	2,8	60	0,041	✓	3,63 €
BPLE22-36	22	36	9,8	3,9	45	29,5	2,9	160	0,128	✓	6,67 €
BPLE30-45	30	45	13,8	6,8	55	37,0	3,6	280	0,253	✓	10,08 €
BPLE45-62	45	62	19,0	9,0	75	53,5	4,0	600	0,720	-	48,86 €
Stainless steel body, stainless steel balls											
BPLE15-24/SS	15	24	9,5	4,6	31	21,0	2,8	40	0,039	✓	11,23 €
BPLE22-36/SS	22	36	9,8	3,9	45	29,5	2,9	90	0,125	✓	14,35 €
BPLE30-45/SS	30	45	13,8	6,8	55	37,0	3,6	200	0,271	✓	24,41 €
BPLE45-62/SS	45	62	19,0	9,0	75	53,5	4,0	260	0,710	-	117,92 €

*Depending on availability - Dimensions in mm

Our other products



G-ECO

Eco range Spur gear,
Steel C45



PCS6255

Chain sprocket -
Stainless steel,
15.875mm (DIN
08B-1)



BLOC

Doorstop, Doorstop



VCMB

Dual-thread screw
wood/metal, Stainless
steel



SSDB

Stainless steel bevel
gear, 2:1



CMA

Eye bolt, Steel



VTSM

Ball head screws
Hygienic Design®,
Stainless steel



KKP-AR

Linear bearing with
inclined ball tracks,
Heavy loads / -20°
+200°




ACL-FPA

Panel mounting block
for aluminium



BABPass

Hardened stainless
steel ball pin with



IN2

Internal gear,
Machined plastic



PR125

Articulated foot Ø123,
Ø 123

Complementary products



BPHClip

Clip for ball transfer
unit, Insert clip -
Installing from above



BPL

Ball transfer unit light
duty, Light



BPLE

Ball transfer unit push
fit, Light



BPPE

Ball transfer unit push
fit, Light