

Ball transfer unit in blue certified plastic

Suitable for foodstuff sector

BPPEBLU



- The ball transfer units are made of a certified blue plastic which is suitable for use in the foodstuff sector
- Press-in assembly
- Conveying speed up to 1.5 m/s
- Foodstuff conform: Food Grade, EU Regulation 1935/2004, EU Regulation 10/2011
- Material :
 - Housing and cap POM
 - Bearing ball stainless steel
 - Load ball stainless steel or plastic
- Temperature range: -30 °C to +50 °C (up to +30°C with plastic load balls)

Advantages

- The ball transfer units are equipped with a gap-free and sealed cap, which prevents the formation of soiled edge
- The dirt holes underneath the housing enable particularly easy cleaning of the ball transfer units



Food industry
NEW!



DISCOUNTS

Qty	1+	6+	20+	30+
Disc.	List	-10%	-15%	On request

Part number	ØD	ØD1	ØDK	H	H1	H2	Load rating C (kg)	Price each 1 to 5
Load ball in POM								
BPPE15-24/PP/BLU	24±0,1	31±0,2	15,875	20,5±0,2	9,5±0,2	4,5	200	
BPPE22-36/PP/BLU	36±0,1	45±0,2	22,225	30,5±0,2	10±0,2	4,5	250	
BPPE30-45/PP/BLU	45±0,1	55±0,1	30,000	37±0,1	14±0,1	5,5	350	
BPPE45-62/PP/BLU	62±0,1	75±0,1	44,500	53,5±0,1	19±0,1	9,0	500	
Load ball in stainless steel								
BPPE15-24/SS/BLU	24±0,1	31±0,2	15,875	20,5±0,2	9,5±0,2	4,5	200	
BPPE22-36/SS/BLU	36±0,1	45±0,2	22,225	30,5±0,2	10±0,2	4,5	250	
BPPE30-45/SS/BLU	45±0,1	55±0,1	30,000	37±0,1	14±0,1	5,5	350	
BPPE45-62/SS/BLU	62±0,1	75±0,1	44,500	53,5±0,1	19±0,1	9,0	500	

All dimensions in mm.


Our other products



RPCplss
Swivel castor with
double brake,
Stainless steel -
Polyamide



BLHB50
Right angled gearbox,
bored shafts, up to 30
Nm



G1
Steel spur gear, Steel
20NCD2



EKONSL
Silicone conical elasto
buffer, Female
mounting



MFBS
Stainless steel flexible
bellows coupling,
Stainless steel - with
se...



QN
Single row cylindrical
roller bearing, Free
outer ring



PSPE20
Conical flexible shaft
handle Ø20, Black
PVC



DOM80
Accessories, Clamping
lever



MLY
Bow shackle with eye
bolt, Steel



SUP
Self-centering
clamping hub steel,



SRG
Adjustable latch
clamp with strike



CHAR7520
Spring hinge, screwed

Complementary products



BPPE
Ball transfer unit push
fit, Light



BPPE
Ball transfer unit push
fit, Light



BPPE
Ball transfer unit push
fit, Light



BPHF
Ball transfer unit push
fit, Heavy