

# Boxed set of wide threaded self tapping inserts

## BOX-INS-W

## For wood

- Selection of self tapping inserts with a large external thread for use in wood
- Assembles by deformation, no special tools required
- With hexagonal socket for assembly
- Material:  
White galvanized steel

### Applications


- Can be used in soft plastics or woods and rubber



480 pieces



| Quantity | Type | ØD | L  | Ød | SW |
|----------|------|----|----|----|----|
| 50       | 010  | 10 | 12 | M5 | 5  |
| 50       | 010  | 12 | 15 | M6 | 6  |
| 30       | 010  | 14 | 15 | M8 | 8  |
| 50       | 440  | 10 | 12 | M5 | 5  |
| 50       | 440  | 12 | 12 | M6 | 6  |
| 30       | 440  | 14 | 15 | M8 | 8  |
| 50       | 002  | 10 | 10 | M5 | -  |
| 50       | 002  | 12 | 15 | M6 | -  |
| 30       | 002  | 14 | 14 | M8 | -  |
| 30       | 006  | 8  | 12 | M5 | -  |
| 30       | 006  | 15 | 15 | M6 | -  |
| 30       | 006  | 12 | 15 | M8 | -  |



### DISCOUNTS

| Qty   | 1+   | 2+  | 5+         |
|-------|------|-----|------------|
| Disc. | List | -5% | On request |

| Part number | Quantity per box | Stock* | Price each |
|-------------|------------------|--------|------------|
| BOX-INS-W   | 480 pieces       | ✓      | 410,02 €   |

\*Depending on availability - Dimensions in mm

- Selection of self tapping inserts with fine external thread


### Assembly

- Refer to INS300


### Applications

- For use in aluminium or other non-ferrous metals, thermosetting plastics or hard woods

297 pieces



| Quantity | ØD        | L  | Ød  |
|----------|-----------|----|-----|
| 30       | M5x0,5    | 6  | M3  |
| 50       | M6,5x0,75 | 8  | M4  |
| 20       | M8x1      | 8  | M5  |
| 40       | M8x1      | 10 | M5  |
| 20       | M9x1      | 8  | M6  |
| 20       | M9x1      | 12 | M6  |
| 40       | M10x1,5   | 14 | M6  |
| 20       | M12x1,5   | 12 | M8  |
| 30       | M12x1,5   | 15 | M8  |
| 20       | M14x1,5   | 18 | M10 |
| 5        | M16x1,5   | 22 | M12 |
| 2        | M20x1,5   | 25 | M10 |



### DISCOUNTS

| Qty   | 1+       | 2+ | 5+         |
|-------|----------|----|------------|
| Disc. | List -5% |    | On request |

| Part number | Material                          | Quantity per box | Stock* | Price each |
|-------------|-----------------------------------|------------------|--------|------------|
| BOX-INS300  | Yellow zinc plated hardened steel | 297 pieces       | ✓      | 496,99 €   |

\*Depending of availability - Dimensions in mm