

# Bolt-on hinge



## CHA

## Opens to 135°




- Accessory for square tube structure
- Surface mounting hinge
- Materials:  
Hinge: reinforced polyamide  
Pin: zinc plated steel

### Info.

- Not sold individually, please contact us for details

### Accessories

- Magnetic lock SER (tome 5 p.284)
- Doorstop BLOC (tome 5 p.277)
- Manual latch LOQ (tome 5 p.285)



### DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	A	B	C	D	E	F	G	ØH	I	ØM	Stock*	Price each 1 to 49
CHA135-48	48	30	30	10	10	15	48	13,5	3,0	6,5	✓	7,32 €
CHA135-64	64	40	40	13	13	19	64	13,5	3,0	6,5	✓	7,81 €
CHA135-96	96	60	63	16	17	24	96	16,0	4,6	8,0	✓	10,20 €

\*Depending on availability - Dimensions in mm

Opens to 138°

CHA



- Accessory for square tube structure
- Surface mounting hinge
- Materials:  
Hinge: reinforced polyamide  
Pin: zinc plated steel  
Inserts: brass

## Info.

- Not sold individually, please contact us for details

## Accessories

- Magnetic lock SER (tome 5 p.284)
- Doorstop BLOC (tome 5 p.277)
- Manual latch LOQ (tome 5 p.285)



Typical application

## DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	A	B	C	D	E	F	G	ØM	Stock*	Price each 1 to 49
CHA138-49-M5	49	30	32	11	13	19	49	M5	-	20,51 €
CHA138-49-M6	49	30	32	11	13	19	49	M6	✓	20,51 €

\*Depending on availability - Dimensions in mm

# Bolt-on hinge with threaded inserts



## CHA

## Opens to 225°




- Accessory for square tube structure
- Surface mounting hinge
- Materials:  
Hinge: reinforced polyamide  
Pin: zinc plated steel  
Inserts: brass

### Info.

- Not sold individually, please contact us for details

### Accessories

- Magnetic lock SER (tome 5 p.284)
- Doorstop BLOC (tome 5 p.277)
- Manual lock LOQ (tome 5 p.285)



### DISCOUNTS

Qty	1+	50+	100+
Disc.	List	-5%	On request

Part number	A	B	C	D	E	F	G	ØM	Stock*	Price each 1 to 49
CHA225-30	30	15	18	11	19	25	36	M5	✓	6,85 €
CHA225-54	54	30	21	13	22	29	42	M6	✓	9,67 €
CHA225-78	78	42	31	16	29	40	62	M8	-	18,81 €

\*Depending on availability - Dimensions in mm