Square hinge with riveted pin, drilled

Eco

CHAC — Sheet metal with rolled knuckle


- **Hinge for plug door**
- **Riveted pin, half swaged**
- Material:
  Stainless steel 304
- Natural finish


stainless steel



Advantages

- Economic hinge





DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request


Part number	A	B	C	ØD	F	G	ØS	Weight (g)	Stock*	Price each 1 to 5
CHAC4040/SS	40	40	2	4	8	24	3,5	34	✔	14,69 €
CHAC5050/SS	50	50	2	6	8	34	4,0	61	✔	17,45 €
CHAC6060/SS	60	60	2	6	8	40	4,0	82	✔	19,89 €

*Depending on avaibility - Dimensions in mm

€ Eco Square hinge with riveted pin, not drilled


Sheet metal with rolled knuckle CHAC-NP


- **Hinge for plug door**
- **Riveted pin, leaves not offset**
- Material:
  CHAC-NP: Steel hinge
  CHAC-NP/SS: Stainless steel 304
- Natural finish



Advantages

- Economic hinge





DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request


Part number	A	B	C	ØD	Weight (g)	Stock*	Price each 1 to 5
Steel							
CHAC4040-NP	40	40	2	4	34	✔	8,69 €
CHAC5050-NP	50	50	2	6	61	✔	10,68 €
CHAC6060-NP	60	60	2	6	82	✔	11,80 €
Stainless steel							
CHAC4040-NP/SS	40	40	2	4	34	✔	14,69 €
CHAC5050-NP/SS	50	50	2	6	61	✔	16,85 €
CHAC6060-NP/SS	60	60	2	6	82	✔	19,03 €

**Depending on availability - Dimensions in mm*

Our other products


PW_PWG1

Worm - precision range, Steel


NKIB

Combined bearing with inner ring, Axial load in both directions


FB_ECO

Eco. range steel bevel gear, 4:1


NCT

Square tube connector, Fixed angle


MCL

Reducing sleeve female/female, Cylindrical - stainless steel


SEH

Horizontal stirrup toggle clamp, Horizontal Latch clamp - stainless ...


RCX-6

Spherical tilt washer - DIN6319, concave


DZY

Cylindrical stop, Steel


CLB_T

Die cast zinc clamping lever - male, Zamak


BTE

Universal tension arm, For standard applications


FRss

Stainless steel thread inserts, Stainless steel


UCF_PBT

Stainless steel/Polymer flanged bearing, Polymer and stainless steel

Complementary products


CHAC4040NP

Square hinge with riveted pin, not drilled, Square with riveted pin,...


CHA60

Rectangular hinge, drilled or countersunk, Rectangular, drilled or c...