

Square hinge with riveted pin, drilled Eco

CHAC Sheet metal with rolled knuckle



- Hinge for plug door
- Riveted pin, half swaged
- Material:
Stainless steel 304
- Natural finish

stainless steel



Advantages

- Economic hinge



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	A	B	C	ØD	F	G	ØS	Weight (g)	Stock*	Price each 1 to 5
CHAC4040/SS	40	40	2	4	8	24	3,5	34	✓	14,69 €
CHAC5050/SS	50	50	2	6	8	34	4,0	61	✓	17,45 €
CHAC6060/SS	60	60	2	6	8	40	4,0	82	✓	19,89 €

*Depending on availability - Dimensions in mm





Square hinge with riveted pin, **not drilled**

Sheet metal with rolled knuckle **CHAC-NP**

- Hinge for plug door
- Riveted pin, leaves not offset
- Material:
 - CHAC-NP:** Steel hinge
 - CHAC-NP/SS:** Stainless steel 304
- Natural finish

Advantages

- Economic hinge



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	A	B	C	ØD	Weight (g)	Stock*	Price each
						1 to 5	
Steel							
CHAC4040-NP	40	40	2	4	34	✓	8,69 €
CHAC5050-NP	50	50	2	6	61	✓	10,68 €
CHAC6060-NP	60	60	2	6	82	✓	11,80 €
Stainless steel							
CHAC4040-NP/SS	40	40	2	4	34	✓	14,69 €
CHAC5050-NP/SS	50	50	2	6	61	✓	16,85 €
CHAC6060-NP/SS	60	60	2	6	82	✓	19,03 €

*Depending on availability - Dimensions in mm

Our other products



ZDB
Machined plastic
bevel gear , 2:1




BPPL
Mini plain bearing ball
transfer unit, For
countersinking



PRF_PL_9090
Joining plate for
aluminium profile,
Joint plate - 90x90
mm



WS16
Drylin® W rail, Rail



BOX-TOR-TOOL
Box set of tool for
Nitrile O-rings,
Extraction tools



LRR
Catch-plate for latch,
Catch-plate



KKB-AR
Linear bearing with
inclined ball tracks,
Standard loads / -20°
+20...



T5P_T10P
Connecting plate for T
type timing belts, T10



SSDB
Stainless steel bevel
gear, 2:1



SHTP
Drylin® Linear table,
Economy range



H1
Crossed helical gear
crossed axis at 90°,
Steel 20NCD2



RLR
Roll-Ring® chain
tensioner, Roll-Ring®
Self-adjusting

Complementary products



CHAC4040NP
Square hinge with
riveted pin, not
drilled, Square with
riveted pin,...



CHA60
Rectangular hinge,
drilled or countersunk,
Rectangular, drilled or
c...