

Square hinge with riveted pin, **drilled**

CHAC Sheet metal with rolled knuckle



- Hinge for plug door
- Riveted pin, half swaged
- Material:
Stainless steel 304
- Natural finish

stainless steel



Advantages

- Economic hinge



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	A	B	C	ØD	F	G	ØS	Weight (g)	Stock*	Price each 1 to 5
CHAC4040/SS	40	40	2	4	8	24	3,5	34	✓	14,69 €
CHAC5050/SS	50	50	2	6	8	34	4,0	61	✓	17,45 €
CHAC6060/SS	60	60	2	6	8	40	4,0	82	✓	19,89 €

*Depending on availability - Dimensions in mm





Square hinge with riveted pin, **not drilled**

Sheet metal with rolled knuckle **CHAC-NP**

- Hinge for plug door
- Riveted pin, leaves not offset
- Material:
 - CHAC-NP:** Steel hinge
 - CHAC-NP/SS:** Stainless steel 304
- Natural finish

Advantages

- Economic hinge



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	A	B	C	ØD	Weight (g)	Stock*	Price each
						1 to 5	
Steel							
CHAC4040-NP	40	40	2	4	34	✓	8,69 €
CHAC5050-NP	50	50	2	6	61	✓	10,68 €
CHAC6060-NP	60	60	2	6	82	✓	11,80 €
Stainless steel							
CHAC4040-NP/SS	40	40	2	4	34	✓	14,69 €
CHAC5050-NP/SS	50	50	2	6	61	✓	16,85 €
CHAC6060-NP/SS	60	60	2	6	82	✓	19,03 €

*Depending on availability - Dimensions in mm

Our other products



INS_SS

Self tapping stainless steel insert, Stainless steel



SA_SAKH

Housing for linear bearing, Closed - light load



ACLBT5

Spherical ended stop for aluminium profile, Spherical ended stop




BPHFclip

Clip for ball transfer unit, Insert clip - Installing from above



EFTC

Fixing support, Stainless steel



TPR

High helix leadscrew, Leadscrew only - up to 40mm per rotation



YG1

HEAVY DUTY spur gear, Steel 35NCD6



GTCS5

Belt tensioner, For use in hostile environments



MFBS5

Stainless steel flexible bellows coupling,



PW_PWG2

Wheel - precision range, Bronze



GMC_GMK_BR

Guiding profile clamp, Flat or rounded



WW20

Drylin® W slide, slide assembly

Complementary products



CHAC4040NP

Square hinge with riveted pin, not drilled, Square with riveted pin,...



CHA60

Rectangular hinge, drilled or countersunk, Rectangular, drilled or c...