

End cap for square tube

Stock Pla


BTC

Black plastic

- Material: black technopolymer

Info.

- Dimensions are given as a guide and are subject to change
- Not sold individually, please contact us for details



DISCOUNTS

Qty	1+	60+	100+	200+
Disc.	List	-5%	-10%	On request

Part number	External Ø of tube	Tube thickness	Stock*	Price each 1 to 59
BTC10	10x10	1,5-2	-	0,16 €
BTC12	12x12	1,5-2	-	0,16 €
BTC13	13x13	1,5-2	-	On request
BTC15	15x15	1,5-2	✓	0,20 €
BTC16	16x16	1,5-2	✓	0,20 €
BTC18	18x18	1,5-3	-	0,20 €
BTC20	20x20	1-3	✓	0,20 €
BTC22	22x22	1-3	-	0,25 €
BTC25/1-3	25x25	1-3	✓	0,25 €
BTC28	28x28	1,5-3	-	0,48 €
BTC30/1-2,5	30x30	1-2,5	✓	0,48 €
BTC30/2,5-4,5	30x30	2,5-4,5	✓	0,59 €
BTC35/1-3	35x35	1-3	✓	0,89 €
BTC35/2,5-5	35x35	2,5-5	✓	0,89 €
BTC40/1-3	40x40	1-3	✓	1,18 €
BTC40/2,5-4	40x40	2,5-4	✓	1,18 €
BTC40/5-5,5	40x40	5-5,5	-	1,18 €

Part number	External Ø of tube	Tube thickness	Stock*	Price each 1 to 59
BTC40/4-4,5	40x40	4-4,5	-	1,18 €
BTC45	45x45	1-3	✓	1,29 €
BTC50/1-2,5	50x50	1-2,5	✓	1,49 €
BTC50/2,6-4	50x50	2,6-4	✓	1,63 €
BTC50/3,5-6	50x50	3,5-6	✓	1,68 €
BTC60/1,5-3,5	60x60	1,5-3,5	✓	2,62 €
BTC60/3-5	60x60	3-5	✓	2,62 €
BTC70	70x70	2-4	✓	4,38 €
BTC80/2-4	80x80	2-4	✓	4,89 €
BTC80/3-5	80x80	3-5	✓	5,11 €
BTC90/2-5	90x90	2-5	-	8,75 €
BTC90/3,6-5	90x90	3,6-5	-	8,65 €
BTC100/1-4	100x100	1-4	✓	9,92 €
BTC100/5-8	100x100	5-8	✓	9,88 €
BTC120	120x120	2,5-5	✓	15,31 €
BTC150/5-8	150x150	5-8	-	25,93 €
BTC150/10-12,5	150x150	10-12,5	-	25,93 €

*Depending on availability - Dimensions in mm

Our other products



PRF-P

Aluminium profile feet support, For feet or casters



BPHT

Ball transfer unit bolt fitting, Heavy




PRF-SRA-78

Lock for aluminium profile, Quick fitting, self locking door lock



DEP

Tools Hygienic Usit® and Hygienic Design®, Socket for mounting Hyg...



PRF4545r90

Standard aluminium profile, 45 x 45 mm - R90°




GARQT

Quarter turn lock pin for clamping, Quarter turn



BCH_SS

Mushroom headed button, M3 to M8



M0

Worm and wheel set, Bronze



FR

Steel thread inserts, Steel



GDR880

Straight track for slat top chain, Ranges 880



NTMdl

Set screw delrin tip, Delrin-point



BOX-CS

Hose clamp, Box set of steel hose clamps

Complementary products



BTC_M

End cap with threaded insert for square tube, With threaded insert



TUBE25_25

Square Tube, Aluminium or Stainless steel