# End cap for square tube


## BTC

### Black plastic


- Material: black technopolymer

**Info.**

- Dimensions are given as a guide and are subject to change
- **Not sold individually, please contact us for details**







**DISCOUNTS**


| Qty | 1+ | 60+ | 100+ | 200+ |
|---|---|---|---|---|
| Disc. | List | -5% | -10% | On request |

| Part number | External tube | Tube thickness | Stock* | Price each 1 to 59 |
|---|---|---|---|---|
| BTC10 | 10x10 | 1-2 | - | 0,18 € |
| BTC12 | 12x12 | 1-2 | - | 0,18 € |
| BTC13 | 13x13 | 0,5-2 | - | On request |
| BTC15 | 15x15 | 1-2 | - | 0,22 € |
| BTC16 | 16x16 | 1-2,5 | - | 0,24 € |
| BTC18 | 18x18 | 1,5-3 | - | 0,24 € |
| BTC20 | 20x20 | 1-3 | ✔ | 0,24 € |
| BTC22 | 22x22 | 1-3 | - | 0,28 € |
| BTC25/1-3 | 25x25 | 1-3 | ✔ | 0,28 € |
| BTC28 | 28x28 | 1-3 | - | 0,56 € |
| BTC30/1-2.5 | 30x30 | 1-3 | ✔ | 0,56 € |
| BTC30/2.5-4.5 | 30x30 | 2,5-4,5 | ✔ | 0,69 € |
| BTC35/1-3 | 35x35 | 1-3 | ✔ | 1,05 € |
| BTC35/2.5-5 | 35x35 | 2,5-5 | ✔ | 1,05 € |
| BTC40/1-3 | 40x40 | 1-3 | ✔ | 1,40 € |
| BTC40/2.5-4 | 40x40 | 3-5 | - | 1,40 € |

| Part number | External tube | Tube thickness | Stock* | Price each 1 to 59 |
|---|---|---|---|---|
| BTC40/5-5.5 | 40x40 | 4,5-5,5 | ✔ | 1,40 € |
| BTC45 | 45x45 | 1-3 | ✔ | 1,52 € |
| BTC50/1-2.5 | 50x50 | 1-2,5 | ✔ | 1,77 € |
| BTC50/2.6-4 | 50x50 | 2,6-4 | ✔ | 1,94 € |
| BTC50/3.5-6 | 50x50 | 3,5-6 | ✔ | 2,01 € |
| BTC60/1.5-3.5 | 60x60 | 1-3,5 | ✔ | 3,13 € |
| BTC60/3-5 | 60x60 | 3-5 | ✔ | 3,13 € |
| BTC70 | 70x70 | 2-5 | ✔ | 5,27 € |
| BTC80/2-4 | 80x80 | 2-4 | ✔ | 5,87 € |
| BTC80/3-5 | 80x80 | 2,5-5 | - | 6,14 € |
| BTC90/2-5 | 90x90 | 2-5 | - | 10,52 € |
| BTC100/1-4 | 100x100 | 1-4 | ✔ | 11,94 € |
| BTC100/5-8 | 100x100 | 5-8 | ✔ | 11,88 € |
| BTC120 | 120x120 | 2,5-6 | ✔ | 18,44 € |
| BTC150/5-8 | 150x150 | 5-8 | - | 31,23 € |
| BTC150/10-12.5 | 150x150 | 10-12,5 | - | 31,23 € |

*Depending on availability - Dimensions in mm

- ***Accessory for square tube structure***
- *Material: reinforced polyamide*





### Info.

- **Not sold individually, please contact us for details**

### Accessories

- **SER** *magnetic lock* **(tome 5 p.284)**
- **CHA** *hinge* **(tome 5 p.288)**
- **LOQ** *manual latch* **(tome 5 p.285)**



**Typical application**

### DISCOUNTS

| Qty | 1+ | 50+ | 100+ |
|---|---|---|---|
| Disc. | List | -5% | On request |

| Part number | Weight (kg) | Stock* | Price each 1 to 49 |
|---|---|---|---|
| BLOC-25 | 0,01 | - | 4,81 € |

**Depending on availability - Dimensions in mm*

# Panel stop

## BUT

## Plastic


- ***Accessory for square tube structure***
- *Material: reinforced polyamide*


**Info.**

- **Not sold individually, please contact us for details**

**Accessories**

- *Tube for structure* **TUBE** ***(tome 5 p.269)***








**Typical application**

**DISCOUNTS**

| Qty | 1+ | 50+ | 100+ |
|---|---|---|---|
| Disc. | List | -5% | On request |

| Part number | Weight (kg) | Stock* | Price each 1 to 49 |
|---|---|---|---|
| BUT40-15 | 0,01 | ✔ | 7,64 € |

**Depending on availability - Dimensions in mm*

# Panel holder

## Plastic

## BRI

- ***Accessory for square tube structure***
- *Materials:*
  *Clamp: reinforced polyamide*
  *Screws: stainless steel*




### Info.

- ***Not sold individually, please contact us for details***

### Accessories

- **PSP** *panel support profile* **(tome 5 p.287)**
- **BUT** *panel stop* **(tome 5 p.278)**






**Typical application**

### DISCOUNTS

| Qty | 1+ | 50+ | 100+ |
|---|---|---|---|
| Disc. | List | -5% | On request |

| Part number | S | Weight (kg) | Stock* | Price each 1 to 49 |
|---|---|---|---|---|
| BRI25-4 | 4 | 0,03 | ✔ | 5,29 € |
| BRI25-5 | 5 | 0,03 | ✔ | 5,29 € |
| BRI25-6 | 6 | 0,03 | ✔ | 5,29 € |

**Depending on availability - Dimensions in mm*