


Retaining cable for ball pin

CDRS



Avoids loss of ball pin

- Cable for use with BAB/S and BAB/S303 ball pins
- With loop on one end and circlip on the other
- Materials:
 - Cable - uncoated stainless steel
 - Circlip/Ring - stainless steel
- T° use max.: 250°C



Assembly

- Use a mallet to secure the circlip to the ball pin, it can be removed using a screwdriver as a lever.



Used with
BAB/S or BAB/S303 ball pin

DISCOUNTS

Qty	1+	6+	10+	25+
Disc.	List	-5%	-10%	On request

Part number	L	ØD	Use with	Weight (g)	Stock*	Price each 1 to 5
CDR8-150/S	150	8,0	BAB5, BAB6	6	-	10,26 €
CDR11-150/S	150	11,6	BAB8, BAB10	7	-	10,96 €
CDR17-150/S	150	17,0	BAB12, BAB16	8	-	11,85 €
CDR24-150/S	150	24,0	BAB20	12	-	14,46 €
CDR8-200/S	200	8,0	BAB5, BAB6	7	✓	10,55 €
CDR11-200/S	200	11,6	BAB8, BAB10	8	✓	11,26 €
CDR17-200/S	200	17,0	BAB12, BAB16	9	-	12,12 €

Dimensions in mm

Fax **0 825 88 6000**
Service 0,15 € / min
+ prix appel

cial2@hpceurope.com

HPC

SUPPLEMENT 2019

175

Our other products



ZBconique

Machined plastic
bevel gear , 1:1



MSP19

Masterplate®
glueable insert
Ø19/Ø20, Cylindrical
with nut



TMR

Rigid manual
tensioner, Adjustable



YG2

HEAVY DUTY spur
gear, Steel 35NCD6



DOMI120

Accessories, Fixing kit



PRF_CHA_D

Hinge and joint, Lift-
off hinge



CLASS

Stainless steel
indexing handle -
male, Stainless steel



P40

Worm and wheel gear
reducer, up to 18 Nm



PR820

Idler sprocket for slat
top chain, Rangs 820
and 815



PCLA_M

Technopolymer
clamping lever -
female, Plastic



MCL

Cylindrical threaded
sleeve, Cylindrical -
steel



CLLCLLP

Clevis components,
long version, Steel -
long range

Complementary products



BABS

630 Stainless steel
compact ball pin,
Hardened stainless
steel



BABS303

303 Stainless steel
compact ball pin,
Stainless steel 303



CDR

Retaining cable for
ball pin, Retaining
cable



BABV

Ball lock pins lockable
, Stainless steel