

Combination spanner



CM^{HD} Hygienic Usit[®] and Hygienic Design[®]

- Combination spanner to be used with protective inserts for mounting Hygienic Usit[®] and Hygienic Design[®] products

- Materials:

Spanner: Tool steel


Inserts: AlSi1MgMn

Advantages

- The protective caps have been specifically designed for fastening and un-fastening screwed connections with delicate surfaces.
- The protective caps will safely avoid the risk of contact corrosion with stainless steel screwed connections.
- The protective cap is safely held in the spanner thanks to its special form and a sprung clip.

Accessories

- * Use the CM/HD/CF insert with the open-ended spanner and the CM/HD/CO insert with the ring spanner. (cf. page 62)



DISCOUNTS

Qty	1+	5+	10+
Disc.	Net	-5%	On request

Part N°	SW	SW2*	A	B	L	Price each
						1 to 4
CM-10/HD	10	7	5,0	8,0	154,5	23,10 €
CM-11/HD	11	8	5,5	8,4	168,5	28,54 €
CM-13/HD	13	10	6,3	10,0	193,0	28,45 €
CM-16/HD	16	13	7,0	11,4	230,5	29,79 €
CM-19/HD	19	16	8,0	13,5	268,5	30,74 €
CM-21/HD	21	18	8,5	13,7	292,0	46,20 €
CM-27/HD	27	24	10,5	16,0	380,0	54,20 €

All dimensions in mm

Our other products



CHAFR-MINI
Miniature friction
hinge, Friction



LVT
Miniature motorised
actuator 2A, 2 amperes



SHSS
Shoulder screw
stainless steel 416,
Pre-treated 416
stainless steel



CHT
Asynchronous AC
motor 0.12 to 0.22kW,
0.12 to 0.22kW



TIF
Threaded rod -
DIN975, Stainless
steel A2



BAN
Angular clamp,
Standard



M1
Worm and wheel set,
Bronze



ACLEPP
Right angled bracket
for aluminium profile,
4 holes



CHV
Mechanical speed
variator, from 0,18 to
1,5kW



HCSS
Set screw with
hexagonal socket,
Cup point



PTA40
Articulated foot with
solid base foot Ø 40,
3000N



H0
Crossed helical gear
crossed axis at 90°,
Steel 20NCD2

Complementary products



VTSM
Ball head screws
Hygienic Design®,
Stainless steel



CM_CO
Tools Hygienic Usit®
and Hygienic
Design®, Protective
inserts for ...



CM_CO
Tools Hygienic Usit®
and Hygienic
Design®, Protective
inserts for ...