


Retaining cable for ball pin

CDRS



Avoids loss of ball pin

- Cable for use with BAB/S and BAB/S303 ball pins
- With loop on one end and circlip on the other
- Materials:
 - Cable - uncoated stainless steel
 - Circlip/Ring - stainless steel
- T° use max.: 250°C



Assembly

- Use a mallet to secure the circlip to the ball pin, it can be removed using a screwdriver as a lever.



Used with
BAB/S or BAB/S303 ball pin

DISCOUNTS

Qty	1+	6+	10+	25+
Disc.	List	-5%	-10%	On request

Part number	L	ØD	Use with	Weight (g)	Stock*	Price each 1 to 5
CDR8-150/S	150	8,0	BAB5, BAB6	6	-	10,26 €
CDR11-150/S	150	11,6	BAB8, BAB10	7	-	10,96 €
CDR17-150/S	150	17,0	BAB12, BAB16	8	-	11,85 €
CDR24-150/S	150	24,0	BAB20	12	-	14,46 €
CDR8-200/S	200	8,0	BAB5, BAB6	7	✓	10,55 €
CDR11-200/S	200	11,6	BAB8, BAB10	8	✓	11,26 €
CDR17-200/S	200	17,0	BAB12, BAB16	9	-	12,12 €

Dimensions in mm

0 825 88 6000
Service 0,15 € / min
+ prix appel


cial2@hpceurope.com

HPC

SUPPLEMENT 2019

175

Our other products



BCM_HPBT

Modular cylindrical brush, PBT polyester bristles



TCXR

Automatic chain tensioner, With steel sprocket



AC

Strike for toggle latch, 13mm



KGS

Ball screw, supplied by the metre, Rolled ball screw, per metre



MRAeco

Low cost quick link, Steel



BABreceptacle

Ball pin socket, Socket



BAP

Plastic clamping collar, Ø10 - Ø20



FBL6000_K13

Brush strip per meter PP fibres Ø0.2, Black striated polypropylene



RBGpl

Fixed castor with plate, Steel - grey rubber



PFC

Fixed rubber levelling foot, Levelling support for small parts



SH1

Parallel axis helical gear, Steel 20NCD2



PRF-SCREEN-4

Screen support, Support with 4 axes of rotation

Complementary products



BABS

630 Stainless steel compact ball pin, Hardened stainless steel



BABS303

303 Stainless steel compact ball pin, Stainless steel 303



CDR

Retaining cable for ball pin, Retaining cable



BABV

Ball lock pins lockable, Stainless steel