

Square hinge with riveted pin, drilled Eco

CHAC Sheet metal with rolled knuckle



- Hinge for plug door
- Riveted pin, half swaged
- Material:
Stainless steel 304
- Natural finish

stainless steel



Advantages

- Economic hinge



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	A	B	C	ØD	F	G	ØS	Weight (g)	Stock*	Price each 1 to 5
CHAC4040/SS	40	40	2	4	8	24	3,5	34	✓	14,69 €
CHAC5050/SS	50	50	2	6	8	34	4,0	61	✓	17,45 €
CHAC6060/SS	60	60	2	6	8	40	4,0	82	✓	19,89 €

*Depending on availability - Dimensions in mm





Square hinge with riveted pin, **not drilled**

Sheet metal with rolled knuckle **CHAC-NP**

- Hinge for plug door
- Riveted pin, leaves not offset
- Material:
 - CHAC-NP:** Steel hinge
 - CHAC-NP/SS:** Stainless steel 304
- Natural finish

Advantages

- Economic hinge



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	A	B	C	ØD	Weight (g)	Stock*	Price each
						1 to 5	
Steel							
CHAC4040-NP	40	40	2	4	34	✓	8,69 €
CHAC5050-NP	50	50	2	6	61	✓	10,68 €
CHAC6060-NP	60	60	2	6	82	✓	11,80 €
Stainless steel							
CHAC4040-NP/SS	40	40	2	4	34	✓	14,69 €
CHAC5050-NP/SS	50	50	2	6	61	✓	16,85 €
CHAC6060-NP/SS	60	60	2	6	82	✓	19,03 €

*Depending on availability - Dimensions in mm

Our other products



CLSCLP_SS
Clevis components,
short version,
Stainless steel - short
range



PO
Pull handle - Multi-
sector, Tapped
recessed insert



BMM
Knurled knob - male,
Knurled



WFRM
Flanged polymer nut,
Polymer (Iglidur®) - 1
thread



ZG125
Plastic spur gear,
Machined plastic
(delrin)




BPHF
Bull transfer unit push
fit, Heavy



CFS
Miniature cam
follower, Miniature



GFX
Curved tooth
coupling, economy
range, Steel and
polyamide



GMK17_P
Flat Guide, Flat guide
for conical profile



BLH20
Right angled gearbox,
from 0.53 to 1.77



PX
Optional output shaft
stainless steel, P
gearboxes single



GSI_A
Gas control screw for
gas spring, Gas
control screw

Complementary products



CHAC4040NP
Square hinge with
riveted pin, not
drilled, Square with
riveted pin,...



CHA60
Rectangular hinge,
drilled or countersunk,
Rectangular, drilled or
c...