

Square hinge with riveted pin, **drilled**

CHAC Sheet metal with rolled knuckle



- Hinge for plug door
- Riveted pin, half swaged
- Material:
Stainless steel 304
- Natural finish

stainless steel



Advantages

- Economic hinge



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	A	B	C	ØD	F	G	ØS	Weight (g)	Stock*	Price each 1 to 5
CHAC4040/SS	40	40	2	4	8	24	3,5	34	✓	14,69 €
CHAC5050/SS	50	50	2	6	8	34	4,0	61	✓	17,45 €
CHAC6060/SS	60	60	2	6	8	40	4,0	82	✓	19,89 €

*Depending on availability - Dimensions in mm





Square hinge with riveted pin, **not drilled**

Sheet metal with rolled knuckle **CHAC-NP**

- Hinge for plug door
- Riveted pin, leaves not offset
- Material:
 - CHAC-NP:** Steel hinge
 - CHAC-NP/SS:** Stainless steel 304
- Natural finish

Advantages

- Economic hinge



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	A	B	C	ØD	Weight (g)	Stock*	Price each
						1 to 5	
Steel							
CHAC4040-NP	40	40	2	4	34	✓	8,69 €
CHAC5050-NP	50	50	2	6	61	✓	10,68 €
CHAC6060-NP	60	60	2	6	82	✓	11,80 €
Stainless steel							
CHAC4040-NP/SS	40	40	2	4	34	✓	14,69 €
CHAC5050-NP/SS	50	50	2	6	61	✓	16,85 €
CHAC6060-NP/SS	60	60	2	6	82	✓	19,03 €

*Depending on availability - Dimensions in mm

Our other products



CHN_CHNSS

Straight long link chain, Galvanised steel



EKN

Bellows coupling Gerwah®, from 0.5 to 12Nm



J52

Spur gear coaxial gearbox, from 0.27 to 0.90 Nm - Inline



PCLA_M

Technopolymer clamping lever - female, Plastic




RAGFLOW

Floway2® roller track, Roller track



SLVHlok

Vertical toggle clamp, Vertical toggle clamp / horizontal foot



CYS

Internal circlip DIN472, internal DIN 472




SBF

Open flange bearing unit for food industry, cover




RLX

Free running conveyor roller, PVC



M2

Worm and wheel set, Machined plastic



PF20

Worm and wheel gear reducer, up to 5 Nm



HW_HT

Half-rail guide, Rail

Complementary products



CHAC4040NP

Square hinge with riveted pin, not drilled, Square with riveted pin,...



CHA60

Rectangular hinge, drilled or countersunk, Rectangular, drilled or c...