

Square hinge with riveted pin, **drilled**

CHAC Sheet metal with rolled knuckle



- Hinge for plug door
- Riveted pin, half swaged
- Material:
Stainless steel 304
- Natural finish

stainless steel



Advantages

- Economic hinge



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	A	B	C	ØD	F	G	ØS	Weight (g)	Stock*	Price each 1 to 5
CHAC4040/SS	40	40	2	4	8	24	3,5	34	✓	14,69 €
CHAC5050/SS	50	50	2	6	8	34	4,0	61	✓	17,45 €
CHAC6060/SS	60	60	2	6	8	40	4,0	82	✓	19,89 €

*Depending on availability - Dimensions in mm





Square hinge with riveted pin, **not drilled**

Sheet metal with rolled knuckle **CHAC-NP**

- Hinge for plug door
- Riveted pin, leaves not offset
- Material:
 - CHAC-NP:** Steel hinge
 - CHAC-NP/SS:** Stainless steel 304
- Natural finish

Advantages

- Economic hinge



DISCOUNTS

Qty	1+	6+	20+	50+
Disc.	List	-5%	-10%	On request

Part number	A	B	C	ØD	Weight (g)	Stock*	Price each
						1 to 5	
Steel							
CHAC4040-NP	40	40	2	4	34	✓	8,69 €
CHAC5050-NP	50	50	2	6	61	✓	10,68 €
CHAC6060-NP	60	60	2	6	82	✓	11,80 €
Stainless steel							
CHAC4040-NP/SS	40	40	2	4	34	✓	14,69 €
CHAC5050-NP/SS	50	50	2	6	61	✓	16,85 €
CHAC6060-NP/SS	60	60	2	6	82	✓	19,03 €

*Depending on availability - Dimensions in mm

Our other products



NT61
Spur gear coaxial gearbox, from 5 to 14 Nm - In-line




PTA150
Articulated levelling foot, pressed base Ø150, Ø 150



ZHG5
Plastic spur gear, Machined plastic (delrin)



PMC48_M8
Anti-vibration machine mount, Oval base plate



T5courroie
T type timing belt, T5 Steel cored polyurethane



PTGT
Tensioner pulley, For V belts



CLLCLLP
Clevis components, long version, Steel - long version



ACL-PL
Joining plate for aluminium profile, joint plate - 86x86 mm



PW_PWG1
Worm - precision range, Stainless steel



BLHT40
Right angled gearbox, from 4 to 10.30 Nm



CHMR40
Worm and wheel gear reducer, up to 57 Nm



PM3
Worm and wheel set, Non hardened steel

Complementary products



CHAC4040NP
Square hinge with riveted pin, not drilled, Square with riveted pin,...



CHA60
Rectangular hinge, drilled or countersunk, Rectangular, drilled or ...